

Bundling and Securing

Self-Affixing Cable Ties


Fir Tree Mount Cable Ties

2-Piece Fir Tree Mount and Cable Tie Assemblies

HellermannTyton's fir tree mounts provide a secure grip in a mounting hole. The mount can slide along the cable tie to adjust orientation as needed. Fir tree mounts are designed to provide a low insertion force and high extraction force. This mount is sold as an assembly with the cable tie.

Features and Benefits

- Friction tab inside the fir tree allows the tie to sit in mount without falling out prior to installation.
- Fir tree provides low insertion effort yet demonstrates high extraction resistance.
- Disc feature prevents rattling in high-vibration applications and protects against debris ingress.



PART NO.	TYPE	Min. Tensile Strength lbs. (N)	Max. Bundle Diameter in. (mm)	Length (L) in. (mm)	Mounting Hole Dia. in. (mm)	Panel Thickness in. (mm)	Material Cable Tie	Material Fir Tree	Color	Pkg. Qty.
156-00953	T30RFT4	30.0 (135.0)	1.4 (35.0)	6.0 (148.0)	0.13 - 0.16 (3.3 - 4.0)	0.04-0.12 (1.0-3.0)	PA66HS	PA66HIRHS	Black	500
150-55948	T30RFT5	30.0 (135.0)	1.4 (34.0)	6.0 (150.0)	0.17 - 0.2 (4.5 - 5.0)	0.03-0.12 (0.7-3.0)	PA46	PA46	Natural, Gray	500
150-55850		30.0 (135.0)	1.4 (34.0)	6.0 (150.0)	0.17 - 0.2 (4.5 - 5.0)	0.03-0.12 (0.7-3.0)	PA66HS	PA66HIRHS	Black	500
150-31090	T30RFT6LG	30.0 (135.0)	1.4 (30.0)	6.0 (148.0)	0.25 - 0.28 (6.5 - 7.0)	0.03-0.24 (0.75-6.0)	PA66HS	PA66HIRHS	Black	500
150-77940	T30RFT6	30.0 (135.0)	1.4 (35.0)	6.0 (148.0)	0.25 - 0.28 (6.4 - 7.1)	0.03-0.12 (0.75-3.0)	PA66HS	PA66HIRHS	Black	500
156-00057	T30RFT7	30.0 (135.0)	1.4 (35.0)	6.0 (150.0)	0.26 - 0.28 (6.5 - 7.0)	0.03-0.28 (0.8-7.0)	PA66HS	PA66HS	Black	500
156-00375	T30RFT8	30.0 (135.0)	1.4 (36.0)	6.0 (148.0)	0.3 - 0.31 (7.7 - 8.0)	0.03-0.31 (0.8-7.9)	PA66HS	PA66HS	Black	500
156-00089	T30RFT10	30.0 (135.0)	1.4 (35.0)	6.0 (148.0)	0.38 - 0.39 (9.7 - 10.0)	0.03-0.20 (0.8-5.0)	PA66HS	PA66HS	Black	500
156-00025	T50RFT5	50.0 (225.0)	2.0 (45.0)	7.9 (200.0)	0.17 - 0.2 (4.5 - 5.0)	0.03-0.12 (0.7-3.0)	PA66HS	PA66HIRHS	Black	500

Dimensions are approximate and subject to technical changes. Use Part No. for ordering and Type for specification purposes.
Installation tools: EVO7, EVO7SP, EVO9, EVO9HT, MK7P, MK7HT, MK9P.