

GC Wheel

GC is a sharp, green colored, and 99% silicon carbide abrasive.

【Applications】 Grinding tungsten carbide, alloy cast iron, non-ferrous metals, and non-metal (such as rubber, and plastic).



| Item No. | Size (mm) | | | Spec. | M.O.S. | Packing | Remarks |
|----------|-----------|------|-------|----------|--------|---------|---------|
| | O.D. | Thk. | Hole | | | | |
| S310010 | 100 | 25 | 15.88 | GC 120 H | 33 | 20 | |
| S310013 | 125 | 13 | 12.7 | GC 120 H | 33 | 20 | |
| S310035 | 150 | 13 | 12.7 | GC 120 H | 33 | 20 | |
| S310037 | 150 | 13 | 31.75 | GC 80 H | 33 | 20 | |
| S310041 | 150 | 16 | 12.7 | GC 80 H | 33 | 20 | |
| S310043 | 150 | 16 | 12.7 | GC 120 H | 33 | 20 | |
| S310390 | 150 | 19 | 12.7 | GC 120 H | 33 | 20 | |
| S310051 | 150 | 19 | 19.05 | GC 80 H | 33 | 20 | |
| S310389 | 150 | 19 | 19.05 | GC 120 H | 33 | 20 | |
| S310070 | 180 | 13 | 31.75 | GC 80 H | 40 | 20 | |
| S310071 | 180 | 13 | 31.75 | GC 80 I | 40 | 20 | |
| S310074 | 180 | 13 | 31.75 | GC 120 H | 40 | 20 | |
| S310076 | 180 | 16 | 31.75 | GC 100 H | 40 | 20 | |
| S310083 | 205 | 6.4 | 15.88 | GC 120 H | 40 | 20 | |
| S310086 | 205 | 6.4 | 25.4 | GC 120 H | 40 | 20 | |
| S310096 | 205 | 13 | 15.88 | GC 120 H | 40 | 20 | |
| S310097 | 205 | 13 | 15.88 | GC 120 I | 40 | 20 | |
| S310099 | 205 | 13 | 31.75 | GC 80 H | 40 | 20 | |
| S310104 | 205 | 13 | 31.75 | GC 120 H | 40 | 20 | |
| S310112 | 205 | 16 | 15.88 | GC 120 H | 40 | 20 | |
| S310116 | 205 | 19 | 15.88 | GC 80 H | 40 | 10 | |
| S310119 | 205 | 19 | 15.88 | GC 100 H | 40 | 10 | |
| S310120 | 205 | 19 | 15.88 | GC 120 H | 40 | 10 | |
| S310121 | 205 | 19 | 15.88 | GC 120 I | 40 | 10 | |
| S310123 | 205 | 19 | 19.05 | GC 120 H | 40 | 10 | |
| S310124 | 205 | 19 | 25.4 | GC 60 H | 40 | 10 | |
| S310126 | 205 | 19 | 25.4 | GC 80 H | 40 | 10 | |
| S310128 | 205 | 19 | 25.4 | GC 100 H | 40 | 10 | |

| Item No. | Size (mm) | | | Spec. | M.O.S. | Packing | Remarks |
|----------|-----------|------|-------|----------|--------|---------|---------|
| | O.D. | Thk. | Hole | | | | |
| S310131 | 205 | 19 | 25.4 | GC 120 H | 40 | 10 | |
| S310132 | 205 | 19 | 25.4 | GC 120 I | 40 | 10 | |
| S310133 | 205 | 19 | 25.4 | GC 120 J | 40 | 10 | |
| S310139 | 205 | 19 | 31.75 | GC 100 H | 40 | 10 | |
| S310158 | 205 | 25 | 25.4 | GC 120 H | 40 | 10 | |
| S310178 | 255 | 19 | 25.4 | GC 120 H | 33 | 10 | |
| S310182 | 255 | 25 | 19.05 | GC 60 I | 33 | 5 | |
| S310185 | 255 | 25 | 19.05 | GC 80 H | 33 | 5 | |
| S310192 | 255 | 25 | 19.05 | GC 120 H | 33 | 5 | |
| S310196 | 255 | 25 | 25.4 | GC 80 H | 33 | 5 | |
| S310198 | 255 | 25 | 25.4 | GC 80 I | 33 | 5 | |
| S310200 | 255 | 25 | 25.4 | GC 100 H | 33 | 5 | |
| S310202 | 255 | 25 | 25.4 | GC 120 H | 33 | 5 | |
| S310203 | 255 | 25 | 25.4 | GC 120 I | 33 | 5 | |
| S310221 | 305 | 19 | 25.4 | GC 120 H | 33 | 5 | |
| S310225 | 305 | 25 | 25.4 | GC 80 H | 33 | 5 | |
| S310230 | 305 | 25 | 25.4 | GC 120 H | 33 | 5 | |
| S310240 | 305 | 32 | 25.4 | GC 80 H | 33 | 3 | |
| S310241 | 305 | 32 | 25.4 | GC 80 I | 33 | 3 | |
| S310244 | 305 | 32 | 25.4 | GC 100 H | 33 | 3 | |
| S310247 | 305 | 32 | 25.4 | GC 120 H | 33 | 3 | |
| S310248 | 305 | 32 | 25.4 | GC 120 I | 33 | 3 | |
| S310263 | 305 | 38 | 25.4 | GC 120 H | 33 | 3 | |
| S310264 | 305 | 38 | 127 | GC 46 H | 33 | 3 | |
| S310282 | 355 | 25 | 127 | GC 120 H | 33 | 3 | |
| S310291 | 355 | 38 | 31.75 | GC 100 H | 33 | 2 | |
| S310292 | 355 | 38 | 31.75 | GC 120 H | 33 | 2 | |
| S310296 | 355 | 38 | 127 | GC 80 H | 33 | 2 | |
| S310301 | 355 | 50 | 31.75 | GC 80 H | 33 | 2 | |
| S310305 | 355 | 50 | 31.75 | GC 120 H | 33 | 2 | |
| S310388 | 355 | 50 | 38.1 | GC 120 H | 33 | 2 | |

Depressed Center Wheel

Flexible Depressed Center Wheel

Cutting-off Wheel

Coated Abrasives/ Non-Woven Abrasives

Alumina Fiber Stones

Mounted Wheel

Straight Wheel

Other Shapes

Diamond /CBN Wheel

Truing & Dressing Tools

Grinding & Cutting Fluids

Filter

Safety Products