


Name sticker



It is possible to set the terminal No. etc. on it. As the partitioning line is printed for TXC type, it is possible to attach it to terminal unit after setting a seal on it, and it is very convenient.

Type name	Type name		Applicable unit TX / TT Series	Material	L (length)	General mass (g)	Number of contents
	Width A	Width of partitioning line W					
TXC 07	9.5	Front	7.3	TX 7	Polyvinyl chloride (Thickness 0.5mm)	5m	37
		Back	8	TX 10S			
TXC 073	9.5	Front	7.3	TX 7	Polypropylene (Thickness 0.5mm)	5m	24
		Back	8	TX 10S			
TXC 1	9.5	Front	8	TX 10S	Polyvinyl chloride (Thickness 0.5mm)	5m	37
		Back	9.5	TX 10			
TXC 13	9.5	Front	8	TX 10S	Polypropylene (Thickness 0.5mm)	5m	26
		Back	9.5	TX 10			
TXC 2	9.5	Front	11.5	TX 20	Polyvinyl chloride (Thickness 0.5mm)	5m	37
		Back	14.5	TX 30			
TXC 23	9.5	Front	11.5	TX 20	Polypropylene (Thickness 0.5mm)	5m	24
		Back	14.5	TX 30			
TRC 21	9.5	Plain	TX · TT (Without TTJ8N)	Fiber (Thickness 0.5mm)	5m	32	1 pieces
TRC 21 L230					230m	1472	1 pieces
TRC 22					5m	37	1 pieces
TRC 22 L100					100m	740	1 pieces
TRC 23					5m	24	1 pieces
TRC 23 L100	100m	480	1 pieces				
TRC 11	6.5	Plain	TTJ8N, TTJ8NU, TR10SK, TR10K, TR20K, TXJ8, TXJ8Z, TEN8, TEN11, TEU8, TEU11	Fiber (Thickness 0.5mm)	5m	24	1 pieces
TRC 11 L230					230m	1104	1 pieces
TRC 12					5m	26	1 pieces
TRC 12 L100					100m	520	1 pieces
TRC 13					5m	18	1 pieces
TRC 13 L100	100m	360	1 pieces				
TXJC 51	5.5	Plain	TXJ7, TXJ7Z, TEN7	Fiber (Thickness 0.5mm)	5m	20	1 pieces
TXJC 52					5m	24	1 pieces
TXJC 53					5m	17	1 pieces
TXJC 53 L100					100m	340	1 pieces

CAUTIONS

- When you use the one made from fiber (TRC21, TRC11), it is not possible to print with auto printer. Stamp with rubber stamp and apply it with tape.
- When the number of pins increases, as the TXC type may generate gap because the tolerance is counted, please use it referencing the table below.

Acceptable maximum number of units of sticker with partitioning line

Terminal unit	Number of units
TX 7, TX10S	60
TX10	50
TX20	40
TX30	30

Name sticker of terminal block (part for maintenance)

The name sticker of assembled terminal block is prepared as a part for maintenance.

Type name of terminal block	name sticker
T 10	Dedicated 5.5 width × 1m made of fiber, sold by one piece (Thickness 1mm)
T 20	Dedicated 6.5 width × 1m made of fiber, sold by one piece (Thickness 1mm)
T 30	Dedicated 9.5 width × 1m made of fiber, sold by one piece (Thickness 1mm)
TC 60	Dedicated 9.5 width × 1m made of fiber, sold by one piece (Thickness 1mm)
TC 100	—
TC 200	—
TC 300B	—
TC 450B	—
TC 600B	—
TL 15	(TRC 11, 12 are used)
TL 25	(TRC 11, 12 are used)
TL 35	(TRC 21, 22 are used)
TC 10S	(TRC 21, 22 are used)