


# PVDF/FH

ポリビニリデンフルオライド / (+) サラ小ネジ  
Polyvinylidene-fluoride / Cross recessed flat head screw




品番 Product number		PVDF/FH-M○-L○						
M	M3	M4	M5					
ピッチ / Pitch	0.5	0.7	0.8					
D	6	8	10					
L	6	100	100	—				
	8	100	100	—				
	10	100	100	100				
	12	100	100	100				
	15	100	100	100				
	16	100	100	100				
	20	100	100	100				
	25	100	100	100				

販売単位 Quantity

# PVDF/BT

ポリビニリデンフルオライド / 六角ボルト  
Polyvinylidene-fluoride / Hexagon head bolt




品番 Product number		PVDF/BT-M○-L○						
M	M4	M5	M6	M8	M10	M12		
ピッチ / Pitch	0.7	0.8	1	1.25	1.5	1.75		
B × H	7×2.8	8×3.5	10×4	13×5.5	17×7	19×8		
L	10	100	100	100	100	—	—	
	12	—	100	100	100	—	—	
	15	100	100	100	100	50	—	
	16	—	—	100	—	—	—	
	20	100	100	100	100	50	50	
	25	100	100	100	100	50	50	
	30	—	100	100	100	50	50	
	35	—	100	100	100	50	50	
40	—	—	100	100	50	50		

販売単位 Quantity

# PVDF/CB

ポリビニリデンフルオライド / 六角穴付ボルト  
Polyvinylidene-fluoride / Hexagon socket head cap bolt



品番 Product number		PVDF/CB-M○-L○						
M	M3	M4	M5	M6	M8	M10	M12	
ピッチ / Pitch	0.5	0.7	0.8	1	1.25	1.5	1.75	
D × H	5.5×3	7×4	8.5×5	10×6	13×8	16×10	18×12	
B	2.5	3	4	5	6	8	10	
L	5	100	100	—	—	—	—	
	6	100	100	—	—	—	—	
	8	100	100	—	—	—	—	
	10	100	100	100	100	100	—	
	12	100	100	100	100	100	—	
	15	100	100	100	100	100	50	
	20	—	100	100	100	100	50	50
	25	—	—	100	100	100	50	50
	30	—	—	100	100	100	50	50
	35	—	—	100	100	100	50	50
40	—	—	—	100	100	50	50	

販売単位 Quantity

- NEW
- PC
- PPS
- RENY
- PEEK
- PVC
- PI
- PP
- PTEE
- PFA
- PVDF
- CERAMIC
- ワッシャー
- ローレット
- 特殊ボルト
- スペーサー
- ワッシャー
- ワッシャー
- 結束バンド
- アラバネ
- オメガ