










Accessories (Collet, etc.)

Collet	Code No.	Model	I.D.	Compatible model
 <p>Collet CHA Group</p>	91494	CHA-3.0AA	$\varnothing 3.0AA$ ※	CTS-3030 EM20-S6000 · EM25-S6000 EMS-3060A · NR-3080S ※ High precision type AA (Run-out Accuracy within 2 μm)
	91496	CHA-3.175AA	$\varnothing 3.175AA$ ※	
	91495	CHA-4.0AA	$\varnothing 4.0AA$ ※	
	91492	CHA-2.35	$\varnothing 2.35$	
	91430	CHA-3.0	$\varnothing 3.0$	
	91493	CHA-3.175	$\varnothing 3.175$	
	91440	CHA-4.0	$\varnothing 4.0$	
 <p>Collet CHA Group</p>	—	CHA-□□	$\varnothing 0.5, \varnothing 0.6, \varnothing 0.7, \varnothing 0.8, \varnothing 0.9$ $\varnothing 1.1, \varnothing 1.2, \varnothing 1.3, \varnothing 1.4, \varnothing 1.7, \varnothing 1.8, \varnothing 1.9$ $\varnothing 2.1, \varnothing 2.2, \varnothing 2.3, \varnothing 2.4, \varnothing 2.6, \varnothing 2.7, \varnothing 2.8, \varnothing 2.9$ $\varnothing 3.1, \varnothing 3.2, \varnothing 3.3, \varnothing 3.4, \varnothing 3.6, \varnothing 3.7, \varnothing 3.8, \varnothing 3.9$ $\varnothing 1.0, \varnothing 1.5, \varnothing 2.0, \varnothing 2.5, \varnothing 3.5$ $\varnothing 1.6$	
	92820	CHB-2.0	$\varnothing 2.0$	NR40-5100 ATC NRR-3060-NRR-2651 NR33-6000ATC-ESD
92830	CHB-3.0	$\varnothing 3.0$		
92893	CHB-3.175	$\varnothing 3.175$		
92835	CHB-3.5	$\varnothing 3.5$		
92840	CHB-4.0	$\varnothing 4.0$		
 <p>Collet CHK Group</p>	91597	CHK-3.0AA	$\varnothing 3.0AA$ ※	EM30-S6000 · EMA-3020K EMS-3060K · EMR-3008K NR-151E · NR-3060S NRF-3060S · NR-3060 NR-403E · RAS-151E RAX-271E · RAX-71E NRAF-5080 ※ High precision type AA (Run-out Accuracy within 2 μm)
	91598	CHK-3.175AA	$\varnothing 3.175AA$ ※	
	91599	CHK-4.0AA	$\varnothing 4.0AA$ ※	
	91600	CHK-6.0AA	$\varnothing 6.0AA$ ※	
	91601	CHK-6.35AA	$\varnothing 6.35AA$ ※	
	91592	CHK-2.35	$\varnothing 2.35$	
	91530	CHK-3.0	$\varnothing 3.0$	
	91593	CHK-3.175	$\varnothing 3.175$	
	91540	CHK-4.0	$\varnothing 4.0$	
	91560	CHK-6.0	$\varnothing 6.0$	
 <p>Collet CHK Group</p>	—	CHK-□□	$\varnothing 0.5, \varnothing 0.6, \varnothing 0.7, \varnothing 0.8, \varnothing 0.9$ $\varnothing 1.0, \varnothing 1.5, \varnothing 2.0, \varnothing 2.5, \varnothing 3.5, \varnothing 4.5, \varnothing 4.76, \varnothing 5.5$ $\varnothing 1.1, \varnothing 1.2, \varnothing 1.3, \varnothing 1.4, \varnothing 1.7, \varnothing 1.8, \varnothing 1.9$ $\varnothing 2.1, \varnothing 2.2, \varnothing 2.3, \varnothing 2.4, \varnothing 2.6, \varnothing 2.7, \varnothing 2.8, \varnothing 2.9$ $\varnothing 3.1, \varnothing 3.2, \varnothing 3.3, \varnothing 3.4, \varnothing 3.6, \varnothing 3.7, \varnothing 3.8, \varnothing 3.9$ $\varnothing 4.1, \varnothing 4.2, \varnothing 4.3, \varnothing 4.4, \varnothing 4.6, \varnothing 4.7, \varnothing 4.8, \varnothing 4.9$ $\varnothing 5.1, \varnothing 5.2, \varnothing 5.3, \varnothing 5.4, \varnothing 5.6, \varnothing 5.7, \varnothing 5.8, \varnothing 5.9$ $\varnothing 1.6, \varnothing 5.0$	
	91596	CHK-6.35	$\varnothing 6.35$	
 <p>Collet CHR Group</p>	91930	CHR-3.0	$\varnothing 3.0$	NR50-5100 ATC
	91993	CHR-3.175	$\varnothing 3.175$	
	91996	CHR-6.35	$\varnothing 6.35$	
	91920	CHR-2.0	$\varnothing 2.0$	
	91940	CHR-4.0	$\varnothing 4.0$	
 <p>Collet CHR RS Group</p>	91960	CHR-6.0	$\varnothing 6.0$	NR50-5100 ATC RS ※ Also available for NR50-5100 ATC
	93201	CHR-3.0RS	$\varnothing 3.0$	
	93202	CHR-3.175RS	$\varnothing 3.175$	
	93203	CHR-4.0RS	$\varnothing 4.0$	
	93204	CHR-6.0RS	$\varnothing 6.0$	
 <p>Collet CHS Group</p>	93205	CHR-6.35RS	$\varnothing 6.35$	RA-271E
	90592	CHS-2.35	$\varnothing 2.35$	
	90530	CHS-3.0	$\varnothing 3.0$	
	90593	CHS-3.175	$\varnothing 3.175$	
	90516	CHS-1.6	$\varnothing 1.6$	
 <p>Collet CHS Group</p>	—	CHS-□□	$\varnothing 0.8, \varnothing 0.9$ $\varnothing 1.0, \varnothing 2.0, \varnothing 2.5$ $\varnothing 1.1, \varnothing 1.2, \varnothing 1.3, \varnothing 1.4, \varnothing 1.5, \varnothing 1.7, \varnothing 1.8, \varnothing 1.9$ $\varnothing 2.1, \varnothing 2.2, \varnothing 2.3, \varnothing 2.4, \varnothing 2.6, \varnothing 2.7, \varnothing 2.8, \varnothing 2.9$	
	93092	CHSS-2.35	$\varnothing 2.35$	EMA-3020S
	93030	CHSS-3.0	$\varnothing 3.0$	
	93093	CHSS-3.175	$\varnothing 3.175$	
 <p>Collet CH8 Group</p>	—	CHSS-□□	$\varnothing 1.0, \varnothing 1.5, \varnothing 2.0, \varnothing 2.5$	
	91092	CH8-2.35	$\varnothing 2.35$	RA-151E
	91030	CH8-3.0	$\varnothing 3.0$	
	91093	CH8-3.175	$\varnothing 3.175$	
	—	CH8-□□	$\varnothing 0.8, \varnothing 0.9$ $\varnothing 1.0, \varnothing 1.5, \varnothing 2.0, \varnothing 2.5$ $\varnothing 1.1, \varnothing 1.2, \varnothing 1.3, \varnothing 1.4, \varnothing 1.6, \varnothing 1.7, \varnothing 1.8, \varnothing 1.9$ $\varnothing 2.1, \varnothing 2.2, \varnothing 2.3, \varnothing 2.4, \varnothing 2.6, \varnothing 2.7, \varnothing 2.8, \varnothing 2.9$	
—	CH8-□□	$\varnothing 0.8, \varnothing 0.9$ $\varnothing 1.0, \varnothing 1.5, \varnothing 2.0, \varnothing 2.5$ $\varnothing 1.1, \varnothing 1.2, \varnothing 1.3, \varnothing 1.4, \varnothing 1.6, \varnothing 1.7, \varnothing 1.8, \varnothing 1.9$ $\varnothing 2.1, \varnothing 2.2, \varnothing 2.3, \varnothing 2.4, \varnothing 2.6, \varnothing 2.7, \varnothing 2.8, \varnothing 2.9$		