

RUBBERIZED ABRASIVES

SHANK $\phi 3.0$

10 pcs./pack WA GC **Green Polisher**

Abrasive Power $\sim 30,000 \text{ min}^{-1}$ $\sim 40,000 \text{ min}^{-1}$ $\sim 30,000 \text{ min}^{-1}$

Grinding Power ★★★★★

Rubber Hardness Medium

Grit	Color	46721	46731	46741	46751	46761	46771
#150 (GC)	Green	46721	46731	46741	46751	46761	46771
#220 (WA)	Green	46722	46732	46742	46752	46762	46772
#320 (WA)	Green	46724	46734	46744	46754	46764	46774
#400 (WA)	Green	46723	46733	46743	46753	46763	46773

10 pcs./pack WA **High Shine Polisher**

Abrasive Power $\sim 30,000 \text{ min}^{-1}$ $\sim 24,000 \text{ min}^{-1}$ $\sim 20,000 \text{ min}^{-1}$

Grinding Power ★★★★★

Rubber Hardness Hard

Grit	Color	46802	46812	46822	46832
#120	Blue	46802	46812	46822	46832
#220	Green	46805	46815	46825	46835
#320	Violet	46803	46813	46823	46833
#500	Brown	46804	46814	46824	46834

SHANK $\phi 3.0$

10 pcs./pack WA **Green Polisher**

Abrasive Power ★★★★★

Grinding Power ★★★★★

Rubber Hardness Medium

Grit	Color	46861	46871
#120	Green	46861	46871
#180	Green	46862	46872
#320	Green	46863	46873
#400	Green	46864	46874

10 pcs./pack WA **Long Reach Power Polisher**

Abrasive Power $\sim 10,000 \text{ min}^{-1}$ $\sim 6,000 \text{ min}^{-1}$ $\sim 5,000 \text{ min}^{-1}$ $\sim 4,500 \text{ min}^{-1}$

Grinding Power ★★★★★

Rubber Hardness Medium

Grit	Color	46901	46911	46921	46931
#80	Red	46901	46911	46921	46931
#120	Dark Green	46902	46912	46922	46932
#180	Olive	46903	46913	46923	46933
#220	Green	46904	46914	46924	46934
#320	Brown	46905	46915	46925	46935

SHANK $\phi 3.0$

10 pcs./pack WA **Special Rubber Grindstone For High-Speed Rotation (For 60,000min⁻¹)**



Special rubber grindstones for high speed rotation.
Useful for grinding and polishing with IMPULSE & ESPERT 500 (Both Nakanishi Micro-grinder Series) because of long durability at high speeds of 60,000min⁻¹.

- Micro Air Grinder "IMPULSE".....Max. Speed: 60,000min⁻¹
- Brushless Micro-Grinder "ESPERT 500"Max. Speed: 50,000min⁻¹

Abrasive Power $\sim 60,000 \text{ min}^{-1}$

Grinding Power ★★★★★

Rubber Hardness Medium

Grit	Color	46951	46956	46961	46966
#80	Brown	46951	46956	46961	46966
#120	Black	46952	46957	46962	46967
#220	Red	46953	46958	46963	46968
#320	Violet	46954	46959	46964	46969

Diamond / CBN

Carbide Cutters

Specialty Tools

Mounted Points

Rubberized Abrasives

Flap Wheels

Polishing Brushes

Felt Bobs

Abrasive Compounds & Polishing Tools

NSK Exclusive Tools