


**CoroTurn® 107 boring bar for turning****Screw clamp design****Metric version**

	Spare parts			Included parts	Accessories
	1	2	3	4	5
Ordering code	Insert screw	Shim	Shim screw	Key	Screwdriver
A25T-SDUCR/L 11	5513 020-10			5680 049-01	5680 046-02
A25T-SDXCR/L 11	5513 020-10			5680 049-01	5680 046-02
A32T-SDUCR/L 11-X	5513 020-01	5322 263-01	5512 090-01	5680 049-01	5680 046-02
A16K-SRDDN 08-R	5513 020-43			5680 049-02	5680 046-02
A20M-SRXDR/L 08-R	5513 020-56			5680 043-10	5680 046-01
A20M-SRXDR/L 10-R	5513 020-43			5680 049-02	5680 046-02
A16R-SSKCR/L 09	5513 020-09			5680 049-01	416.1-864
A16R-SSKCR/L 09-R	5513 020-09			5680 049-01	416.1-864
A20S-SSKCR/L 09	5513 020-09			5680 049-01	416.1-864
A20S-SSKCR/L 09-R	5513 020-09			5680 049-01	416.1-864
A25T-SSKCR/L 12	5513 020-17			5680 049-02	416.1-864
A32T-SSKCR/L 12	5513 020-18	5322 420-02	5512 090-03	5680 049-02	416.1-864
A05F-STUCR/L 05-GR	5513 020-53			5680 041-03	
A06F-STFCR/L 06	5513 020-28			5680 051-01	
A06F-STFCR/L 06-R	5513 020-28			5680 051-01	
A06F-STUCR/L 05-GR	5513 020-53			5680 041-03	
A08H-STFCR/L 06	5513 020-28			5680 051-01	
A08H-STFCR/L 06-R	5513 020-27			5680 051-01	
A08H-STUCR/L 06-GR	5513 020-44			5680 041-03	
A10K-STFCR/L 09	5513 020-05			5680 051-02	5680 046-03
A10K-STFCR/L 09-R	5513 020-05			5680 051-02	5680 046-03
A10K-STUCR/L 06-GR	5513 020-28			5680 041-03	
A12M-STFCR/L 09	5513 020-05			5680 051-02	5680 046-03
A12M-STFCR/L 09-R	5513 020-05			5680 051-02	5680 046-03
A12M-STFCR/L 11	5513 020-03			5680 051-02	5680 046-03
A12M-STFCR/L 11-B1	5513 020-03			5680 051-02	5680 046-03
A12M-STFCR/L 11-RB1	5513 020-03			5680 051-02	5680 046-03
A16R-STFCR/L 11	5513 020-03			5680 051-02	5680 046-03
A16R-STFCR/L 11-B1	5513 020-03			5680 051-02	5680 046-03
A16R-STFCR/L 11-RB1	5513 020-03			5680 051-02	5680 046-03
A20S-STFCR/L 11	5513 020-03			5680 051-02	5680 046-03
A20S-STFCR/L 11-B1	5513 020-03			5680 051-02	5680 046-03
A20S-STFCR/L 11-RB1	5513 020-03			5680 051-02	5680 046-03
A25T-STFCR/L 11-RB1	5513 020-03			5680 051-02	5680 046-03
A25T-STFCR/L 16	5513 020-10			5680 049-01	5680 046-02
A32T-STFCR/L 16	5513 020-01	5322 320-01	5512 090-01	5680 049-01	5680 046-02
A40T-STFCR/L 16	5513 020-01	5322 320-01	5512 090-01	5680 049-01	5680 046-02

Keys (mm/Torx Plus) sizes, see page P4  
 For optional shims, see page A133.  
 Accessories, must be ordered separately.