


### ストレートリニアシャフト (S, SS, PS, NS) の規格長さ





型番	材質	表面処理
S	SUJ-2	—
SS	SUS440C相当	—
PS	SUJ-2	—
NS	SUJ-2	硬質クロムメッキ

型番	外径 D	シャフト長さ L													
		100	150	200	300	400	500	600	800	1000	1200	1500	2000	2500	3000
S	3	●	●	●	●	●	●	●	●	●					
	4	●	●	●	●	●	●	●	●						
	5	●	●	●	●	●	●	●	●						
	6	●	●	●	●	●	●	●	●	●					
	8	●	●	●	●	●	●	●	●	●	●				
	10	●	●	●	●	●	●	●	●	●	●	●			
	12	●	●	●	●	●	●	●	●	●	●	●			
	13	●	●	●	●	●	●	●	●	●	●	●			
	16	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	20		●	●	●	●	●	●	●	●	●	●	●	●	●
	25		●	●	●	●	●	●	●	●	●	●	●	●	●
	30			●	●	●	●	●	●	●	●	●	●	●	●
	35				●	●	●	●	●	●	●	●	●	●	●
40					●	●	●	●	●	●	●	●	●	●	
50						●	●	●	●	●	●	●	●	●	
60							●	●	●	●	●	●	●	●	

型番	外径 D	シャフト長さ L													
		100	150	200	300	400	500	600	800	1000	1200	1500	2000	2500	3000
SS	3	●	●	●	●	●	●	●	●	●					
	4	●	●	●	●	●	●	●	●						
	5	●	●	●	●	●	●	●	●						
	6	●	●	●	●	●	●	●	●	●					
	8	●	●	●	●	●	●	●	●	●	●				
	10	●	●	●	●	●	●	●	●	●	●	●			
	12	●	●	●	●	●	●	●	●	●	●	●			
	13	●	●	●	●	●	●	●	●	●	●	●			
	16	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	20		●	●	●	●	●	●	●	●	●	●	●	●	●
	25		●	●	●	●	●	●	●	●	●	●	●	●	●
	30			●	●	●	●	●	●	●	●	●	●	●	●
	35				●	●	●	●	●	●	●	●	●	●	●
40					●	●	●	●	●	●	●	●	●	●	
50						●	●	●	●	●	●	●	●	●	
60							●	●	●	●	●	●	●	●	

型番	外径 × 内径 D × d	シャフト長さ L													
		100	150	200	300	400	500	600	800	1000	1200	1500	2000	2500	3000
PS	10 × 4	●	●	●	●	●	●	●	●	●					
	12 × 6	●	●	●	●	●	●	●	●	●					
	13 × 7	●	●	●	●	●	●	●	●	●					
	16 × 9	●	●	●	●	●	●	●	●	●	●				
	20 × 14		●	●	●	●	●	●	●	●	●	●	●	●	●
	25 × 16		●	●	●	●	●	●	●	●	●	●	●	●	●
	30 × 17			●	●	●	●	●	●	●	●	●	●	●	●
	35 × 20				●	●	●	●	●	●	●	●	●	●	●
	40 × 22					●	●	●	●	●	●	●	●	●	●
50 × 25						●	●	●	●	●	●	●	●	●	
60 × 32							●	●	●	●	●	●	●	●	

型番	外径 D	シャフト長さ L													
		100	150	200	300	400	500	600	800	1000	1200	1500	2000	2500	3000
NS	3	●	●	●	●	●	●	●	●	●					
	4	●	●	●	●	●	●	●	●						
	5	●	●	●	●	●	●	●	●						
	6	●	●	●	●	●	●	●	●	●					
	8	●	●	●	●	●	●	●	●	●	●				
	10	●	●	●	●	●	●	●	●	●	●	●			
	12	●	●	●	●	●	●	●	●	●	●	●			
	13	●	●	●	●	●	●	●	●	●	●	●			
	16	●	●	●	●	●	●	●	●	●	●	●	●	●	●
	20		●	●	●	●	●	●	●	●	●	●	●	●	●
	25		●	●	●	●	●	●	●	●	●	●	●	●	●
	30			●	●	●	●	●	●	●	●	●	●	●	●
	35				●	●	●	●	●	●	●	●	●	●	●
40					●	●	●	●	●	●	●	●	●	●	
50						●	●	●	●	●	●	●	●	●	
60							●	●	●	●	●	●	●	●	