

Hand-held Loupes/Pocket Loupes (with light)

Stock 227 Items

1-1427

Prices displayed include 8% tax.

For Batteries, see p. 10-461 to 474

TRUSCO Stock 38,650 Items **Acrylic Rectangular Type Loupe** RoHS

ENGINEER Stock 641 Items **Hand Loupe "Monsieur Magni"** RoHS

Com Drawing



- Features**
- The use of an aspherical lens enables undistorted view throughout the field.
- Use**
- For general inspections requiring magnification and small letters such as in books etc.
- Materials**
- Lens: Acrylic
- Origin**
- Japan

Sublens




Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Magnification (times)	W x H (mm)	SPQ (piece)	Weight (g)
484-2987	TAKL-15	¥2,777	¥3,000	1.5	185 x 120	5	91
484-2995	TAKL-20	¥2,638	¥2,850	2.0	165 x 112	5	87
484-3002	TAKL-25	¥2,222	¥2,400	2.5	145 x 102	5	60

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items **Slide Pocket Loupe with LED** RoHS

Com Drawing



- Features**
- Slide type and convenient for storage in pocket.
 - The LED will light up when the lens is open.
 - Since it is equipped with LED, can be used even if it is dark.
- Use**
- For general inspection.
 - For magnifying small letters and parts.
- Specs**
- Power: Button Battery (CR2016) x 2 Pieces (Sold separately)
 - Size when stored: 90mm
 - Replacement Lamp: No
- Materials**
- Lens: Acrylic
 - Body: ABS Resin
- Origin**
- China



Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Magnification (times)	Lens Dimension (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
798-5436	TSPL-45	¥2,278	¥2,460	3	φ45	145	10	49

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items **Slide Pocket Loupe with LED** RoHS

Com Drawing



- Features**
- Slide type and convenient for storage in pocket.
 - The LED will light up when the lens is open.
 - Since it is equipped with LED, can be used even if it is dark.
- Use**
- For general inspection.
 - For magnifying small letters and parts.
- Specs**
- Power: Button Battery (CR2016) x 2 Pieces (Sold separately)
 - Size when in storage: 79mm
 - Replacement Lamp: No
- Materials**
- Lens: Acrylic
 - Body: ABS Resin
- Origin**
- China



Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Magnification (times)	Lens Dimension (mm)	Total Length (mm)	SPQ (piece)	Weight (g)
478-9326	TSPL-35	¥1,481	¥1,600	3.5	35	124	10	38

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock 38,650 Items **Card Type Loupe with LED** RoHS

Com Drawing



- Features**
- This card type compact loupe is convenient for keeping in a pocket.
 - A 45mm x 45mm 2x lens and a φ20 5x lens are integrated.
 - Since it is equipped with LED, can be used even if it is dark.
- Use**
- For general inspection.
 - For product inspection and document verification in dark places.
- Specs**
- Power: Button Battery (CR2016) x 2 Pieces (Sold separately)
 - Replacement Lamp: No
- Materials**
- Lens: Acrylic
- Origin**
- China



SPQ: 10 Pieces


Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Magnification (times)	Lens Dimension (mm)	W x D x Thickness (mm)	Weight (g)
478-9300	TCPL-45	¥1,545	¥1,670	2-5	45 x 45	85 x 54 x 9	31

Contact us: 0120-509-849 <http://www.orange-book.com/>

ESCHENBACH Stock 30 Items **Card Type Loupe "Easy Pocket"** RoHS

Com Drawing



- Features**
- The newly developed "diffractive aspherical lens" prevents scratches and soil, enabling high transparency and high magnification.
 - The LED light automatically turns on when the lens is opened. It automatically turns off when the lens is stored away.
 - It is a credit card size with the thickness of 6mm only.
- Use**
- For product inspection and document verification in dark places.
- Specs**
- Power supply: Lithium coin cell battery (CR2025) x 2 (included)
 - Replacement Lamp: No
- Materials**
- Lens: PXM Optical Plastic
- Origin**
- Germany

SPQ: 1 Piece

ESCHENBACH

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Magnification (times)	Lens Dimension (mm)	W x D x Thickness (mm)	Weight (g)
336-6201	1521-11	¥8,100	¥7,500	3	46 x 50	85 x 55 x 6	31
356-0198	1521-22	¥10,260	¥9,500	4	46 x 50	85 x 55 x 6	31

Contact us: 03-3293-8567 <http://www.stac-optik.co.jp/>

Optical Precision Measuring Instruments

Surface Roughness Testers

Shape Measuring Instruments

Stereo Microscopes

Microscopes

Illuminated Magnifiers

Lighting for Inspection

Loupe

Inspection Mirrors

Binoculars, Monocles

Drones

Wearable Cameras

Time Lapse Cameras

3D Printers