


Prices displayed include 8% tax.

TRUSCO  
 Stock 38,650 Items

## Trunk Handle (stainless steel)



- Features • Made of stainless steel and excellent in corrosion resistance.  
 Use • As a part of a member for machinery or as a handle.  
 Materials • Stainless Steel (SUS304)  
 Origin • China



Order Unit: 1 Piece (Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	W x H (mm)	Hole Diameter (mm)	Reference Working Load (kN)	SPQ (piece)	Weight (g)
284-8040	TTT-1	¥1,750	¥1,890	86 x 46	5.2	0.2	15	142
284-8058	TTT-2	¥1,713	¥1,850	122 x 78	5.4	0.2	15	142

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO  
 Stock 38,650 Items


## Trunk Handle with Spring



- Features • By mechanical spring attachment, it has no backlash of the handle due to vibration.  
 Use • For container and business equipment.  
 • For various cabinet, etc.  
 Origin • Japan



TT-105TC (steel)



(Unit: mm)

Item No.	A	B	L	H	P	P1	P2	t	ta	tb
TT-85 to	84	62	70	40	52	32	26	7	12	1.2
TT-105 to	105	75	88	47	65	40	30	8	13	1.5
TT-135 to	136	91	88	47	65	40	30	8	13	1.6

\*Product numbers ending with a G are those equipped with a rubber grip.

### Steel

- Materials • Steel (SPCC)  
 • Surface Treatment: Trivalent Chromate Plating

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	W x H (mm)	Hole Diameter (mm)	Reference Working Load (kN)	SPQ (piece)	Weight (g)
441-9227	TT-85TC	¥ 778	¥ 840	70 x 40	4.5	0.2	10	90
441-9235	TT-105TC	¥ 852	¥ 920	88 x 47	5.5	0.3	10	152
856-4060	TT-105TCG	¥1,221	¥1,320	88 x 47	5.5	0.3	10	159
441-9243	TT-135TC	¥1,481	¥1,600	88 x 47	5.5	0.3	10	178
856-4062	TT-135TCG	¥1,685	¥1,820	88 x 47	5.5	0.3	10	188

### Stainless Steel

- Materials • Stainless Steel (SUS304)

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	W x H (mm)	Hole Diameter (mm)	Reference Working Load (kN)	SPQ (piece)	Weight (g)
329-1634	TT-85S	¥1,481	¥1,600	70 x 40	4.5	0.2	10	82
329-1642	TT-105S	¥1,685	¥1,820	88 x 47	5.5	0.3	10	155
856-4059	TT-105SG	¥2,110	¥2,280	88 x 47	5.5	0.3	10	162
441-9251	TT-135S	¥1,990	¥2,150	88 x 47	5.5	0.3	10	180
856-4061	TT-135SG	¥2,453	¥2,650	88 x 47	5.5	0.3	10	190

Contact us: 0120-509-849 <http://www.orange-book.com/>

MK  
 Stock 88 Items

## Black Trunk Handle (steel)




- Features • A common handle for carrying box.  
 Use • Carrying boxes, etc.  
 Materials • Steel (SPCC)  
 Origin • Japan



C-540-70U

(Unit: mm)

Item No.	L	P	P1	D	D1	H	t	t1
C-540-70U	68.5	58	-	60	43	54	6	10
C-540-80U	83	63	45	76	44	73	7	11
C-540-90U	90	68	48	84	53	75	8	13
C-540-10U	102	76	50	95	59	85	9	15



Order Unit: 1 Piece (Price revision date: Jan, 2018) MARUKI HARDWARE CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	W x H (mm)	Hole Diameter (mm)	SPQ (piece)	Weight (g)
380-2876	C-540-70U	¥241	¥270	68.5 x 54	4.5	24	60
380-2884	C-540-80U	¥309	¥350	83.0 x 73	4.8	12	100
380-2892	C-540-90U	¥379	¥430	90.0 x 75	4.8	12	130
380-2868	C-540-10U	¥449	¥510	102.0 x 85	6.0	12	200

Contact us: 06-6262-0350 <http://www.maruki-mk.co.jp/>