


Prices displayed include 8% tax.

TRUSCO Stock 38,650 Items **Pipe Vice**



- Features
- Made with stout ductile cast iron, it has firm tightening and excellent durability.
 - For standard steel pipes. Origin • Taiwan

Order Unit: 1 Piece TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Height (mm)	Applicable Pipe	SPQ (piece)	Weight (kg)
488-8944	TPV-1	¥12,798	¥15,800	280	10A to 65A (3/8 to 2 1/2)	1	5.6
488-8979	TPV-2	¥17,820	¥22,000	300	10A to 100A (3/8 to 4)	1	8.6

Cap set for pipe vice

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	Compatible Model	SPQ (set)	Weight (g/set)
488-8952	TPV-1KNS	¥1,620	¥2,000	TPV-1	1	500
488-8987	TPV-2KNS	¥2,025	¥2,500	TPV-2	1	500


Shaft for pipe vice

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Compatible Model	SPQ (piece)	Weight (g)
488-8961	TPV-1SF	¥2,430	¥3,000	TPV-1	1	700
488-8995	TPV-2SF	¥2,835	¥3,500	TPV-2	1	900

Contact us: 0120-509-849 <http://www.orange-book.com/>

REX Stock 210 Items **Pipe Vice**



- Features
- Firmly tighten with excellent durability.
 - Can be used with VS4 (stand only).
 - For standard steel pipes. Origin • Taiwan

Warning
• Please prepare bolts and nut for installation separately.

Order Unit: 1 Piece REX INDUSTRIES Co.Ltd.


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Height (mm)	Applicable Pipe	SPQ (piece)	Weight (kg)
122-9133	PV-0	¥12,825	¥13,200	205 to 270	6A-50A (1/8-2)	2	3.0
122-9141	PV-1	¥16,605	¥17,100	250 to 340	6A-65A (1/8-2 1/2)	2	4.2
122-9150	PV-2	¥23,085	¥23,800	330 to 445	6A-80A (1/8-3)	2	8.2
122-9168	PV-3	¥28,350	¥29,200	350 to 495	6A-100A (1/8-4)	2	10.8
122-9176	PV-4	¥43,065	¥44,300	500 to 650	6A-150A (1/8-6)	1	15.3

Contact us: 0120-475-476 <http://www.rexind.co.jp/>

MCC Stock 405 Items **Pipe Vice**



- Features
- A pipe vice that has pursued its function. Origin • Japan




Order Unit: 1 Piece (Price revision date: Feb, 2016) MCC CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Height (mm)	Applicable Pipe	Weight (kg)
367-3235	PV-0200	¥13,346	¥17,300	295	6A to 50A (1/8 to 2)	3
367-3243	PV-0201	¥15,490	¥20,080	370	6A to 80A (1/8 to 3)	6
367-3251	PV-0202	¥24,362	¥31,570	430	15A to 100A (1/2 to 4)	9
367-3260	PV-0203	¥31,783	¥41,190	520	15A to 125A (1/2 to 5)	14

Contact us: 06-6747-6921 <http://www.mccc corp.co.jp/>

RIDGID Stock 913 Items **Bench York Vise**



- Features
- York and base are made of iron with excellent durability.
 - Jaw is quenched alloy steel and comes with easy-to-use pipe fixture and bender.
 - Can be used by placing on a workbench. Origin • USA

Item No.	Model Name
40080	21A
40090	23A
40100	25A
40110	27A

SPQ: 1 Piece

Order Unit: 1 Piece Ridge Tool Company

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Height (mm)	Applicable Pipe	Weight (kg)
495-0992	40080	¥ 60,912	¥ 56,400	205 to 260	6A to 50A (1/8 to 2)	4.0
495-1000	40090	¥ 84,564	¥ 78,300	275 to 370	6A to 80A (1/8 to 3)	9.0
495-1018	40100	¥ 95,256	¥ 88,200	325 to 445	6A to 100A (1/8 to 4)	12.6
495-1026	40110	¥131,760	¥122,000	435 to 610	6A to 150A (1/8 to 6)	29.6

Contact us: 03-5403-2951 <http://www.ridgid.jp/>

RIDGID Stock 913 Items **Portable York Vise**



- Features
- Can be easily attached to planks, workbench and pillars. Origin • USA

40125 (main body only)

Order Unit: 1 Piece (Price revision date: Jun, 2015) Ridge Tool Company

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Height (mm)	Applicable Pipe	SPQ (piece)	Weight (kg)
474-3482	40125	¥95,796	¥88,700	400 to 570	6A to 65A	1	7.0

Contact us: 03-5403-2951 <http://www.ridgid.jp/>

Threading Machines

Pipe Vices

Thread Cutting Oils

Pipe Cutters

Tube Cutters

Pipe Reamers

Copper Pipe Brushes

Tube Benders

Flaring Tools

Pipe Wrenches

Chain Wrenches

Belt Wrenches

Water Pump Pliers

Motor Wrenches

Plumbing Tools Sets

Plumbing Tools

Drain Cleaners

Pipe Inspection Equipments

Refrigerant Recovery Equipments

Vacuum Pumps

Manifolds

Air Conditioning -Related Articles