

Saber Saw Replacement Blades

Stock 291 Items

5-859

Prices displayed include 8% tax.

For Saber Saw Main Bodies, see p. 5-324 to 336

Cutting Supplies

TRUSCO Stock 38,650 Items

Saber Saw Blade



- Features**
- Adopted a unique blade shape design that guarantees outstanding sharpness and blade life.
 - For cutting wooden materials such as round material, square material, sheet material, etc.
- Use**
- Compatible Model Manufacturer: Compatible With All Manufacturers
- Specs**
- High Carbon Steel (HCS)
- Materials**
- High Carbon Steel (HCS)
- Origin**
- Taiwan



Estimated Unit Price per Sheet
¥509

Order Unit: 1 Bag

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Total Length (mm)	Thickness (mm)	Effective Cutting Length (mm)	Cutting Performance (mm)			Q'ty Per Bag (sheet)	Weight (g/bag)
								Steel Material	Wood	Wood (width)		
389-5254	THS1509-5P	¥2,546	¥2,750	9	150	1.4	130	-	75	-	5	80

Contact us:0120-509-849 <http://www.orange-book.com/>

MPS Stock 64 Items

Double Blade Type Saber Saw Blade "MULTI CUTTER"

RoHS



- Features**
- Edges with different pitches on both sides of the blade to enable continuous cutting work.
 - Suitable on sites where different materials need to be cut such as at demolition sites.
 - Uses high-grade raw materials and achieves both high cutting ability and durability.
 - For cutting metals and wood.
- Use**
- Compatible Models: Compatible With All Manufacturers
- Specs**
- Tri-metal
- Materials**
- Tri-metal
- Origin**
- Germany



Estimated Unit Price per Sheet
¥555 to ¥1,152

Order Unit: 1 Bag

(Price revision date: Jan, 2016) Monolithic Power Systems, Inc.


Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Total Length (mm)	Thickness (mm)	Effective Cutting Length (mm)	Cutting Performance (mm)		Q'ty Per Bag (sheet)	Weight (g/bag)
								Steel Material	Wood		
479-3536	4701-2	¥1,110	-	Under Side 14/Back Side 18/Tip 10	150	0.90	125	2 to 8	2 to 50	2	43.2
479-3544	4702-2	¥1,110	-	Under Side 10/Back Side 14/Tip 10	150	0.90	125	3 to 12	3 to 100	2	43.0
479-3552	4703-2	¥1,110	-	Under Side 6/Back Side 10/Tip 6	150	0.90	125	-	6 to 100	2	42.7
479-3561	4704-2	¥1,483	-	Under Side 10/Back Side 14/Tip 10	200	1.27	175	3 to 12	3 to 150	2	77.0
479-3579	4705-2	¥1,483	-	Under Side 6/Back Side 10/Tip 6	200	1.27	175	-	6 to 180	2	75.2
479-3587	4706-2	¥2,304	-	Under Side 6/Back Side 10/Tip 6	250	1.57	225	-	6 to 200	2	93.0
479-3595	4707-2	¥1,377	-	Under Side 6/Back Side 10/Tip 6	150	1.10	125	-	6 to 100	2	50.4

Contact us:03-3433-9841

BOSCH Stock 1,429 Items

Saber Saw Blade

RoHS



- Features**
- It is outstanding sharpness because it is processed with traditional quenching technology and advanced polishing technology.
 - Bimetal blade that does not snap, burn, and has long life.
 - For cutting wood and metal (wood and plywood containing nails, plastic, fiberglass).
- Use**
- Compatible Model: BOSCH, Makita, HITACHI, RYOBI, ASADA, MCC
- Specs**
- Bimetal
- Materials**
- Bimetal
- Origin**
- Switzerland

Estimated Unit Price per Sheet
¥437 to ¥697

Order Unit: 1 Bag

Bosch


Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Total Length (mm)	Thickness (mm)	Effective Cutting Length (mm)	Cutting Performance (mm)				Q'ty Per Bag (sheet)	Weight (g/bag)
								Wood Containing Nail, Plywood	Plastic, Glass Fiber	Soft Steel, Non-Ferrous	PVC Pipe		
498-6351	S511DF	¥2,187	¥2,700	6	100	0.90	80	10 to 50	8 to 50	-	-	5	230
733-5831	S711DF	¥2,673	¥3,300	6	150	1.25	130	10 to 100	8 to 50	-	-	5	70
733-5725	S3456XF	¥3,483	¥4,300	6 to 12	200	1.25	180	5 to 150	-	3 to 18	5 to 150	5	160

Contact us:0120-345-762 <http://www.bosch.co.jp/>

BOSCH Stock 1,429 Items

Saber Saw Blade

RoHS



- Features**
- It is outstanding sharpness because it is processed with traditional quenching technology and advanced polishing technology.
 - For cutting wood materials (wood materials, particle boards, cutting wooden pockets, plastic).
- Use**
- Compatible Model: BOSCH, Makita, HITACHI, RYOBI, ASADA, MCC
- Specs**
- Carbon Steel Tools
- Materials**
- Carbon Steel Tools
- Origin**
- Switzerland

Estimated Unit Price per Sheet
¥421 to ¥616

Order Unit: 1 Bag

Bosch

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Number of Ridges	Total Length (mm)	Thickness (mm)	Effective Cutting Length (mm)	Cutting Performance (mm)			Q'ty Per Bag (sheet)	Weight (g/bag)
								Particle Board	Cutting wooden pockets, Plastic	Coarse cutting wood		
733-5822	S644D	¥2,106	¥2,600	6	150	1.25	130	6 to 60	6 to 100	-	5	90
733-5563	S1111K	¥2,187	¥2,700	3	225	1.25	205	-	-	20 to 175	5	190
733-5709	S1542K	¥2,592	¥3,200	3	240	1.50	220	-	-	15 to 190	5	160
733-5717	S1617K	¥3,078	¥3,800	3	300	1.25	280	-	-	20 to 250	5	221

Contact us:0120-345-762 <http://www.bosch.co.jp/>

Please wear protective equipment to use safely.