


Prices displayed include 8% tax.

TRUSCO
 Stock 38,650 Items

Rubber Whetstone with Shaft for Aluminum (shaft diameter 3mm)



- Features**
- A grinding stone that prevents workpiece chips from adhering with a strong synthetic rubber having strong elasticity and crushing polycrystalline abrasive grains.
 - For grinding non-ferrous metals such as aluminum and copper.
- Use**
- Japan

Order Unit: 1 Box

TRUSCO NAKAYAMA CORPORATION

| Order Code | Item No. | Price (per box) | MSRP (per box) | Grain Size (#) | Outer Diameter x W x Shaft Diameter x Shaft Length (mm) | Max Working Rotation Speed (rpm) | Q'ty Per Box (piece) | SPQ (box) | Weight (g/box) |
|------------|----------|-----------------|----------------|----------------|---|----------------------------------|----------------------|-----------|----------------|
| 768-3545 | BL3204F | ¥1,907 | ¥2,060 | 320 | 4 x 13 x 3 x 30 | 30000 | 10 | 10 | 32 |
| 768-3553 | BL3206F | ¥2,046 | ¥2,210 | 320 | 6 x 17 x 3 x 30 | 30000 | 10 | 10 | 40 |
| 768-3561 | BL3208F | ¥2,148 | ¥2,310 | 320 | 8 x 20 x 3 x 30 | 30000 | 10 | 10 | 52 |
| 768-3570 | BL3210F | ¥2,323 | ¥2,510 | 320 | 10 x 20 x 3 x 30 | 30000 | 10 | 10 | 66 |

Estimated Unit Price per Piece
 ¥191 to ¥232

Contact us: 0120-509-849 <http://www.orange-book.com/>

MURAKI
 Stock 514 Items

High Speed Daiwa Rubber Grinding Wheel (shaft diameter 3mm)



- Features**
- Even with grinding and polishing of aluminum and stainless steel, it does not get clogged.
 - High rigidity by using stainless steel shank, it can be used even at high speed rotation.
 - 60000 rotation correspondence, a cleaner finished surface can be obtained.
 - Since scattering of the whetstone is unlikely to occur, safety and durability are improved.
 - Unlike flapwheel, dust is difficult to fly, contributing to improvement of work environment.
 - For standard steel materials such as soft steel and semi-soft steel.
 - Stainless steel, hardened steel, aluminum and others, especially when preventing burn.
- Use**
- Japan

#80/Color: Light Brown

Order Unit: 1 Bag

(Price revision date: Jun, 2015) MURAKI CO.,LTD.

| Order Code | Item No. | Price (per bag) | MSRP (per bag) | Grain Size (#) | Outer Diameter x W x Shaft Diameter x Shaft Length (mm) | Max Working Rotation Speed (rpm) | Q'ty Per Bag (piece) | SPQ (bag) | Weight (g/bag) |
|------------|----------|-----------------|----------------|----------------|---|----------------------------------|----------------------|-----------|----------------|
| 272-4910 | GRA8-4H | ¥1,959 | ¥2,450 | 80 | 4 x 13 x 3 x 30 | 60000 | 10 | 10 | 20 |
| 272-4928 | GRA8-6H | ¥2,114 | ¥2,570 | 80 | 6 x 16 x 3 x 30 | 60000 | 10 | 10 | 27 |
| 272-4936 | GRA8-8H | ¥2,191 | ¥2,670 | 80 | 8 x 17 x 3 x 30 | 60000 | 10 | 10 | 34 |
| 272-4944 | GRA8-10H | ¥2,391 | ¥2,920 | 80 | 10 x 17 x 3 x 30 | 60000 | 10 | 10 | 44 |

#120/Color: Blue

Order Unit: 1 Bag

(Price revision date: Jun, 2015)

| Order Code | Item No. | Price (per bag) | MSRP (per bag) | Grain Size (#) | Outer Diameter x W x Shaft Diameter x Shaft Length (mm) | Max Working Rotation Speed (rpm) | Q'ty Per Bag (piece) | SPQ (bag) | Weight (g/bag) |
|------------|-----------|-----------------|----------------|----------------|---|----------------------------------|----------------------|-----------|----------------|
| 272-4952 | GRA12-4H | ¥1,959 | ¥2,450 | 120 | 4 x 13 x 3 x 30 | 60000 | 10 | 10 | 20 |
| 272-4961 | GRA12-6H | ¥2,114 | ¥2,570 | 120 | 6 x 16 x 3 x 30 | 60000 | 10 | 10 | 27 |
| 272-4979 | GRA12-8H | ¥2,191 | ¥2,670 | 120 | 8 x 17 x 3 x 30 | 60000 | 10 | 10 | 34 |
| 272-4987 | GRA12-10H | ¥2,391 | ¥2,920 | 120 | 10 x 17 x 3 x 30 | 60000 | 10 | 10 | 44 |

#220/Color: Yellow Green

Order Unit: 1 Bag

(Price revision date: Jun, 2015)

| Order Code | Item No. | Price (per bag) | MSRP (per bag) | Grain Size (#) | Outer Diameter x W x Shaft Diameter x Shaft Length (mm) | Max Working Rotation Speed (rpm) | Q'ty Per Bag (piece) | SPQ (bag) | Weight (g/bag) |
|------------|-----------|-----------------|----------------|----------------|---|----------------------------------|----------------------|-----------|----------------|
| 272-4995 | GRA22-4H | ¥1,959 | ¥2,450 | 220 | 4 x 13 x 3 x 30 | 60000 | 10 | 10 | 20 |
| 272-5002 | GRA22-6H | ¥2,114 | ¥2,570 | 220 | 6 x 16 x 3 x 30 | 60000 | 10 | 10 | 27 |
| 272-5011 | GRA22-8H | ¥2,191 | ¥2,670 | 220 | 8 x 17 x 3 x 30 | 60000 | 10 | 10 | 34 |
| 272-5029 | GRA22-10H | ¥2,391 | ¥2,920 | 220 | 10 x 17 x 3 x 30 | 60000 | 10 | 10 | 44 |

Estimated Unit Price per Piece
 ¥195 to ¥239

Contact us: 03-3273-7511 <http://www.muraki-ltd.co.jp/>

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes