


Prices displayed include 8% tax.

TRUSCO **Stock 38,650 Items** **File Set**



- Features**
- Sharp dressing, excellent durability. For flat, the side (one side only) is also engraved with a blade.
  - Other shapes are engraved with blades all around.
  - This item is equivalent to JIS-B4704.
- Use**
- For grinding of iron, copper, brass, aluminum and plastics, etc.
- Materials**
- Hand, Half round: Alloy Tool Steel (SKS-8)
  - Round, Square, Triangle: Carbon Steel Tools (SK-2)
- Origin**
- Japan

**Warning**

- The 5 for assorted files refers to the total length. 5 pieces set=215mm
- When the file is clogged, clean it with a brush or the like.

**Shape: Flat**

Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	Total Length (mm)	Blade Length (mm)	SPQ (piece)	Weight (g)
432-8914	THI005-01-1P	¥ 741	¥ 800	5 Pieces Set Bastard	215	110	25	60
432-8922	THI005-02-1P	¥ 741	¥ 800	5 Pieces Set Second	215	110	25	60
432-8931	THI005-03-1P	¥ 1,065	¥ 1,150	5 Pieces Set Smooth	215	110	25	60
432-8949	THI005-04-1P	¥ 1,389	¥ 1,500	5 Pieces Set Dead Smooth	215	110	25	60

**Shape: Half Round**

Order Unit: 1 Piece

(Price revision date: Jan, 2017)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	Total Length (mm)	Blade Length (mm)	SPQ (piece)	Weight (g)
432-8884	THA005-01-1P	¥ 1,250	¥ 1,350	5 Pieces Set Bastard	215	110	25	57
432-8892	THA005-02-1P	¥ 1,203	¥ 1,300	5 Pieces Set Second	215	110	25	57
432-8906	THA005-03-1P	¥ 1,574	¥ 1,700	5 Pieces Set Smooth	215	110	25	57

**Shape: Round**

Order Unit: 1 Piece

(Price revision date: Jan, 2017)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	Total Length (mm)	Blade Length (mm)	SPQ (piece)	Weight (g)
432-8981	TMA005-01-1P	¥ 833	¥ 900	5 Pieces Set Bastard	215	110	25	45
432-8990	TMA005-02-1P	¥ 833	¥ 900	5 Pieces Set Second	215	110	25	45
432-9007	TMA005-03-1P	¥ 1,157	¥ 1,250	5 Pieces Set Smooth	215	110	25	45

**Shape: Square**

Order Unit: 1 Piece

(Price revision date: Jan, 2017)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	Total Length (mm)	Blade Length (mm)	SPQ (piece)	Weight (g)
432-8957	TKA005-01-1P	¥ 1,018	¥ 1,100	5 Pieces Set Bastard	215	110	25	52
432-8965	TKA005-02-1P	¥ 972	¥ 1,050	5 Pieces Set Second	215	110	25	52
432-8973	TKA005-03-1P	¥ 1,296	¥ 1,400	5 Pieces Set Smooth	215	110	25	52

**Shape: Triangular**


Order Unit: 1 Piece

(Price revision date: Jan, 2017)

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	Total Length (mm)	Blade Length (mm)	SPQ (piece)	Weight (g)
432-9015	TSA005-01-1P	¥ 1,157	¥ 1,250	5 Pieces Set Bastard	215	110	25	58
432-9023	TSA005-02-1P	¥ 1,111	¥ 1,200	5 Pieces Set Second	215	110	25	58
432-9031	TSA005-03-1P	¥ 1,481	¥ 1,600	5 Pieces Set Smooth	215	110	25	58

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items** **Super-cut File**



- Features**
- The cutting edge surface treatment (electrolytic polishing) realized the strongest sharpness.
  - Blade edge is like a knife and crumbs off easily.
  - The electrolytic polishing makes the recess of the concave deeper.
  - Can grind from wood, plastic to metal.
- Use**
- Wood, plastic, iron and stainless steel, etc.
- Specs**
- Grain Size: 02 (second), 03 (smooth)
- Materials**
- Alloy Tool Steel (SKS-8)
- Origin**
- Japan

**Warning**

- 5 to 12 pieces set of file set refers to the total length. 5 Pieces Set=215mm 8 Pieces Set=200mm 10 Pieces Set=185mm 12 Pieces Set=170mm
- When the file is clogged, clean it with a brush or the like.



The file is pointed and sharp.

Order Unit: 1 Piece

(Price revision date: Jan, 2017) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Type	Shape	Total Length (mm)	Blade Length (mm)	SPQ (piece)	Weight (g)
433-4931	TSHI005-02P	¥ 1,342	¥ 1,450	5 Pieces Set Second	Hand	215	110	25	60
433-4949	TSHI005-03P	¥ 1,944	¥ 2,100	5 Pieces Set Smooth	Hand	215	110	25	60
433-4957	TSHI008-02P	¥ 1,296	¥ 1,400	8 Pieces Set Second	Hand	200	100	25	39
433-4965	TSHI008-03P	¥ 1,851	¥ 2,000	8 Pieces Set Smooth	Hand	200	100	25	39
433-4973	TSHI010-02P	¥ 1,203	¥ 1,300	10 Pieces Set Second	Hand	185	85	25	28
433-4981	TSHI010-03P	¥ 1,713	¥ 1,850	10 Pieces Set Smooth	Hand	185	85	25	28
433-4990	TSHI012-02P	¥ 1,250	¥ 1,350	12 Pieces Set Second	Hand	170	70	25	13
433-5007	TSHI012-03P	¥ 1,620	¥ 1,750	12 Pieces Set Smooth	Hand	170	70	25	13

Contact us:0120-509-849 <http://www.orange-book.com/>

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes