

# Wrapping Film Sheets/Felt Sheets

The number next to the logo mark indicates items in stock for each brand.

Abrasives

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft

Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes



Stock 38,650 Items

## Lapping Film Polishing Agent



TLF Series

Estimated Unit Price per Sheet  
¥243



TLFC Series (cut type)

Estimated Unit Price per Sheet  
¥130

- Features**
- 10 bags that easy to purchase.
  - Ultra fine particle polishing agent is used.
  - The resin adhesive and the abrasive are uniformly coated polishing agent on the film substrate, making it possible to obtain a uniform finishing surface without deep scratches.
- Use**
- Polishing of precision equipment parts.
  - Polishing of printed circuit board and optical fiber.
  - Polishing of various rolls.
- Specs**
- Thickness: 75 μm
- Materials**
- Abrasive: Aluminum Oxidation
- Origin**
- Japan



Example

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Grain Size (#)	Color	W x L (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
473-6541	TLF-400	¥2,430	¥3,000	400	Light Blue	230 x 280	10	10	100
473-6559	TLF-600	¥2,430	¥3,000	600	Light Green	230 x 280	10	10	110
473-6567	TLF-1000	¥2,430	¥3,000	1000	Purple	230 x 280	10	10	95
473-6575	TLF-1500	¥2,430	¥3,000	1500	Skin Color	230 x 280	10	10	93
473-6583	TLF-2000	¥2,430	¥3,000	2000	Light Blue	230 x 280	10	10	89
473-6591	TLF-4000	¥2,430	¥3,000	4000	Pink	230 x 280	10	10	91
473-6605	TLF-8000	¥2,430	¥3,000	8000	Light Purple	230 x 280	10	10	89
473-6613	TLF-10000	¥2,430	¥3,000	10000	White	230 x 280	10	10	83
473-6621	TLF-20000	¥2,430	¥3,000	20000	White	230 x 280	10	10	83

TRUSCO NAKAYAMA CORPORATION

Cut Type

Order Unit: 1 Bag


Order Code	Item No.	Price (per bag)	MSRP (per bag)	Grain Size (#)	Color	W x L (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
473-6630	TLFC-400	¥1,296	¥1,400	400	Light Blue	115 x 140	10	10	26
473-6648	TLFC-600	¥1,296	¥1,400	600	Light Green	115 x 140	10	10	29
473-6656	TLFC-1000	¥1,296	¥1,400	1000	Purple	115 x 140	10	10	25
473-6664	TLFC-1500	¥1,296	¥1,400	1500	Skin Color	115 x 140	10	10	24
473-6672	TLFC-2000	¥1,296	¥1,400	2000	Light Blue	115 x 140	10	10	23
473-6681	TLFC-4000	¥1,296	¥1,400	4000	Pink	115 x 140	10	10	24
473-6699	TLFC-8000	¥1,296	¥1,400	8000	Light Purple	115 x 140	10	10	23
473-6702	TLFC-10000	¥1,296	¥1,400	10000	White	115 x 140	10	10	22
473-6711	TLFC-20000	¥1,296	¥1,400	20000	White	115 x 140	10	10	22

Contact us:0120-509-849 <http://www.orange-book.com/>



Stock 3,858 Items

## Wrapping Film Sheet (super thin film type)



569 Series

Estimated Unit Price per Sheet  
¥864

- Features**
- Extremely thin, has flexibility, and is ideal for precision polishing of rolls, curved surfaces, and slits.
- Origin**
- Japan

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Grain Size (#)	Color	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
477-1664	56961	¥4,320	¥4,000	320	Purple	5	1	80
833-8127	56962	¥4,320	¥4,000	400	Ivory	5	1	221
833-8128	56963	¥4,320	¥4,000	600	Green	5	1	86
833-8129	56964	¥4,320	¥4,000	800	Blue	5	1	155
833-8130	56965	¥4,320	¥4,000	1000	Orange	5	1	87
833-8131	56966	¥4,320	¥4,000	1200	Gray	5	1	132
477-1672	56967	¥4,320	¥4,000	1500	Yellow ochre	5	1	80
477-1681	56968	¥4,320	¥4,000	3000	Violet	5	1	80
477-1699	56969	¥4,320	¥4,000	6000	Light Blue	5	1	144
477-1702	56970	¥4,320	¥4,000	10000	Yellow	5	1	144

NAKANISHI,INC

Contact us:0289-64-3280 <http://www.nakanishi-inc.com/>



Stock 1,533 Items

## Felt Sheet



RD7001 (standard)

- Features**
- A polishing sheet which compressed fine wool at high density.
- Specs**
- Compatible materials: ceramics, glass, tool steel, alloy steel, carbide alloy, cermet, common steel, stainless steel, aluminum, copper
- Origin**
- Japan

Order Unit: 1 Sheet

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Size (mm)	Type	SPQ (sheet)	Weight (g)
751-0039	RD7001	¥2,614	¥2,420	250 x 250 x 1	Standard	1	58
751-0047	RD7002	¥3,089	¥2,860	250 x 250 x 2	Standard	1	105
751-0055	RD7003	¥3,920	¥3,630	250 x 250 x 3	Standard	1	144
751-0063	RD7011	¥3,089	¥2,860	250 x 250 x 1	Hard	1	63
751-0071	RD7012	¥3,445	¥3,190	250 x 250 x 2	Hard	1	101
751-0080	RD7013	¥4,277	¥3,960	250 x 250 x 3	Hard	1	146

MINITOR Co.Ltd

Contact us:03-3633-7181 <http://www.minitor.co.jp/>

