


TRUSCO Stock **38,650** Items

Blank Glass



- Features** • Low price type with cost emphasis.
Use • As a cover lens for shanding glass.
Specs • Applicable Models: HS/TPW-T/TPW-K/TWHM, etc.
Materials • Glass
Origin • Japan

Shielding Plate Mounting Method



- ① Prepare one shielding plate and two transparent cover plates.
- ② Place the transparent cover plates on the front and rear of the light-shielding plate to make 3 sheets set.
- ③ Attach the lens from the inside of the hand-held mask.

Order Unit: 1 Bag

(Price revision date: Jan, 2015) TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	L x W (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
228-2798	GT	¥3,055	¥3,300	50 x 103	100	5	2820
228-2836	P-GT	¥208	¥225	50 x 103	2	20	66

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock **38,650** Items

Transparent Plastic Cover Plate



- Features** • Light and hard to crack, it is strong against scratches.
 • Spatters are difficult to adhere. Being excellent in impact resistance, it prevents spatters from adhering on shielding plates.
Use • As a transparent plastic cover plate.
Specs • Applicable Models: HS/TPW-T/TPW-K/TWHM, etc.
Materials • Polycarbonate
Origin • Germany



- Features** • Shielding plate cuts harmful ultraviolet rays and infrared rays.
 • Light and hard to crack, it is strong against scratches.
 • Spatters are difficult to adhere.
 • The greater the shielding degree, the thicker it becomes.
 • JIS T8141 standard product.
 • For arc welding.
Use • For arc welding.
Specs • Applicable Models: HS/TPW-T/TPW-K/TWHM, etc.
Materials • Polycarbonate (hard coating specification)
Origin • Japan

Order Unit: 1 Bag

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Shielding Degree	L x W (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
284-7493	PC-9	¥10,785	¥11,650	#9	50 x 105	20	20	322
284-7507	PC-10	¥10,785	¥11,650	#10	50 x 105	20	20	322
228-2810	PC-11	¥10,785	¥11,650	#11	50 x 105	20	20	322
284-7515	P-PC-9	¥1,203	¥1,300	#9	50 x 105	2	20	40
284-7523	P-PC-10	¥1,203	¥1,300	#10	50 x 105	2	20	40
228-2852	P-PC-11	¥1,203	¥1,300	#11	50 x 105	2	20	40

Order Unit: 1 Bag TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per bag)	MSRP (per bag)	L x W (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
423-8401	TPCCS	¥3,425	¥3,700	50 x 105	20	20	216
423-8419	P-TPCCS	¥426	¥460	50 x 105	2	20	29

Contact us: 0120-509-849 <http://www.orange-book.com/>

Contact us: 0120-509-849 <http://www.orange-book.com/>

TRUSCO Stock **38,650** Items

Shielding Glass



- Features** • Low price type with cost emphasis.
 • It is strong against scratches.
 • The greater the shielding degree, the thicker it becomes.
 • It is a DIN EN 166 standard product.
Use • For arc welding.
Specs • Applicable Models: HS/TPW-T/TPW-K/TWHM, etc.
Materials • Glass
Origin • Germany

20 Sheets

Including 2 sheets

Order Unit: 1 Bag TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Bag

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Shielding Degree	L x W (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
409-8480	GC-8	¥4,397	¥4,750	#8	50 x 105	20	20	752
284-7108	GC-9	¥4,397	¥4,750	#9	50 x 105	20	20	752
284-7094	GC-10	¥4,397	¥4,750	#10	50 x 105	20	20	752
228-2780	GC	¥4,397	¥4,750	#11	50 x 105	20	20	752
409-8471	GC-12	¥4,397	¥4,750	#12	50 x 105	20	20	752

Order Code	Item No.	Price (per bag)	MSRP (per bag)	Shielding Degree	L x W (mm)	Q'ty Per Bag (sheet)	SPQ (bag)	Weight (g/bag)
409-8501	P-GC-8	¥472	¥510	#8	50 x 105	2	20	83
284-7124	P-GC-9	¥472	¥510	#9	50 x 105	2	20	83
284-7116	P-GC-10	¥472	¥510	#10	50 x 105	2	20	83
228-2828	P-GC	¥472	¥510	#11	50 x 105	2	20	83
409-8498	P-GC-12	¥472	¥510	#12	50 x 105	2	20	83

Contact us: 0120-509-849 <http://www.orange-book.com/>