


MXL

(ピッチ:2.032mm)

● ベルト歯形寸法




● ベルト呼称例

B 126 MXL 6.4

幅(mm)
タイプ記号
ベルト歯数
ベルト記号

● プーリ歯形寸法



● プーリ呼称例

P 20 MXL 6.4-6F

形状
ベルト幅(mm)
タイプ記号
歯数(溝数)
プーリ記号

MXLプーリ

P.132

参照

ベルトサイズ一覧表

呼称	ピッチ周長(mm)	歯数	呼称	ピッチ周長(mm)	歯数	呼称	ピッチ周長(mm)	歯数
B 39MXL	79.25	39	B128MXL	260.10	128	B 315MXL	640.08	315
B 40MXL	81.28	40	B129MXL	262.13	129	B 318MXL	646.18	318
B 41MXL	83.31	41	B130MXL	264.16	130	B 322MXL	654.30	322
B 42MXL	85.34	42	B131MXL	266.19	131	B 323MXL	656.34	323
B 43MXL	87.38	43	B132MXL	268.22	132	B 324MXL	658.37	324
B 45MXL	91.44	45	B134MXL	272.29	134	B 325MXL	660.40	325
B 46MXL	93.47	46	B135MXL	274.32	135	B 328MXL	666.50	328
B 48MXL	97.54	48	B136MXL	276.35	136	B 330MXL	670.56	330
B 49MXL	99.57	49	B137MXL	278.38	137	B 332MXL	674.62	332
B 50MXL	101.60	50	B138MXL	280.42	138	B 334MXL	678.69	334
B 52MXL	105.66	52	B140MXL	284.48	140	B 337MXL	684.78	337
B 53MXL	107.70	53	B142MXL	288.54	142	B 338MXL	686.82	338
B 54MXL	109.73	54	B144MXL	292.61	144	B 339MXL	688.85	339
B 55MXL	111.76	55	B148MXL	300.74	148	B 340MXL	690.88	340
B 56MXL	113.79	56	B150MXL	304.80	150	B 342MXL	694.94	342
B 58MXL	117.86	58	B151MXL	306.83	151	B 343MXL	696.98	343
B 59MXL	119.89	59	B154MXL	312.93	154	B 347MXL	705.10	347
B 60MXL	121.92	60	B155MXL	314.96	155	B 350MXL	711.20	350
B 61MXL	123.95	61	B156MXL	316.99	156	B 354MXL	719.33	354
B 62MXL	125.98	62	B158MXL	321.06	158	B 356MXL	723.39	356
B 63MXL	128.02	63	B159MXL	323.09	159	B 360MXL	731.52	360
B 64MXL	130.05	64	B160MXL	325.12	160	B 365MXL	741.68	365
B 65MXL	132.08	65	B162MXL	329.18	162	B 371MXL	753.87	371
B 67MXL	136.14	67	B163MXL	331.22	163	B 380MXL	772.16	380
B 68MXL	138.18	68	B165MXL	335.28	165	B 388MXL	788.42	388
B 69MXL	140.21	69	B166MXL	337.31	166	B 390MXL	792.48	390
B 70MXL	142.24	70	B167MXL	339.34	167	B 397MXL	806.70	397
B 71MXL	144.27	71	B169MXL	343.41	169	B 400MXL	812.80	400
B 72MXL	146.30	72	B170MXL	345.44	170	B 402MXL	816.86	402
B 73MXL	148.34	73	B171MXL	347.47	171	B 408MXL	829.06	408
B 74MXL	150.37	74	B175MXL	355.60	175	B 419MXL	851.41	419
B 75MXL	152.40	75	B177MXL	359.66	177	B 420MXL	853.44	420
B 76MXL	154.43	76	B180MXL	365.76	180	B 421MXL	855.47	421
B 77MXL	156.46	77	B184MXL	373.89	184	B 425MXL	863.60	425
B 78MXL	158.50	78	B186MXL	377.95	186	B 427MXL	867.66	427
B 79MXL	160.53	79	B190MXL	386.08	190	B 434MXL	881.89	434
B 80MXL	162.56	80	B192MXL	390.14	192	B 436MXL	885.95	436
B 81MXL	164.59	81	B194MXL	394.21	194	B 442MXL	898.14	442
B 82MXL	166.62	82	B195MXL	396.24	195	B 447MXL	908.30	447
B 83MXL	168.66	83	B200MXL	406.40	200	B 448MXL	910.34	448
B 84MXL	170.69	84	B205MXL	416.56	205	B 453MXL	920.50	453
B 85MXL	172.72	85	B210MXL	426.72	210	B 458MXL	930.66	458
B 86MXL	174.75	86	B212MXL	430.78	212	B 464MXL	942.85	464
B 87MXL	176.78	87	B216MXL	438.91	216	B 466MXL	946.91	466
B 88MXL	178.82	88	B220MXL	447.04	220	B 472MXL	959.10	472
B 89MXL	180.85	89	B221MXL	449.07	221	B 475MXL	965.20	475
B 90MXL	182.88	90	B222MXL	451.10	222	B 482MXL	979.42	482
B 91MXL	184.91	91	B224MXL	455.17	224	B 487MXL	989.58	487
B 92MXL	186.94	92	B228MXL	463.30	228	B 488MXL	991.62	488
B 94MXL	191.01	94	B230MXL	467.36	230	B 490MXL	995.68	490
B 95MXL	193.04	95	B232MXL	471.42	232	B 497MXL	1009.90	497
B 96MXL	195.07	96	B236MXL	479.55	236	B 498MXL	1011.94	498
B 97MXL	197.10	97	B239MXL	485.65	239	B 500MXL	1016.00	500
B 98MXL	199.14	98	B240MXL	487.68	240	B 522MXL	1060.70	522
B100MXL	203.20	100	B243MXL	493.78	243	B 535MXL	1087.12	535
B101MXL	205.23	101	B248MXL	503.94	248	B 537MXL	1091.18	537
B102MXL	207.26	102	B249MXL	505.97	249	B 540MXL	1097.28	540
B103MXL	209.30	103	B250MXL	508.00	250	B 543MXL	1103.38	543
B104MXL	211.33	104	B251MXL	510.03	251	B 548MXL	1113.54	548
B105MXL	213.36	105	B256MXL	520.19	256	B 562MXL	1141.98	562
B106MXL	215.39	106	B262MXL	532.38	262	B 571MXL	1160.27	571
B107MXL	217.42	107	B265MXL	538.48	265	B 591MXL	1200.91	591
B109MXL	221.49	109	B267MXL	542.54	267	B 599MXL	1217.17	599
B110MXL	223.52	110	B271MXL	550.67	271	B 612MXL	1243.58	612
B112MXL	227.58	112	B273MXL	554.74	273	B 622MXL	1263.90	622
B114MXL	231.65	114	B275MXL	558.80	275	B 648MXL	1316.74	648
B115MXL	233.68	115	B280MXL	568.96	280	B 694MXL	1410.21	694
B117MXL	237.74	117	B285MXL	579.12	285	B 913MXL	1855.22	913
B118MXL	239.78	118	B288MXL	585.22	288	B1189MXL	2416.05	1189
B120MXL	243.84	120	B290MXL	589.28	290			
B122MXL	247.90	122	B295MXL	599.44	295			
B123MXL	249.94	123	B300MXL	609.60	300			
B125MXL	254.00	125	B305MXL	619.76	305			
B126MXL	256.03	126	B310MXL	629.92	310			
B127MXL	258.06	127	B312MXL	633.98	312			