


RNYパッキン



RNYパッキン寸法表

単位: mm

呼び番号 標準(RN 922)	パッキンおよびみぞ寸法							併用バック アップリング	互換SKY パッキン
	d	D	H	G _A	G _B	d ₁ (参考)	ℓ		
RNY- 16	16	24	5.1	5.7	6.7	16.4	2.5	TCS- 24 × 16	SKY- 16
RNY- 18	18	26	5.1	5.7	6.7	18.4	2.5	TCS- 26 × 18	SKY- 18
RNY- 20	20	28	5.1	5.7	6.7	20.4	2.5	TCS- 28 × 20	SKY- 20
RNY- 22	22	30	5.1	5.7	6.7	22.4	2.5	TCS- 30 × 22	SKY- 22
RNY- 22.4	22.4	30	5.1	5.7	6.7	22.8	2.5	TCS- 30 × 22.4	SKY- 22.4
RNY- 25	25	33	5.1	5.7	6.7	25.4	2.5	TCS- 33 × 25	SKY- 25
RNY- 28	28	35.5	5.1	5.7	6.7	28.4	2.5	TCS- 35.5 × 28	SKY- 28
RNY- 30	30	40	6.2	7	8.5	30.5	3	TCS- 40 × 30	SKY- 30
RNY- 31.5	31.5	41.5	6.2	7	8.5	32	3	TCS- 41.5 × 31.5	SKY- 31.5
RNY- 32	32	42	6.2	7	8.5	32.5	3	TCS- 42 × 32	SKY- 32
RNY- 35	35	45	6.2	7	8.5	35.5	3	TCS- 45 × 35	SKY- 35
RNY- 35.5	35.5	45	6.2	7	8.5	36	3	TCS- 45 × 35.5	SKY- 35.5
RNY- 36	36	46	6.2	7	8.5	36.5	3	TCS- 46 × 36	SKY- 36
RNY- 40	40	50	6.2	7	8.5	40.5	3	TCS- 50 × 40	SKY- 40
RNY- 45	45	55	6.2	7	8.5	45.5	3	TCS- 55 × 45	SKY- 45
RNY- 45A	45	56	7.2	8	9.5	45.5	3	TCS- 56 × 45	SKY- 45A
RNY- 50	50	60	6.2	7	8.5	50.5	3	TCS- 60 × 50	SKY- 50
RNY- 55	55	65	6.2	7	8.5	55.6	3	TCS- 65 × 55	SKY- 55
RNY- 56	56	66	6.2	7	8.5	56.6	3	TCS- 66 × 56	SKY- 56
RNY- 60	60	70	6.2	7	8.5	60.6	3	TCS- 70 × 60	SKY- 60
RNY- 60A	60	71	7.2	8	9.5	60.6	3	TCS- 71 × 60	SKY- 60A
RNY- 63	63	73	6.2	7	8.5	63.6	3	TCS- 73 × 63	SKY- 63
RNY- 65	65	75	6.2	7	8.5	65.6	3	TCS- 75 × 65	SKY- 65
RNY- 65B	65	78	8.2	9	11	65.6	3.5	TCS- 78 × 65	—
RNY- 70	70	80	6.2	7	8.5	70.6	3.5	TCS- 80 × 70	SKY- 70
RNY- 70B	70	85	9.2	10	12	70.6	3.5	TCS- 85 × 70	—
RNY- 71	71	80	6.2	7	8.5	71.6	3.5	TCS- 80 × 71	SKY- 71
RNY- 75	75	85	6.2	7	8.5	75.6	3.5	TCS- 85 × 75	SKY- 75
RNY- 75B	75	90	9.2	10	12	75.6	3.5	TCS- 90 × 75	—
RNY- 80	80	90	6.2	7	8.5	80.6	3.5	TCS- 90 × 80	SKY- 80
RNY- 80B	80	95	9.2	10	12	80.6	4	TCS- 95 × 80	—
RNY- 85	85	100	9.2	10	12	85.6	4	TCS-100 × 85	SKY- 85
RNY- 90	90	105	9.2	10	12	90.6	4	TCS-105 × 90	SKY- 90
RNY- 100	100	115	9.2	10	12	100.6	4	TCS-115 × 100	SKY-100
RNY- 110	110	125	9.2	10	12	110.6	4	TCS-125 × 110	SKY-100 12 59
RNY- 112	112	125	8.7	10	12	112.6	4	TCS-125 × 112	SKY-112, 112A
RNY- 125	125	140	9.2	10	12	125.6	4	TCS-140 × 125	SKY-125
RNY- 140	140	155	9.2	10	12	140.6	4	TCS-155 × 140	SKY-140
RNY- 160	160	175	9.2	10	12	160.6	4	TCS-175 × 160	SKY-160
RNY- 180	180	200	12.2	13	15.5	180.7	5.5	TCS-200 × 180	SKY-180

★ご注文・お問い合わせは、呼び番号にてご指示下さい。

★表中・呼び番号が色地のものは、在庫しております。