


The number next to the logo mark indicates items in stock for each brand.

TRUSCO **Stock 38,650 Items**

Diamond Hand Polisher



- Features**
- There is no directionality. Can polish any direction from front to back and left and right.
 - Any hard material can be polished easily.
- Use**
- Polishing of carbide alloy, hardened steel, ceramics, glass, engraving blade and hardness rubber, etc.
 - Polishing of hardened material such as reinforced plastics.
- Materials**
- Carbon Steel for Structures (S45C)
- Origin**
- Japan



TRUSCO NAKAYAMA CORPORATION


Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Grain Size (#)	Shape	Total Length (mm)	Blade Length (mm)	SPQ (piece)	Weight (g)
272-6254	TDP-1	¥1,703	¥1,840	270	Sword Blade	200	50	10	36.5
272-6262	TDP-2	¥1,703	¥1,840	270	Half-round	200	50	10	49.6
272-6271	TDP-3	¥1,703	¥1,840	270	Hand	200	50	10	47.7
272-6289	TDP-5	¥2,222	¥2,400	270	Round	170	50	10	17.7
272-6297	TDP-6	¥2,222	¥2,400	270	Oval	170	50	10	8.3
272-6301	TDP-7	¥2,222	¥2,400	270	Triangle	170	50	10	9.5
272-6319	TDP-8	¥1,481	¥1,600	270	Hand Smooth	200	50	10	28.3
272-6327	TDP-9	¥3,795	¥4,100	270	Hand Thick	200	60	10	89.9

Contact us:0120-509-849 <http://www.orange-book.com/>

TRUSCO **Stock 38,650 Items**

Diamond Hand Lapper Set



- Features**
- Little clogging and several dozen times the durability of normal polishing cloth paper.
 - The model for the diamond hand lapper (GDA) is equipped with an elastic sponge sheet that fits perfectly in the palm of one's hand.
- Use**
- Glass, woodwork, aluminum, copper, plastic, and stone materials.
- Set Contents**
- Pad, replacement sheets #80, #180, #320, #400 x 1 of each
- Origin**
- Japan

TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Set

Order Code	Item No.	Price (per set)	MSRP (per set)	SPQ (set)	Weight (g/set)
171-4503	GDA-5ST	¥14,987	¥16,190	1	87.1

Replacement sheet Features • Because the pad is set on the sheet with Velcro, it can be exchanged with one touch.

Order Unit: 1 Sheet

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Grain Size (#)	L x W x Thickness (mm)	SPQ (sheet)	Weight (g)
171-4589	GDA-80	¥2,879	¥3,110	80	120 x 65 x 1.8	1	10.80
171-4597	GDA-180	¥2,879	¥3,110	180	120 x 65 x 1.8	1	11.45
171-4601	GDA-320	¥2,879	¥3,110	320	120 x 65 x 1.8	1	11.00
171-4619	GDA-400	¥2,879	¥3,110	400	120 x 65 x 1.8	1	11.05

Pad

Order Unit: 1 Sheet

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	L x W x Thickness (mm)	SPQ (sheet)	Weight (g)
171-4571	GDA-PT	¥3,444	¥3,720	120 x 65 x 43.0	1	42.80

Contact us:0120-509-849 <http://www.orange-book.com/>