

The number next to the logo mark indicates items in stock for each brand.

Grinding Wheels

Disk Papers

Papers for Double Action Sander

Nylon Discs

Urethane Discs

Felt Discs

Diamond Wheels

Grinding Wheels

Dressers

Flap Wheels

Nylon Wheel with Shaft
Shank Mounted Felt Wheels with Shaft

Bands

Shank Mounted Stones

Carbide Bars

Diamond Bars

CBN Bars

Files

Diamond Files

Grinding Stones

Abrasives

Sheet Sanding Papers

Abrasive Belts

Cup Brushes

Wheel Brushes with Shank

Hand Brushes

KANAI Stock 14 Items

New Travelon Sheet



NTS series

- Features**
- Fits nicely along the shape of work and is less likely to clog due to being a non-woven fabric structure.
 - Has excellent water resistance and oil resistance.
 - Does not create deep scratches.
 - Can be used for a wide range of applications from creating hairline finishes to rust removal.
- Use**
- Hairline finishing, paint removal, and rust removal.
- Materials**
- Fiber: nylon
- Origin**
- Japan

Item No.	Abrasive material
NTS-60	Aluminum Oxidation
NTS-150	
NTS-320	
NTS-800	Silicone Carbide
NTS-2000	

Order Unit: 20 Sheets

Kanai Juyo Kogyo Co.Ltd.

Order Code	Item No.	Price (per sheet)	MSRP (per sheet)	Q'ty Per Pack (sheet)	Finishing Equivalent Grit Designation (#)	Color	W x L (mm)	Weight (g)
364-0795	NTS-60	¥386*	¥-	20	60	Black	150 x 230	52
364-0761	NTS-150	¥219*	¥-	20	150	Ocher	150 x 230	24
364-0787	NTS-320	¥219*	¥-	20	320	Chestnut Color	150 x 230	22
364-0809	NTS-800	¥219*	¥-	20	800	Dark Gray	150 x 230	15
364-0779	NTS-2000	¥219*	¥-	20	2000	Light Gray	150 x 230	14

Contact us:06-6346-3351 <http://www.kanaijuyo.co.jp/>

TRUSCO Stock 38,650 Items

Steel Wool



TSW003-200

- Features**
- Special fibers processed into the form of a wool easily removes rust and dirt.
 - You can choose the thickness of the fiber according to the application.
 - Since the wool is produced without using oil, it can be used in combination with detergent and industrial oil.
 - Since the wool is in a tape form, it can be freely cut with scissors.
 - A 200g size that can be used up which eliminates waste and is economical.
- Materials**
- Iron
- Origin**
- Japan

Item No.	Main Use
TSW003-200	Polishing of metal, etc. Peeling of rust and paint. Removal of wax from floors
TSW0-200	Polishing and cleaning of metal and floors. Dirt removal of glass, tile, and aluminum products
TSW0000-200	Polishing and finishing of lacquer and varnish on furniture and woodwork items, etc. Dirt removal and finish polishing of metal.

Order Unit: 1 Piece

TRUSCO NAKAYAMA CORPORATION

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Finishing Equivalent Grit Designation (#)	Color	L x W x Thickness (mm)	SPQ (piece)	Weight (g)
489-2658	TSW003-200	¥370	¥400	3 (medium rough)	Silver	140 x 270 x 75	10	200
489-2666	TSW0-200	¥426	¥460	0 (small fine)	Silver	140 x 270 x 75	10	200
489-2640	TSW0000-200	¥713	¥770	0000 (super fine)	Silver	140 x 270 x 75	10	200

Contact us:0120-509-849 <http://www.orange-book.com/>

Warning

- Please discard immediately after use as it rusts once it contains water.

BONSTAR Stock 31 Items

Steel Wool (commercial 1-pound roll)



- Features**
- Since it was produced without using oil, can be used in combination with detergent and industrial oil.
- Origin**
- Japan

Bon Star Materials •Iron

BONSTAR SALES Co.Ltd.

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Finishing Equivalent Grit Designation (#)	Fiber Center Diameter Approximation (mm)	Package Size Vertical x Horizontal x Thickness (mm)	SPQ (piece)	Weight (g)
416-5501	B-204	¥2,031	¥2,150	0000 (super fine)	0.012	75 x 390 x 110	25	450
416-5497	B-203	¥1,607	¥1,700	000 (very fine)	0.014	75 x 390 x 110	25	450
416-5489	B-202	¥1,229	¥1,300	00 (medium fine)	0.020	75 x 390 x 110	25	450
416-5471	B-201	¥ 897	¥ 950	0 (small fine)	0.025	75 x 390 x 110	25	450
416-5519	B-205	¥ 897	¥ 950	1 (fine)	0.035	75 x 390 x 110	25	450
416-5527	B-207	¥ 897	¥ 950	2 (rough)	0.050	75 x 390 x 110	25	450
416-5535	B-208	¥ 897	¥ 950	3 (medium rough)	0.070	75 x 390 x 110	25	450
416-5543	B-209	¥ 897	¥ 950	4 (very rough)	0.080	75 x 390 x 110	25	450
416-5551	B-210	¥ 897	¥ 950	5 (super rough)	0.090	75 x 390 x 110	25	450

Sunrise Materials •Iron

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Finishing Equivalent Grit Designation (#)	Fiber Center Diameter Approximation (mm)	Package Size Vertical x Horizontal x Thickness (mm)	SPQ (piece)	Weight (g)
416-5659	SB-203	¥1,371	¥1,450	000 (very fine)	0.014	75 x 390 x 110	25	450
416-5641	SB-202	¥1,002	¥1,060	00 (medium fine)	0.020	75 x 390 x 110	25	450
416-5632	SB-201	¥ 728	¥ 770	0 (small fine)	0.025	75 x 390 x 110	25	450
416-5667	SB-204	¥ 728	¥ 770	1 (fine)	0.035	75 x 390 x 110	25	450
416-5675	SB-205	¥ 728	¥ 770	2 (rough)	0.050	75 x 390 x 110	25	450
416-5683	SB-206	¥ 728	¥ 770	3 (medium rough)	0.070	75 x 390 x 110	25	450

Stainless Steel Materials •Stainless Steel

Order Unit: 1 Piece

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Finishing Equivalent Grit Designation (#)	Fiber Center Diameter Approximation (mm)	Package Size Vertical x Horizontal x Thickness (mm)	SPQ (piece)	Weight (g)
416-5691	SW-201	¥5,670	¥6,000	F (fine)	0.040	75 x 390 x 110	25	450
416-5705	SW-202	¥5,670	¥6,000	M (medium)	0.060	75 x 390 x 110	25	450
416-5713	SW-203	¥5,670	¥6,000	C (coarse)	0.090	75 x 390 x 110	25	450

Contact us:03-3449-0216 <http://www.bonstar.co.jp/>

Warning

- Since bonther and sunrise go rusty once containing water moisture, please discard immediately after use.

