


Prices displayed include 8% tax.

For Single Wheels, see p. 8-1296

TRUSCO **Stock 38,650 Items** Wheel Conveyor (wheel diameter 25.4mm) **Made to Order**



- Features**
- It uses pressed wheels so it is lightweight and easy to handle, and it is easy to mount onto racks.
 - It has wheels with small diameters so it can even convey small workpieces smoothly.
- Use**
- For conveying parts between processes. For conveying items with unusual shape.
- Specs**
- Wheel: Pressed Steel
 - Load Per Wheel: 20kg
 - Wheel width: 9mm
- Materials**
- Frame: Hot dip zinc-plated steel plate
 - Wheel: Steel
- Origin**
- Japan




TRUSCO NAKAYAMA CORPORATION

Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★461-1811	V2509P-30-1000	¥ 6,369	¥ 6,880	30	1000	1	1.85
★461-1829	V2509P-30-1500	¥ 9,238	¥ 9,980	30	1500	1	2.78
★461-1837	V2509P-30-2000	¥ 12,118	¥ 13,090	30	2000	1	3.70
★461-1845	V2509P-35-1000	¥ 5,666	¥ 6,120	35	1000	1	1.68
★461-1853	V2509P-35-1500	¥ 8,220	¥ 8,880	35	1500	1	2.52
★461-1861	V2509P-35-2000	¥ 10,757	¥ 11,620	35	2000	1	3.36

Contact us: 0120-509-849 <http://www.orange-book.com/>

TS **Wheel Conveyor (wheel diameter 25mm)** **Made to Order** **RoHS**



- Features**
- φ25mm steel press wheels are used.
- Use**
- For conveying parts between processes. For conveying items with unusual shape.
- Specs**
- Wheel: Pressed Steel
 - Load per wheel: 7kg
 - Wheel width: 7.2mm
- Materials**
- Frame: Steel
 - Wheel: Steel
- Origin**
- Japan



Order Unit: 1 Piece | Factory direct | Shipping not included | TERAUCHI CORPORATION


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★462-4408	KR-A0-P30X900L	¥ 7,938	¥ 8,400	30	900	1	1.7
★462-4386	KR-A0-P30X1200L	¥ 9,639	¥ 10,200	30	1200	1	2.4
★462-4394	KR-A0-P30X1500L	¥ 11,435	¥ 12,100	30	1500	1	2.9
★462-4432	KR-A0-P50X900L	¥ 5,576	¥ 5,900	50	900	1	1.3
★462-4416	KR-A0-P50X1200L	¥ 6,615	¥ 7,000	50	1200	1	1.9
★462-4424	KR-A0-P50X1500L	¥ 7,844	¥ 8,300	50	1500	1	2.3

Contact us: 072-259-4584 <http://www.tsconveyor.co.jp/>

MISUZU **Wheel Conveyor (wheel diameter 38mm)** **Made to Order** **RoHS**



- Features**
- It is a general purpose type suitable for conveying various products. It is suitable for light load.
- Use**
- Conveying cardboard cases.
- Specs**
- Wheel: Pressed Steel
 - Load Per Wheel: 10kg
 - Wheel Width: 12mm
- Materials**
- Frame: Steel
 - Wheel: Steel
- Origin**
- Japan



MISUZU KOKI Co.Ltd.

Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands


Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★465-8884	MWF38T-0518	¥ 8,465	¥ 11,400	50	1800	1	5.7
★465-8892	MWF38T-0524	¥ 10,470	¥ 14,100	50	2400	1	7.4
★465-8906	MWF38T-0530	¥ 12,696	¥ 17,100	50	3000	1	9.3
★465-8914	MWF38T-0718	¥ 6,980	¥ 9,400	75	1800	1	4.9
★465-8922	MWF38T-0724	¥ 8,538	¥ 11,500	75	2400	1	6.2
★465-8931	MWF38T-0730	¥ 10,320	¥ 13,900	75	3000	1	7.9
★465-8949	MWF38T-1018	¥ 6,237	¥ 8,400	100	1800	1	4.5
★465-8957	MWF38T-1024	¥ 7,574	¥ 10,200	100	2400	1	5.7
★465-8965	MWF38T-1030	¥ 9,132	¥ 12,300	100	3000	1	7.2

Contact us: 059-397-3220 <http://www.misuzukoki.jp/>

MISUZU **Wheel Conveyor (wheel diameter 50mm)** **Made to Order** **RoHS**



- Features**
- The place wheels have plating finish and have a wide wheel width, therefore they are ideal specially for conveying cardboard cases without damaging the bottom.
- Use**
- Conveying cardboard cases.
- Specs**
- Wheel: Pressed Steel
 - Load per wheel: 15kg
 - Wheel width: 20mm
- Materials**
- Frame: Steel
 - Wheel: Steel
- Origin**
- Japan



MISUZU KOKI Co.Ltd.

Order Unit: 1 Piece | Factory direct | No freight charge | Excluding remote islands

Order Code	Item No.	Price (per piece)	MSRP (per piece)	Pitch (mm)	Conveyor Length (mm)	SPQ (piece)	Weight (kg)
★465-9139	MWS50T-0718	¥ 7,722	¥ 10,400	75	1800	1	5.8
★465-9147	MWS50T-0724	¥ 9,504	¥ 12,800	75	2400	1	7.5
★465-9155	MWS50T-1018	¥ 6,831	¥ 9,200	100	1800	1	5.2
★465-9163	MWS50T-1024	¥ 8,316	¥ 11,200	100	2400	1	6.0

Contact us: 059-397-3220 <http://www.misuzukoki.jp/>

Steel Roller Conveyors

Stainless Steel Roller Conveyors

Aluminum Roller Conveyors

Resin Roller Conveyors

Extension Roller Conveyors

Wheels Conveyors

Ball Casters Units

Upward Ball Casters

Downward Ball Casters

Upward/Downward Combined Use Ball Casters

Cleanroom Type Ball Casters

Ball Casters for Special Purpose

Motor Pulleys, Motor Rollers

Belt Conveyors

Mini Belt Conveyors

Belts