



Concrete Drill Bit **B Type**



- A wide range of sizes to meet the broad needs of the work environment.
- Demonstrate an outstanding cutting feel with uniquely designed cutting edge shape and angle employing ultra-hard tips with emphasis on durability.
- SKS(alloy tool steel) material is selected for the under 5.0 mm sizes from the cutting edge giving excellent abrasion and shock resistance. This reduces snapping and bending of drill bits to a minimum.



Applicable Electric Tool Percussion Drill



CONCRETE	BLOCK / BRICK	MORTAR
SLATE	ALC	JAPANESE WALL
PLASTERBOARD	STONE	PORCELAIN TILE

B Type (Straight) Blister pack

	Code	Diameter (mm)	Overall Length (mm)	Effective Length (mm)	Pcs./Box	
○	B2.5X85BP	*2.5	85	50	10	
	B2.6X85BP	*2.6				
	B2.8X85BP	*2.8				
◎	B3.0X85BP	3.0				
○	B3.2X85BP	3.2				
◎	B3.4X85BP	3.4				
◎	B3.5X85BP	3.5				
△	B3.8X85BP	3.8				
○	B4.0X85BP	4.0				
◎	B4.3X85BP	4.3				
	B4.4X85BP	*4.4				
◎	B4.5X85BP	4.5				
○	B4.8X85BP	4.8				
◎	B5.0X85BP	5.0				
	B5.3X100BP	5.3	100	65	10	
	B5.4X100BP	5.4				
○	B5.5X100BP	5.5				
◎	B6.0X100BP	6.0				
◎	B6.4X100BP	6.4				
△	B6.5X100BP	6.5				
	B6.6X100BP	*6.6				
○	B7.0X125BP	7.0	125	75	10	
	B7.2X125BP	*7.2				
△	B7.5X125BP	7.5				
○	B8.0X125BP	8.0				
◎	B8.5X125BP	8.5				
	B8.7X125BP	*8.7				
△	B9.0X150BP	9.0	150	90	10	
	B9.5X150BP	9.5				
○	B10.0X150BP	10.0				
◎	B10.5X150BP	10.5				
△	B11.0X150BP	11.0				

Items marked * are special size. Please confirm stock before ordering.

B Type (Combination Straight)

	Code		Diameter (mm)	Overall Length (mm)	Effective Length (mm)	Pcs./Box	
	Non-pack	Blister Pack					
	B11.5X200	B11.5X200BP	11.5	200	120	6	
○	B12.0X200	B12.0X200BP	12.0				
	B12.3X200	B12.3X200BP	*12.3				
○	B12.5X200	B12.5X200BP	12.5				
○	B12.7X200	B12.7X200BP	12.7				
	B13.0X200	B13.0X200BP	13.0				
	B13.5X200	B13.5X200BP	13.5				
△	B14.0X200	B14.0X200BP	14.0				
	B14.3X200	B14.3X200BP	14.3				
○	B14.5X200	B14.5X200BP	14.5				
	B15.0X200	B15.0X200BP	15.0				
	B16.0X240	B16.0X240BP	16.0	240	120	6	
	B16.5X240	B16.5X240BP	16.5				
	B17.0X240	B17.0X240BP	17.0				
	B17.5X240	B17.5X240BP	17.5				
△	B18.0X240	B18.0X240BP	18.0				
	B19.0X240	B19.0X240BP	19.0				
	B19.2X240	B19.2X240BP	*19.2				
	B20.0X240	B20.0X240BP	20.0				
	B21.0X240	B21.0X240BP	21.0				
	B21.5X240	B21.5X240BP	21.5				
	B22.0X240	B22.0X240BP	22.0				
	B23.0X280		23.0	280	140	3	
	B24.0X280		24.0				
	B25.0X280		25.0				
	B25.5X280		25.5				
	B26.0X280		26.0				
	B27.0X280		27.0				
	B28.0X280		28.0				
	B28.5X280		28.5				
	B29.0X280		29.0				
	B30.0X280		30.0				
	B32.0X280		32.0				
	B35.0X280		35.0	280	140	1	
	B38.0X280		38.0				
	B40.0X280		40.0				

Items marked * are special size. Please confirm stock before ordering.



TOOL BOX SET

There is also the tool box set which is convenient to carrying and receiving.

- [Concrete Drill Set]** 10 Pcs Set [TB-20]
 (Overall Length: 85 mm Type)
 3.2/3.5/4.3/4.5/4.8/5.0mm×each 1
 (Overall Length: 100 mm Type)
 6.0/6.4mm×each 1
 (Overall Length: 125 mm Type)
 8.0/8.5mm×each 1

*Products any size outside the standard are also available by special order. Contact us for terms and conditions, etc.