


Note that, for some of the types shown here, order might be unable to be received by the MISUMI Malaysia, Indonesia and/or India offices.

Aluminum Extrusions 15mm Square


Brackets for Aluminum Extrusions 15mm Square / Square Nuts for Aluminum Extrusions 15mm Square

Aluminum Extrusions 15mm Square




RoHS10

HFS3-1515 (Configurable Length Extrusion)
KHFS3-1515 (Fixed Length Extrusion)



ⓘ Cut surfaces are not anodized. ⓘ Material: A6N01SS-T5 ⓘ Surface Treatment: Anodize

Slot Details



Enlarged View of A


Part Number	L	Mass kg/m	Sectional Area mm ²	Cross Sectional Moment of Inertia mm ⁴		Unit Price (Less than 300mm)	Unit Price/m (300mm or More)	Unit Price 1 ~ 9 pc(s).	Volume Discount Rate 10~20
				lx	ly				
HFS3	1515	0.34	126	0.280x10 ⁴	0.280x10 ⁴				
KHFS3									

Ordering Example

Part Number	-	L
HFS3-1515	-	800
KHFS3-1515	-	2000


When L<300mm
Unit prices are indicated in the table regardless of the length.
When L≥300mm
Prices are calculated as follows:
Unit Price/m x Specified O.A.L. = Sales Price

Brackets for Aluminum Extrusions 15mm Square




RoHS10


HPTBS3
(Sheet Metal Bracket)



HBLPBS3
(Sheet Metal Blind Bracket)



HBLTBS3
(Extruded Brackets)




Type	Material	Surface Treatment
HPTBS3	SPOC	Trivalent Chromate
HBLPBS3		Trivalent Chromate
HBLTBS3	A6N01SS-T5	Clear Anodize

Part Number Type	Mass (g)	Applicable Extrusion	Applicable Screw, T Nut				Allowable Load (N)	Unit Price 1~99 pc(s).	Volume Discount Rate 100~200
			Screw	Quantity	T Nut	Quantity			
HPTBS3	8	HFS3-1515	CBM3-6	2	HNSQ3-3	2	160		
HBLPBS3	2		Set Screw M3x4 (Included)				140		
HBLTBS3	10		CBM3-8	2	HNSQ3-3	2	530		


ⓘ For orders larger than indicated quantity, please check with WOS.

Square Nuts for Aluminum Extrusions 15mm Square




RoHS10

HNSQ



ⓘ Material: SS400
ⓘ Surface Treatment: Trivalent Chromate

Example



Part Number		M	Applicable Extrusion	Unit Price		Volume Discount Rate	
Type	No.			1~4 pkg(s)	5~9	10~150	
HNSQ	3	3	HFS3-1515				

Ordering Example

Part Number	-	M
HPTBS3	-	
HBLPBS3	-	
HNSQ3	-	3