

Mushroom Shaped Plastic Knobs / Butterfly Shaped Plastic Knobs / Plastic Wing Knobs / Three Lobed Plastic Knobs


Mushroom Shaped Plastic Knobs




RoHS10

Type	Screw	Knobs		Screw	
		M Material	M Material	S Surface Treatment	S Surface Treatment
NMM	Threaded	Phenol Resin (Black)	SWCH12A	Trivalent Chromate	-
NMF	Tapped	-	Brass (Insert)	-	-

Threaded



Tapped




Part Number		L	Lf	H	d	Mass (g)		Unit Price	
Type	M (Coarse) - D					NMM	NMF	NMM	NMF
NMM (Threaded)	5-17	10	7	15	10	5	4		
	6-21			18	12	9	6		
NMF (Tapped)	6-25	15	11	22	14	12	9		
	8-33			30	18	26	19		

Ordering Example Part Number NMM5-17

Butterfly Shaped Plastic Knobs



Type	Screw	Knobs		Screw	
		M Material	M Material	S Surface Treatment	S Surface Treatment
NWGM	Threaded	Phenol	SS400	Trivalent Chromate	-



Part Number		L Selection	Mass (g)	Unit Price
Type	M (Coarse)			
NWGM	3	10	5	
	4	10 15	10	
	5	10 15	13	


Plastic Wing Knobs




RoHS10

Type	Screw	Knobs		Screw	
		M Material	M Material	S Surface Treatment	S Surface Treatment
NWGM	Threaded	ABS (Matt Black)	SWCH12A	Trivalent Chromate	-
NWGF	Tapped	-	Brass	-	-

Threaded



Tapped



Part Number		L	Lf	B	H	S	d	R	Mass (g)		Unit Price	
Type	M (Coarse) - D								NWGM	NWGF	NWGM	NWGF
NWGM	4-30	15	10	8	20	5	14	B/2	10	6		
	5-30			12								
	6-40			15	8							
	8-50	20	19	10	28	8	19		30	13		
	8-65	25	11	11	28	8	22		35	17		


Three Lobed Plastic Knobs




RoHS10

Type	Screw	Knobs		Screw	
		M Material	M Material	S Surface Treatment	S Surface Treatment
NTM	Threaded	Phenol	SWCH12A	Bright Chromate Plating (Matt Black)	-
NTLF	Tapped	-	Brass	-	-

Threaded



Tapped



Part Number		L Selection	Lf	D	d	H	S	Mass (g)		Unit Price	
Type	M (Coarse)							NTM	NTLF	NTM	NTLF
NTM	5	10 20	8.5	25	14	15	8	9	7		
	6	10 20	10	31	17	17	9.5	15	12		
	8	20 30	12	39	20	20	12	27	18		
	10	20 30	14	49	22	23	12	44	28		

Ordering Example Part Number - L
 NWGMC3 - 10
 NWGM5-30
 NTM8 - 30