


# Weld-On Fittings

## 90° Elbow Short



RoHS 10

Type	Material
WEJES	SUS304W



Part Number		(D)	L	T	Unit Price	
Type	No.				1 - 9 pc(s)	10 - 30 pcs.
WEJES	25A	34	25.4	2.8		
	32A	42.7	31.8	2.8		


For orders larger than indicated quantity, please check with WOS.

## 90° Elbow Long



RoHS 10

Type	Material
WEJELS	SUS304W



Part Number		(D)	L	T	Unit Price	
Type	No.				1 - 9 pc(s)	10 - 30 pcs.
WEJELS	15A	21.7	38.1	2.1		
	20A	27.2	38.1	2.1		
	25A	34	38.1	2.8		
	32A	42.7	47.6	2.8		


For orders larger than indicated quantity, please check with WOS.

## Tees



RoHS 10

Type	Material
WEJTS	SUS304W



Part Number		(D)	A	T	Unit Price	
Type	No.				1 - 9 pc(s)	10 - 30 pcs.
WEJTS	15A	21.7	25.4	2.1		
	20A	27.2	28.6	2.1		
	25A	34	38.1	2.8		
	32A	42.7	47.6	2.8		


For orders larger than indicated quantity, please check with WOS.

## Caps



RoHS 10

Type	Material
WEJCS	SUS304



Part Number		(D)	L	T	Unit Price	
Type	No.				1 - 9 pc(s)	10 - 30 pcs.
WEJCS	15A	21.7	25.4	2.1		
	20A	27.2	25.4	2.1		
	25A	34	38.1	2.8		
	32A	42.7	38.1	2.8		


For orders larger than indicated quantity, please check with WOS.

## Flanges



RoHS 10

Type	Material
SGPFRW	SS400
SUTFRW	SUS304



Part Number		D	(T)	P.C.D.	d	d1	Applicable Bolt Dia.	SGPFRW		SUTFRW	
Type	No.							Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SGPFRW	10A	90	12	65	15	17.8	M12	1 - 9 pc(s)	10 - 30 pcs.	1 - 9 pc(s)	10 - 30 pcs.
	15A	95	12	70	15	22.2	M12				
	20A	100	14	75	15	27.7	M12				
	25A	125	14	90	19	34.5	M16				


For orders larger than indicated quantity, please check with WOS.

## Blind Flanges



RoHS 10

Type	Material
SGPFRB	SS400
SUTFRB	SUS304



Part Number		D	(T)	P.C.D.	d	Applicable Bolt Dia.	SGPFRB		SUTFRB	
Type	No.						Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SGPFRB	10A	90	12	65	15	M12	1 - 9 pc(s)	10 - 30 pcs.	1 - 9 pc(s)	10 - 30 pcs.
	15A	95	12	70	15	M12				
	20A	100	14	75	15	M12				
	25A	125	14	90	19	M16				

For orders larger than indicated quantity, please check with WOS.



Ordering Example

Part Number  
WEJES25A