

Safety Protection Materials

D Type Rubber Bumpers for Corner / Safety Tapes



RoHS10

Standard Type


- PRGDSC** (Compact)
- PRGDSCY** (Compact, for Stripe)
- PRGDMC** (Standard)
- PRGDMCY** (Standard, for Stripe)

Hole Type

- PRGDSCH** (Compact)
- PRGDSCHY** (Compact, for Stripe)
- PRGDMCH** (Standard)
- PRGDMCHY** (Standard, for Stripe)

M Material
Main Body: Ethylene Rubber (EPDM)
Adhesive Part: Acrylic Adhesives
H Hardness: Shore A60

- ⚠ Only yellow bumpers are available for Stripe Type. Black painting is not available from MISUMI.
- ⚠ Adhesive is not applied to Hole Type.



*** Hole Machining Details**

Type	Screw Nominal Dia.	d	d1
PRGDSCH PRGDSCHY	5	6.0	11.0
PRGDMCH PRGDMCHY	6	7.0	13.5

⚠ Screw holes may be oval due to its machining characteristics.

Standard Type

Part Number Type	L Selection (mm)	A	W	R1	R2	t	a	b	c	s	Unit Price	Volume Discount Rate	
											1 ~ 3 pcs.	4 ~ 7 pcs.	8~30
Compact Type PRGDSC (Black) PRGDSCY (Yellow)	70	14	20	R10	R7	3	2	18	2	0.3			
Standard Type PRGDMC (Black) PRGDMCY (Yellow)	100	20	30	R15	R11	4	3	28	4	0.4			

- ⚠ Peel off backing paper to adhere it to an object. Clean the mating surface off oil and dust. ⚠ For orders larger than indicated quantity, please check with WOS.
- ⚠ Can be cut with a utility knife. ⚠ Adhesive Strength (180° Peeling): 16N/20mm Width (When affixed to SUS304) ⚠ Properties: see the Ethylene Rubber of P.391


Hole Type

Part Number Type	L Selection (mm)	H Selection (mm)	A	W	R1	R2	t	a	b	c	s	Unit Price	Volume Discount Rate	
												1 ~ 3 pcs.	4 ~ 7 pcs.	8~30
Compact Type PRGDSCH (Black) PRGDSCHY (Yellow)	70	20	14	20	R10	R7	3	2	18	2	0.3			
Standard Type PRGDMCH (Black) PRGDMCHY (Yellow)	100	30	20	30	R15	R11	4	3	28	4	0.4			


- ⚠ Can be cut with a utility knife. ⚠ Properties: see the Ethylene Rubber of P.391 ⚠ Adhesive is not applied to Hole Type. ⚠ For orders larger than indicated quantity, please check with WOS.

Ordering Example

Part Number	-	L	-	H
PRGDSC	-	70		
PRGDMCH	-	100	-	30



PRTRT



M Material
Main Body: Polyethylene Foam
Surface: Polyethylene Print
Adhesive Part: Acrylic Adhesives

Part Number		L(m)	Unit Price
Type	W Selection (mm)		
PRTRT	50	10	
	100		

- ⚠ L dimension is in meters.

Ordering Example

Part Number	
PRTRT50	