

Casters with Mounting Plates / Leveling Mounts



Leveling Mount Unit

Part Number		Allowable Load kN(kgf)	Mass (kg)	Component					Unit Price		Volume Discount Rate
Type	No.			Plate	Leveling Mount	Screw	Nut	Quantity	Quantity	1~8 pc(s).	
HAJPS	5	4.9(500)	0.45	HAJP5	NFJN12-100	CBM5-10	4	HNTT5-5	4		
	6		0.46	HAJP6		CBM6-12		HNTT6-6			
	8*	16.6(1700)	1.15	HAJPC8	FJFN16-150	CBM8-20	8	HNTT8-8	8		
	5050			HAJPC5050		CBM6-15		HNTT6-6			
	6060		1.6	HAJPC6060	FJFN20-150	CBM8-25	8	HNTT8-8			
	8080		2.5	HAJPC8080							
9090	39.2(4000)	2.9	HAJPC9090								

8* is used in common with 8-45. Washers are included with HAJPS8080 only.
 No. 6060, 8080 and 9090 are applicable to HFS6-6060, HFS8-8080 and HFS8-9090.

RoHS 10



Plate with Caster Unit (Caster with Stopper)

Part Number		Allowable Load kN(kgf)	Mass (kg)	Component					Unit Price		Volume Discount Rate
Type	No.			Plate	Caster	Screw	Nut	Quantity	Quantity	1~8 pc(s).	
HCHPS	5	0.9(100)	0.69	HAJP5	HCHAS12-100	CBM5-10	4	HNTT5-5	4		
	6	1.4(150)	0.7	HAJP6	HCHAS12-150	CBM6-12		HNTT6-6			
	8*	1.7(170)	1.8	HAJP8	HCHAS16-170	CBM8-20	HNTT8-8				

8* is used in common with 8-45.
 No. 5 and 6 apply to extrusions with 6-slot Width 20 Square Type and 8-slot Width 30 Square Types. No. 8 applies to extrusions 10-slot Width 40 and 45 Square Type.

RoHS 10



Leveling Mount + Plate with Caster Unit (Swivel Caster)

Part Number		Caster Allowable Load kN(kgf)	Leveling Mount Allowable Load kN(kgf)	Mass (kg)	Component						Unit Price		Volume Discount Rate			
Type	No.				Plate	Leveling Mount	Caster		Extrusion Mounting		Nut	Quantity		1~8 pc(s).	9~20	
HAJCHP	5	0.9(100)	4.9(500)	0.86	HAJPC5	NFJN12-100	HCHA12-100	-	-	CBM5-10	4	HNTT5-5	4			
	2525				HAJPC2525											
	54040	16.6(1700)	1.62	HAJPC54040	NFJN16-150	CHJF50S	CBM6-10	4	CBM5-15	8	HNTT5-5	8				
	6												4.9(500)	0.9	HAJPC6	NFJN12-100
	8*	1.7(170)	16.6(1700)	2.2	HAJPC8	FJFN16-150	CHJF50S	CBM6-10	4	CBM8-20	8	HNTT8-8	8			
	5050				HAJPC5050					CBM6-15		HNTT6-6				
	6060			1.4(150)	1.9	HAJPC6060	FJFN20-150	CSHN-S75-H	CBM8-12	8	CBM8-25	8	HNTT8-8	8		
	8080			2.9(300)	3.4	HAJPC8080										
	9090	39.2(4000)	3.9	HAJPC9090												

8* is used in common with 8-45. Washers are included with HAJCHP8080 only.

RoHS 10



Ordering Example Part Number
HAJCHP6060



Example

Mounting Example

● Leveling Mount Plate Mounting

● Mounting of Plate with Caster

● Mounting of Leveling Mount + Plate with Caster

● Mounting of HAJPD (Next Page)

