



Economy Type Post-Assembly Insertion Screws / Pre-Assembly Insertion Screws for Aluminum Extrusions For 6 Series (Slot Width 8mm)




Economy Type of Post-Assembly Insertion Screw is offered. (This type is priced approx. 50% lower than HATLSN6-6 of Post-Assembly Insertion Screw.)

Economy Type Post-Assembly Insertion Screw




* Electrically conductive RoHS10

HATL6-6



Material: SWRCH35K (Carbon Steel Wire Rod)
Surface Treatment: Trivalent Chromate


Effective Length of Economy Type Post-Assembly Insertion Screws M6




Slot of Aluminum Extrusion

Part Number	L	H	Applicable Extrusion (Series)	Reference Tightening Torque (N·m)	Unit Price 1~29 pc(s).	Volume Discount Rate 30~149	Volume Discount Rate 150~600
HATL6-6	13	12.0	6 Series	11.7			
	17	17.0					
	22	22.0					

Ordering Example: Part Number - L
HATL6-6 - 17




Post-Assembly Insertion Screw




* Electrically conductive RoHS10

HATLSN6-6



Material Nuts: SUS316 Equivalent (Sintered) Screw: SUS304

Effective Length of Post-Assembly Insertion Screws M6




Slot of Aluminum Extrusion

Part Number	L	H	Applicable Extrusion (Series)	Reference Tightening Torque (N·m)	Unit Price 1~29 pc(s).	Volume Discount Rate 30~149	Volume Discount Rate 150~600
HATLSN6-6	13	12.0	6 Series	11.7			
	17	17.0					
	22	22.0					


Ordering Example: Part Number - L
HATLSN6-6 - 17

Pre-Assembly Insertion Screw




* Electrically conductive RoHS10

HNTLSN6-6



Material Nuts: SUS316 Equivalent (Sintered) Screw: SUS304

Effective Length of Pre-Assembly Insertion Screws M6




Slot of Aluminum Extrusion

Part Number	L	H	Applicable Extrusion (Series)	Ref. Tightening Torque (N·m)	Unit Price 1~29 pc(s).	Volume Discount Rate 30~149	Volume Discount Rate 150~600
HNTLSN6-6	13	11.8	6 Series	11.7			
	17	16.8					
	22	21.8					


Ordering Example: Part Number - L
HNTLSN6-6 - 17

Flanged Nut




RoHS10

HTDN



Material: SUS304

Effective Length of Post-Assembly Insertion Screws M6



Part Number Type	M	B	T	D	Unit Price 1~499 pc(s).	Volume Discount Rate 500~999	Volume Discount Rate 1000~1500
HTDN (Stainless Steel)	4	7	4.2	10			
	5	8	5.5	12			
	6	10	6.0	13			

Ordering Example: Part Number
HTDN6