



Flanged Spade Tongue															Manual Hand Tools		Dies for Powered Tools		
Wire Size		Studsize		Standard Part Number	Width (W)		Length (L)		Style	Wire Barrel Min. Inside Dia		Also available in ⁵		Re-marks	Certi-Crimp Hand Tool (Premium)	Pro-Crimper (SDE) Hand Tool (Commercial)	SDE Die Set (Commercial) (see Note 1)	U-Style Dies (see Note 2 on page 11)	
AWG	mm ²	U.S.	mm		inch	mm	inch	mm		inch	mm	Tape & Reel	Small Pack					Nest	Indenter
22-16	0,26 - 1,65	2	M2	324605	.182	4.62	.504	12.80	-	.061	1.55	-	✓	49935	58546-1	58545-1			
		6	M3.5	323136	.250	6.35	.514	13.06	-	.061	1.55	✓	-	49935	58546-1	58545-1			
		8	M4	52730	.296	7.52	.514	13.06	-	.061	1.55	✓	-	49935	58546-1	58545-1			
16-14	1,04 - 2,62	6	M3.5	320855	.294	7.47	.514	13.06	-	.085	2.16	✓	✓	49935	58546-1	58545-1			
		8	M4	320856	.294	7.47	.514	13.06	-	.085	2.16	✓	✓	49935	58546-1	58545-1			
		10		320857	.294	7.47	.514	13.06	-	.085	2.16	✓	✓	49935	58546-1	58545-1			
12-10	2,62 - 6,64	8	M4	323143	.416	10.57	.694	17.63	-	.129	3.28	-	-	49935	58546-1	58545-1			
		10		323144	.416	10.57	.694	17.63		.129	3.28	✓	-						



Standard Butt Splices															Manual Hand Tools		Dies for Powered Tools		
Wire Size		Studsize		Standard Part Number	Width (W)		Length (L)		Style	Wire Barrel Min. Inside Dia		Also available in ⁵		Re-marks	Certi-Crimp Hand Tool (Premium)	Pro-Crimper (SDE) Hand Tool (Commercial)	SDE Die Set (Commercial) (see Note 1)	U-Style Dies (see Note 2 on page 11)	
AWG	mm ²	U.S.	mm		inch	mm	inch	mm		inch	mm	Tape & Reel	Small Pack					Nest	Indenter
22-16	0,26 - 1,65	n.a.	n.a.	31818	.136	3.45	.578	14.68	A	.065	1.65	✓	✓	2	49935	58546-1	58545-1		
16-14	1,04 - 2,62	n.a.	n.a.	31819	.160	4.06	.567	14.40	A	.089	2.26	✓	✓	2	49935	58546-1	58545-1		
12-10	2,62 - 6,64	n.a.	n.a.	32151	.221	5.61	.565	14.35	A	.134	3.40	-	✓	2	49935	58546-1	58545-1		
8	6.64 - 10.5	n.a.	n.a.	34321	.296	7.52	.827	21.01	A	.172	4.37	-	✓	2				1490413-1	1490414-1
6	10.5 - 16.8	n.a.	n.a.	34322	.369	9.37	1.015	25.78	A	.232	5.89	-	✓	2				1490413-2	1490414-2
4	16.8 - 26.7	n.a.	n.a.	34323	.463	11.76	1.140	28.96	A	.296	7.52	-	✓	2				1490413-3	1490414-2
2	26.7 - 42.4	n.a.	n.a.	35189	.539	13.69	1.265	32.13	A	.370	9.40	-	✓	2				1490413-4	1490414-2



Sighthole Butt Splices															Manual Hand Tools		Dies for Powered Tools		
Wire Size		Studsize		Standard Part Number	Width (W)		Length (L)		Style	Wire Barrel Min. Inside Dia		Also available in ⁵		Re-marks	Certi-Crimp Hand Tool (Premium)	Pro-Crimper (SDE) Hand Tool (Commercial)	SDE Die Set (Commercial) (see Note 1)	U-Style Dies (see Note 2 on page 11)	
AWG	mm ²	U.S.	mm		inch	mm	inch	mm		inch	mm	Tape & Reel	Small Pack					Nest	Indenter
22-16	0,26 - 1,65	n.a.	n.a.	330367	.141	3.58	.578	14.68	B	.061	1.55	✓	✓	2	49935	58546-1	58545-1		
16-14	1,04 - 2,62	n.a.	n.a.	330368	.165	4.19	.567	14.40	B	.085	2.16	-	-	2	49935	58546-1	58545-1		
14-12	1.65 - 4.17	n.a.	n.a.	321280	.178	4.52	.690	17.53	B	.098	2.49	✓	-	2	49592				
12-10	2,62 - 6,64	n.a.	n.a.	330369	.226	5.74	.567	14.40	B	.129	3.28	-	✓	2	49935	58546-1	58545-1		
8	6.64 - 10.5	n.a.	n.a.	36906	.296	7.52	.827	21.01	B	.172	4.37	-	✓	2				1490413-1	1490414-1
6	10.5 - 16.8	n.a.	n.a.	36886	.369	9.37	1.015	25.78	B	.232	5.89	-	✓	2				1490413-2	1490414-2
4	16.8 - 26.7	n.a.	n.a.	320238	.463	11.76	1.140	28.96	B	.296	7.52	-	-	2				1490413-3	1490414-2
2	26.7 - 42.4	n.a.	n.a.	322246	.539	13.69	1.265	32.13	B	.370	9.40	-	-	2				1490413-4	1490414-2