

スパーギヤ(ボス付) **SNB**

キャスト
ナイロン



製品仕様

材質	キャストナイロンNB
歯形	並歯
圧力角	20°
表面処理	無し
歯面仕上	切削
穴径公差	—

MP=1.0

製品記号	モジュール	歯数 Z	ピッチ円直径	歯先円直径	歯幅 W	穴径	ボス径	ボス長	全長 L
	m		P.C.D.	D		d	B	BL	
SNB1016	1	16	16	18	12	8	18	13	25
SNB1017	1	17	17	19	12	8	19	13	25
SNB1018	1	18	18	20	10	8	15	10	20
SNB1019	1	19	19	21	10	8	16	10	20
SNB1020	1	20	20	22	10	8	16	10	20
SNB1021	1	21	21	23	10	8	18	10	20
SNB1022	1	22	22	24	10	8	18	10	20
SNB1023	1	23	23	25	10	8	20	10	20
SNB1024	1	24	24	26	10	8	20	10	20
SNB1025	1	25	25	27	10	8	20	10	20
SNB1026	1	26	26	28	10	8	22	10	20
SNB1027	1	27	27	29	10	8	22	10	20
SNB1028	1	28	28	30	10	10	24	10	20
SNB1029	1	29	29	31	10	10	24	10	20
SNB1030	1	30	30	32	10	10	25	10	20
SNB1032	1	32	32	34	10	10	25	10	20
SNB1034	1	34	34	36	10	10	26	10	20
SNB1035	1	35	35	37	10	10	26	10	20
SNB1036	1	36	36	38	10	10	28	10	20
SNB1038	1	38	38	40	10	10	28	10	20
SNB1040	1	40	40	42	10	10	30	10	20
SNB1042	1	42	42	44	10	10	30	10	20
SNB1044	1	44	44	46	10	10	30	10	20
SNB1045	1	45	45	47	10	10	30	10	20
SNB1046	1	46	46	48	10	10	30	10	20
SNB1048	1	48	48	50	10	10	30	10	20
SNB1050	1	50	50	52	10	10	35	10	20
SNB1052	1	52	52	54	10	10	35	10	20
SNB1054	1	54	54	56	10	10	35	10	20
SNB1055	1	55	55	57	10	10	35	10	20
SNB1058	1	58	58	60	10	10	35	10	20
SNB1060	1	60	60	62	10	10	35	10	20