


ハイス

DCB

切削条件表

P268

六角穴付ボルト用ドリル付沈めフライス Counterbore With Drill



公差 (Tolerance)	D1: h8	D: $\begin{smallmatrix} +0.1 \\ 0 \end{smallmatrix}$	d: h8
----------------	--------	--	-------

右刃右ネジレ25°(D1) 刃数:2 SKH51
Helix Angle-Right25°(D1) Number of Flute:2 HSS

呼び寸法 Size	ドリル径 ($\phi D1$) Drill Dia.	ドリル長 ($\ell 1$) Length of Drill	刃径 (ϕD) Dia.	刃長 (ℓ) Length of Flutes	全長 (L) Overall Length	シャンク径 (ϕd) Shank Dia.
M 3	3.5	10	5.9	7	48	6
M 4	4.5	15	7.4	9	55	6
M 5	5.5	20	8.9	12	64	6
M 6	6.5	25	10.4	13	70	8
M 8	8.5	30	13.4	16	78	10
M10	10.6	35	16.8	20	87	12
M12	12.7	35	18.8	23	90	12

呼び寸法 Size	ドリル径 ($\phi D1$) Drill Dia.	ドリル長 ($\ell 1$) Length of Drill	刃径 (ϕD) Dia.	刃長 (ℓ) Length of Flutes	全長 (L) Overall Length	シャンク径 (ϕd) Shank Dia.
M14	16	35	23	35	110	12
M16	18	40	26	40	120	12
M18	20	45	29	45	130	12
1/4	6.85	25	11	13	69	8
5/16	8.55	30	14	17	81	10
3/8	10.1	35	15	18	87	12
1/2	13.5	35	20	23	92	12

※テーパシャンク (Taper Shank)

呼び寸法 Size	ドリル径 ($\phi D1$) Drill Dia.	ドリル長 ($\ell 1$) Length of Drill	刃径 (ϕD) Dia.	刃長 (ℓ) Length of Flutes	全長 (L) Overall Length	MT No. Shank MTNo.
M16	18	40	26	40	179	3

呼び寸法 Size	ドリル径 ($\phi D1$) Drill Dia.	ドリル長 ($\ell 1$) Length of Drill	刃径 (ϕD) Dia.	刃長 (ℓ) Length of Flutes	全長 (L) Overall Length	MT No. Shank MTNo.
M18	20	45	29	45	189	3