

# AXEL

Testo K. K.

1-6434-01 Digital Vibrometer OH-580A



Order No.	1-6434-01
Model No.	OH-580A
JAN Code	0000000000000
	<b>JPY:</b> <b>158,000</b>
	<b>USD:</b> <b>1,055.87</b>
Standard price	
	Exchange rate 1USD= 149.64JPY Valid price in Japan
Quantity	1unit

Calibration Available

## Features

- 3 mode measuring of acceleration, speed, and displacement are possible.
- Max. holdfunction provided.

## Spec

- Model number: OH-580A
- Main unit size (mm): 72 x 24 x 220
- Body weight (g): 200 (including dry cell)
- Detection method: Effective value detection
- Measurement accuracy: Within FS±5%
- Display cycle: 3 times/second
- Power supply: AA dry cell x 2 pieces (attached), AC100V (optional)
- 
- Acceleration rate (ACC1): 10 - 6000Hz, Hi: 1.0 - 199.9m/sec<sup>2</sup>, Lo: 0.1 - 19.99m/sec<sup>2</sup>
- Acceleration rate (ACC2): 10 - 300Hz, Hi: 1.0 - 199.9m/sec<sup>2</sup>, Lo: 0.1 - 19.99m/sec<sup>2</sup>
- Velocity (VEL): 10 - 1000Hz, Hi: 1.0 - 199.9mm/sec, Lo: 0.1 - 19.99mm/sec
- Displacement (DIS): 10 - 1000Hz, Hi: 10 - 1999μm, Lo: 1 - 199.9μm
- ■Accessories: Pickup, Pickup cable, Magnet holder, Attachment, Hand strap, Microdriver, Storage case

▶ Package size : 360×290×100 mm 1.3 kg

## Product Catalog

Catalog Name	Page
AS ONE Catalog 2021 [Instruments for Laboratory]	815
AS ONE Catalog 2019 [Instruments for Laboratory]	792
AS ONE Catalog 2017 [Instruments for Laboratory]	623
AS ONE Catalog 2015 [Instruments for Laboratory]	590