

High-performance clamps



- Clamping force up to 8,500 N at tightening torque of 25 Nm
- 20 % more clamping force per spindle rotation with optimised rail profile
- Maximum safety due to the better linear transfer of force of the sliding arm
- Long life due to heat-resistant pressure plate with sintered steel insert, which can be tilted up to 35°



Fitters' clamp SLM



| № | <a> | | <x> | ⚖️ | 📦 | V2 |
|-------|-----|-----|---------|------|------|----|
| | mm | mm | mm | kg | qty. | |
| SL20M | 200 | 120 | 28 x 11 | 1.81 | 5 | |
| SL25M | 250 | 120 | 28 x 11 | 1.91 | 5 | |
| SL30M | 300 | 120 | 28 x 11 | 2.00 | 5 | |
| SL40M | 400 | 120 | 28 x 11 | 2.20 | 5 | |
| SL50M | 500 | 120 | 28 x 11 | 2.41 | 5 | |
| SL60M | 600 | 120 | 28 x 11 | 2.61 | 5 | |

[YouTube ▶](#)



- Clamping force up to 12,000 N at tightening torque of 40 Nm
- 20 % more clamping force per spindle rotation with optimised rail profile
- Maximum safety due to the better linear transfer of force of the sliding arm
- Long life due to heat-resistant pressure plate with sintered steel insert, which can be tilted up to 35°



High-performance clamp SGM



| № | <a> | | <x> | ⚖️ | 📦 | V2 |
|--------|------|-----|---------|------|------|----|
| | mm | mm | mm | kg | qty. | |
| SG25M | 250 | 140 | 34 x 13 | 2.58 | 5 | |
| SG30M | 300 | 140 | 34 x 13 | 3.03 | 5 | |
| SG40M | 400 | 140 | 34 x 13 | 3.17 | 5 | |
| SG50M | 500 | 140 | 34 x 13 | 3.40 | 5 | |
| SG60M | 600 | 140 | 34 x 13 | 3.80 | 5 | |
| SG80M | 800 | 140 | 34 x 13 | 4.45 | 5 | |
| SG100M | 1000 | 140 | 34 x 13 | 4.95 | 5 | |
| SG125M | 1250 | 140 | 34 x 13 | 5.87 | 1 | |
| SG150M | 1500 | 140 | 34 x 13 | 6.63 | 1 | |

[YouTube ▶](#)