



# CAP

## CAP

キャップ



### (METRIC)

(Unit:mm)

TUBE O.D. T	PART. No.	A	C	D	F	G	H
2	CAP- 2	17.5	11.9	9.5	8	8	13
3	CAP- 3	22	16	15	12	12	15
4	CAP- 4	25.3	18.3	15.3	14	14	18
6	CAP- 6	25.4	18.4	15.4	14	14	18
8	CAP- 8	25.8	18.8	16.8	14	15.87	18
10	CAP-10	27.7	21.7	18.7	17	19	19
12	CAP-12	29.8	22.8	22.8	22	23	19
14	CAP-14	30.5	24.5	24.5	23	26	20
15	CAP-15	30	24.5	24	23	26	20
16	CAP-16	30.5	24.5	24.5	23	26	20
18	CAP-18	34	25.5	25	27	30	23
20	CAP-20	34	25.5	25	30	32	23
22	CAP-22	35.2	26.7	25.2	30	35	24
25	CAP-25	40.5	28	33.5	35	38	26

### (INCHES)

※管外径5φも製作しております。

1/16" : 1.6	CAP-005	17	11.4	9	8	8	13
1/8" : 3.18	CAP- 01	15	16	15	12	12	15
1/4" : 6.35	CAP- 02	25.4	18.4	15.4	14	14	18
5/16" : 7.94	CAP-025	25.8	18.8	16.8	14	15.87	18
3/8" : 9.53	CAP- 03	27.3	20.8	17.8	17	17.46	19
1/2" : 12.7	CAP- 04	29.8	22.8	22.8	22	23	19
5/8" : 15.87	CAP- 05	30	24.5	24	23	26	20
3/4" : 19.05	CAP- 06	34	25.5	25	27	30	23
7/8" : 22.23	CAP- 07	35.2	26.7	25.2	30	35	24
1" : 25.4	CAP- 08	40	28	33	35	38	26

### (SCHEDULE)

※管外径3/16"も製作しております。


1/8" B : 10.5	CAP-10.5	28.2	21.2	19.2	17	19	19
1/4" B : 13.8	CAP-13.8	30	24.5	24	23	26	20
3/8" B : 17.3	CAP-17.3	34	25.5	25	27	30	23
1/2" B : 21.7	CAP-21.7	35.2	26.7	25.2	30	35	24

A.C.D.:FINGER TIGHT-±0.5mm (about)

# PG

## PLUG

プラグ



### (METRIC)

(Unit:mm)

TUBE O.D. T	PART. No.	G	L
2	PG- 2	8	8
3	PG- 3	12	12
4	PG- 4	14	14
5	PG- 5	14	14
6	PG- 6	14	14
8	PG- 8	15.87	14.5
10	PG-10	19	16
12	PG-12	23	17.5
14	PG-14	26	17.5
15	PG-15	26	17.5
16	PG-16	26	17.5
18	PG-18	30	19
20	PG-20	32	19
22	PG-22	35	19
25	PG-25	38	22

### (INCHES)

(Unit:mm)

TUBE O.D. T	PART. No.	G	L
1/16" : 1.6	PG- 005	8	8
1/8" : 3.18	PG- 01	12	12
1/4" : 6.35	PG- 02	14	14
3/16" : 4.76	PG- 015	14	14
5/16" : 7.94	PG- 025	15.87	14.5
3/8" : 9.53	PG- 03	17.46	15.5
1/2" : 12.7	PG- 04	23	17.5
5/8" : 15.87	PG- 05	26	17.5
3/4" : 19.05	PG- 06	30	19
7/8" : 22.23	PG- 07	35	19
1" : 25.4	PG- 08	38	22

### (SCHEDULE)

1/8" B : 10.5	PG-10.5	19	16
1/4" B : 13.8	PG-13.8	26	17.5
3/8" B : 17.3	PG-17.3	30	19
1/2" B : 21.7	PG-21.7	35	19