


ネガティブ 80°トリゴンチップ 仕上用


WNMG 08 04 08-

切刃長さ 厚み コーナーR プレーカ
*詳細はA24~A26頁をご参照下さい。


WNMG 06T302-NF





WNMG 06T304-SF



WNMG 080408-VL



WNMG 080408-WG



WNMG ■ WNMZ ■ WNGP <仕上加工用>

販売単位：10個

型番	在庫															コーナ r (mm)	チップ形状					
	CVDコーティング					PVDコーティング					PVDサーメット		サーメット	超硬								
	IC5005	IC5010	IC6015	IC6025	IC8150	IC8250	IC8350	IC9150	IC9250	IC570	IC806	IC807	IC907	IC908	IC520N			IC530N	IC20N	IC30N	IC20	
WNMG 06T302-SF										○						○					0.2	
WNMG 06T304-SF																●					0.4	
WNMZ 06T304-RF										○						○				○	0.4	
WNMZ 080404-RF										○						○				○	0.4	
WNMZ 06T304-LF										○						○					0.4	
WNMZ 080404-LF										○						○				○	0.4	
WNMG 06T301-NF														○							0.1	
WNMG 06T302-NF					●	●	○					○	○			○	●	○			0.2	
WNMG 06T304-NF					●	●	○	○	●			○	●		○	●	●	○	○		0.4	
WNMG 06T308-NF					●	●	○		●								●				0.8	
WNMG 06T312-NF							○														1.2	
WNMG 060402-NF																					0.2	
WNMG 060404-NF							●														0.4	
WNMG 060408-NF						○			○												0.8	
WNMG 080404-NF								●	●							●	○				0.4	
WNMG 080408-NF								●	●		●	●				●	○				0.8	
WNMG 080412-NF								●													1.2	
WNMG 060402-WF																					0.2	
WNMG 060404-WF																					0.4	
WNMG 060408-WF																					0.8	
WNMG 080408-WF								●			●					○					0.8	
WNMG 06T304-WG							○	○		○	●				○	●	○				0.4	
WNMG 06T308-WG							○	○		○	○				○						0.8	
WNMG 060404-WG							○	○		○	○				○						0.4	
WNMG 060408-WG							▲	●		○											0.8	
WNMG 080408-WG	○						●	●		●	●				○	○	○				0.8	
WNMG 080412-WG	●						●	●		○					○						1.2	
WNMG 06T308-VL														○							0.8	
WNMG 080404-VL											▲										0.4	
WNMG 080408-VL											▲				●						0.8	
WNMG 080412-VL														○							1.2	
WNMG 060404-F3P ^{FLASH}							●	●							▲		▲				0.4	
WNMG 060408-F3P ^{FLASH}							●	●							▲		▲				0.8	
WNMG 060412-F3P ^{FLASH}							●	●							▲		▲				1.2	
WNMG 080404-F3P							●	●							▲		▲				0.4	
WNMG 080408-F3P							●	●							▲		▲				0.8	
WNMG 080412-F3P							●	●							▲		▲				1.2	
WNMG 060404-F3M							▲	▲													0.4	
WNMG 060408-F3M							▲	▲													0.8	
WNMG 060412-F3M							▲	▲													1.2	
WNMG 080404-F3M							▲	▲													0.4	
WNMG 080408-F3M							▲	▲													0.8	
WNMG 080412-F3M							▲	▲													1.2	
WNGP 040302R/L-F2P																▲					0.2	
WNGP 040304R/L-F2P																▲					0.4	
WNGP 040308R/L-F2P																▲					0.8	
WNGP 040302R/L-F2M														▲							0.2	
WNGP 040304R/L-F2M														▲							0.4	
WNGP 040308R/L-F2M														▲							0.8	

-WG仕上刃付チップについてはA28頁をご参照下さい。

* ^{FLASH} : フラッシュターン、経済性に優れた厚みある小型形状チップ

適合ホルダーはA52、A55、A59、A60、A65、A66、A67、A70、F8、F11頁をご参照下さい。