


エア抜きバルブ

AP




継手の呼び	(PT) T	D	d	六角対辺		L	鋼球
				H ₁	H		
AP - 1/8	1/8	4	3	13	14	51	7/32
AP - 1/4	1/4	4	3	13	14	53	7/32
AP - 3/8	3/8	6	4	13	19	54	7/32
AP - 1/2	1/2	6	4	19	27	69	5/16

※Average Values

※上記諸元は品質の向上により若干変わることがあります。

ホース接続ハーフユニオン(オス)

HJ-K




※Average Values

継手の呼び	適用管 外径A	(PF) T	E	六角対辺		I	ℓ	手締め L(約)
				H ₁	H			
HJ-K - 8×1/4	8	1/4	6	17	17	7	35	45.5
HJ-K - 8×3/8	8	3/8	6	19	17	7	37	47.5
HJ-K - 10×1/4	10	1/4	6	17	19	7	35	46.5
HJ-K - 10×3/8	10	3/8	8	19	19	7	37	48.5
HJ-K - 10×1/2	10	1/2	8	22	19	7	40	51.5
HJ-K - 12×1/4	12	1/4	6	19	22	7	35	46.5
HJ-K - 12×3/8	12	3/8	9	19	22	7	37	48.5
HJ-K - 12×1/2	12	1/2	10	22	22	7	40	51.5
HJ-K - 15×3/8	15	3/8	9	24	27	7.5	40	52.5
HJ-K - 15×1/2	15	1/2	12	24	27	7.5	42	54.5
HJ-K - 16×3/8	16	3/8	9	27	30	7.5	40	52.5
HJ-K - 16×1/2	16	1/2	12	27	30	7.5	42	54.5
HJ-K - 18×1/2	18	1/2	12	27	32	8	42	54.5
HJ-K - 20×3/4	20	3/4	16	30	36	8	46	58.5
HJ-K - 22×1/2	22	1/2	12	32	36	9	44	56.5
HJ-K - 22×3/4	22	3/4	16	32	36	9	46	58.5
HJ-K - 25×3/4	25	3/4	16	36	41	10	47	60.5
HJ-K - 25×1	25	1	20	36	41	10	49	62.5
HJ-K - 28×3/4	28	3/4	16	41	46	10	49	63
HJ-K - 28×1	28	1	22	41	46	10	51	65
HJ-K - 30×3/4	30	3/4	16	41	46	10	49	63.5
HJ-K - 30×1	30	1	22	41	46	10	51	65.5
HJ-K - 32×1	32	1	22	46	50	11	52	66.5
HJ-K - 32×1 1/4	32	1 1/4	28	46	50	11	56	70.5

※上記諸元は品質の向上により若干変わることがあります。

ホース接続ハーフユニオン(メス)

HJ-K₂



※Average Values

継手の呼び	適用管 外径A	(PF) T	E	六角対辺		I	ℓ	手締め L(約)
				H ₁	H			
HJ-K ₂ - 8×1/4	8	1/4	6	17	17	7	33	43.5
HJ-K ₂ - 8×3/8	8	3/8	6	19	17	7	34	44.5
HJ-K ₂ - 10×1/4	10	1/4	6	17	19	7	33	44.5
HJ-K ₂ - 10×3/8	10	3/8	8	19	19	7	34	45.5
HJ-K ₂ - 10×1/2	10	1/2	8	22	19	7	38	49.5
HJ-K ₂ - 12×1/4	12	1/4	6	19	22	7	33	44.5
HJ-K ₂ - 12×3/8	12	3/8	9	19	22	7	34	45.5
HJ-K ₂ - 12×1/2	12	1/2	10	22	22	7	38	49.5
HJ-K ₂ - 15×3/8	15	3/8	9	24	27	7.5	37	49.5
HJ-K ₂ - 15×1/2	15	1/2	12	24	27	7.5	40	52.5
HJ-K ₂ - 16×3/8	16	3/8	9	27	30	7.5	37	49.5
HJ-K ₂ - 16×1/2	16	1/2	12	27	30	7.5	40	52.5
HJ-K ₂ - 18×1/2	18	1/2	12	27	32	8	40	52.5
HJ-K ₂ - 20×3/4	20	3/4	16	30	36	8	43	55.5
HJ-K ₂ - 22×1/2	22	1/2	12	32	36	9	42	54.5
HJ-K ₂ - 22×3/4	22	3/4	16	32	36	9	43	55.5
HJ-K ₂ - 25×3/4	25	3/4	16	36	41	10	44	57.5
HJ-K ₂ - 25×1	25	1	20	36	41	10	46	59.5
HJ-K ₂ - 28×3/4	28	3/4	16	41	46	10	46	60
HJ-K ₂ - 28×1	28	1	22	41	46	10	48	62
HJ-K ₂ - 30×3/4	30	3/4	16	41	46	10	46	60.5
HJ-K ₂ - 30×1	30	1	22	41	46	10	48	62.5
HJ-K ₂ - 32×1	32	1	22	46	50	11	49	63.5
HJ-K ₂ - 32×1 1/4	32	1 1/4	28	46	50	11	55	69.5
HJ-K ₂ - 38×1 1/2	38	1 1/2	32	50	60	12	57	76.5
HJ-K ₂ - 40×1 1/2	40	1 1/2	32	55	60	12	62	81.5
HJ-K ₂ - 50×2	50	2	40	65	75	12	70	91.5

※上記諸元は品質の向上により若干変わることがあります。