

ラジアスゲージ 178

RADIUS GAUGES 178 TYPE

ラジアスゲージ178型は、パイプの外径等の円溝型のR部測定が迅速に出来ます。
Used for checking convex and concave radii of tool patterns and other machining jobs.
Each leaves stamped with size. High precision is guaranteed.

ケースの両端に凸型と凹型のリーフが
サイズ順に収納されています。



178MA

材質 : Material
鋼板(SPCC)
Steel

178-112・178-213
ステンレス製(Stainless Steel)

精度 : Accuracy
0.1R~3.0R (±0.03mm)
3.25R~23.0R (±0.04mm)
24.0R~30.0R (±0.05mm)
31.0R~50.0R (±0.08mm)

コードNo. Code No.	型式 Model No.	枚数 Leaves	内容 (R寸法) Size Composition/Contents										mm mm
01-308	178MAA	20	0.1	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0	
01-316	178-112	20	1.1	1.2	1.3	1.4	1.5	1.6	1.7	1.8	1.9	2.0	
01-317	178-213	20	2.1	2.2	2.3	2.4	2.5	2.6	2.7	2.8	2.9	3.0	
01-309	178MA	34	1.0	1.25	1.5	1.75	2.0	2.25	2.5	2.75	3.0		
			3.5	4.0	4.5	5.0	5.5	6.0	6.5	7.0			
01-310	178MB	32	7.5	8.0	8.5	9.0	9.5	10.0	10.5	11.0			
			11.5	12.0	12.5	13.0	13.5	14.0	14.5	15.0			
01-315	178MR	30	15.5	16.0	16.5	17.0	17.5	18.0	18.5				
			19.0	19.5	20.0	21.0	22.0	23.0	24.0	25.0			
01-311	178MC	16	16.0	17.0	18.0	19.0	20.0	21.0	22.0	23.0			
01-312	178MD	14	24.0	25.0	26.0	27.0	28.0	29.0	30.0				
01-313	178ME	20	31.0	32.0	33.0	34.0	35.0	36.0	37.0	38.0	39.0	40.0	
01-314	178MF	20	41.0	42.0	43.0	44.0	45.0	46.0	47.0	48.0	49.0	50.0	
Code No.	Model No.	Leaves	Size Composition/Contents										inch
01-301	178A	30	1/32" to 1/4" by 64ths										
01-302	178B	32	17/64" to 1/2" by 64ths										

ラジアスゲージ 272

RADIUS GAUGES 272 TYPE

ラジアスゲージ272型は、机のコーナー等の角溝型のR部測定が迅速に出来ます。
Used for checking internal and external radius on each leaf or convex and concave surfaces.
Toolmakers and Inspectors can measure the radii of the edges and corners of works.
Each leaves stamped with size. High precision is guaranteed.

1枚のリーフに内検査用と外検査用のRがついており
ケースの両端にサイズ順に収納されています。



272MA

材質 : Material
鋼板(SPCC)
Steel

272-112・272-213
ステンレス製(Stainless Steel)

精度 : Accuracy
0.1R~3.0R (±0.03mm)
3.25R~23.0R (±0.04mm)
24.0R~30.0R (±0.05mm)
31.0R~50.0R (±0.08mm)

コードNo. Code No.	型式 Model No.	枚数 Leaves	内容 (R寸法) Size Composition/Contents										mm mm
01-408	272MAA	10	0.1	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0	
01-415	272-112	10	1.1	1.2	1.3	1.4	1.5	1.6	1.7	1.8	1.9	2.0	
01-416	272-213	10	2.1	2.2	2.3	2.4	2.5	2.6	2.7	2.8	2.9	3.0	
01-409	272MA	18	0.75	1.0	1.25	1.5	1.75	2.0	2.25	2.5	2.75		
			3.0	3.25	3.5	3.75	4.0	4.25	4.5	4.75	5.0		
01-410	272MB	16	5.5	6.0	6.5	7.0	7.5	8.0	8.5	9.0			
			9.5	10.0	10.5	11.0	11.5	12.0	12.5	13.0			
01-411	272MC	10	13.0	14.0	15.0	16.0	17.0	18.0	19.0	20.0	21.0	22.0	
01-412	272MD	8	23.0	24.0	25.0	26.0	27.0	28.0	29.0	30.0			
01-413	272ME	10	31.0	32.0	33.0	34.0	35.0	36.0	37.0	38.0	39.0	40.0	
01-414	272MF	10	41.0	42.0	43.0	44.0	45.0	46.0	47.0	48.0	49.0	50.0	
Code No.	Model No.	Leaves	Size Composition/Contents										inch
01-401	272A	16	1/32" to 17/64" by 64ths										
01-402	272B	16	9/32" to 1/2" by 64ths										