


Flange Type U-NUT

Features

- No washer is needed so it can improve work efficiency.
- Can reduce the number of parts.
- Can achieve stable locking performance.
- The appearance can be improved by the FUJIOK U-NUT with integrated washer.



●: Available

Thread Accuracy: ISO6H (JIS6H) Unit: mm

Material of the Nut Body														SS400	S45C-H	Unit Weight (g) Approx.
Material of the Friction Ring														SUS301		
Nominal Diameter (d)	Pitch (p)	Width Across Flat (s)		Flange Diameter (ødc)		Overall Height (h)		Thread Height (m) Approx.	Across Corners (e) Approx.	Depth of Counter Bores (b)	Diameter of Counter Bores (ødb)		Flange Thickness (c) MIN	Property Class		
		Base	Tolerance	Base	Tolerance	Base	Tolerance				Base	Tolerance		6T	8T	
M 4	0.7	7	0 -0.2	10	0 -0.4	5.0	±0.3	4.2	8.1	-	-	-	0.6	●	1.3	
M 5	0.8	8		11		6.0		5.3	9.2				1.0	●	2.0	
M 6	1	10		13		6.9		6.0	11.5				1.2	●	3.5	
M 8	1.25	12	0 -0.25	17	±0.4	8.5	7.5	13.9	-	-	-	1.5	●	●	6.8	
		14		19									10.0	8.8	16.2	●
M10	1.25	14	0 -0.25	19	±0.4	10.0	8.8	19.6	-	-	-	1.7	●	●	9.2	
		17		20									11.2	11.0	21.9	2
M12	1.25	17	0 -0.5	24	±0.5	12.5	11.0	25.4	3	15	±0.3	1.4	●	●	17.4	
		19		26									13.5	11.0	21.9	2
M14	1.5	19	0 -0.35	26	±0.5	15.0	±0.5	13.5	25.4	3	17	±0.3	1.6	●	22.6	
		22		30		15.0		14.5					27.7	3	17	3.0
M16	1.5	22	0 -0.35	30	±0.5	16.5	±0.5	15.0	27.7	3	20	±0.3	3.0	●	35.7	
		24		32		16.0		16.5					27.7	3	20	3.0
M18	1.5	24		32		18.0		16.5					3.0	●	41.7	

* Please check the stock condition of each size. * The material also includes items with equivalent materials. * Dimensions may change for improvement.

Introduction of Applications



Engine Mounts



Rear Axles



Trimmers



Sprockets



Electric Wheelchairs



Muffler Brackets