



スモウカム(ヘッド交換式ドリルボディ)

DCN-3D

加工径 6.0mm~32.9mm



本図はAタイプ(回り止め付)を示す。



加工深さ : 3×D

型番	在庫*		寸法(mm)							付属品		適合ヘッド
	A	R	φD加工径	φPd	L	L ₁ ±0.2	L ₂	φd	φd ₁	脱着キー		
DCN 060-018-12A/R-3D	●	●	6.0-6.4	6	18	32.0	45	12	16	K DCN 6-9.99-Y	ICP/M/K,ICF	060~064
DCN 065-020-12A/R-3D	●	●	6.5-6.9	6	20	33.8	45	12	16	K DCN 6-9.99-Y	ICP/M/K	065~069
DCN 070-021-12A/R-3D	●	●	7.0-7.4	7	21	35.6	45	12	16	K DCN 6-9.99	ICP/M/K	070~074
DCN 075-023-12A/R-3D	●	●	7.5-7.9	7	23	37.1	45	12	16	K DCN 6-9.99	ICP/M/K,ICF	075~079
DCN 080-024-12A/R-3D	●	●	8.0-8.4	8	24	39.4	45	12	16	K DCN 6-9.99	ICP/M/K,FCP,HCP	080~084
DCN 085-025-12A/R-3D	●	●	8.5-8.9	8	25	40.9	45	12	16	K DCN 6-9.99	ICP/M/K,FCP,HCP	085~089
DCN 090-027-12A/R-3D	●	●	9.0-9.4	9	27	42.8	45	12	16	K DCN 6-9.99	ICP/M/K,FCP,HCP	090~094
DCN 095-029-12A/R-3D	●	●	9.5-9.9	9	29	44.3	45	12	16	K DCN 6-9.99	ICP/M/K,FCP,ICF,HCP	095~099
DCN 100-030-16A/R-3D	●	●	10.0-10.4	10	30	46.2	48	16	20	K DCN 10-13.99	ICP/M/K,FCP,HCP	100~104
DCN 105-032-16A/R-3D	●	●	10.5-10.9	10	32	47.7	48	16	20	K DCN 10-13.99	ICP/M/K,FCP,HCP	105~109
DCN 110-033-16A/R-3D	●	●	11.0-11.4	11	33	49.6	48	16	20	K DCN 10-13.99	ICP/M/K,FCP,ICF,HCP	110~114
DCN 115-035-16A/R-3D	●	●	11.5-11.9	11	35	51.1	48	16	20	K DCN 10-13.99	ICP/M/K,FCP,HCP	115~119
DCN 120-036-16A/R-3D	●	●	12.0-12.4	12	36	53.0	48	16	20	K DCN 10-13.99	ICP/M/K,FCP,HCP	120~124
DCN 125-037-16A/R-3D	●	●	12.5-12.9	12	37	54.5	48	16	20	K DCN 10-13.99	ICP/M/K,FCP,ICF,HCP	125~129
DCN 130-039-16A/R-3D	●	●	13.0-13.4	13	39	56.6	48	16	20	K DCN 10-13.99	ICP/M/K,FCP,HCP	130~134
DCN 135-041-16A/R-3D	●	●	13.5-13.9	13	41	58.1	48	16	20	K DCN 10-13.99	ICP/M/K,FCP,HCP	135~139
DCN 140-042-16A/R-3D	●	●	14.0-14.4	14	42	62.1	48	16	20	K DCN 14-17.99	ICP/M/K,FCP,HCP	140~144
DCN 145-044-16A/R-3D	●	●	14.5-14.9	14	44	63.6	48	16	20	K DCN 14-17.99	ICP/M/K,FCP,HCP	145~149
DCN 150-045-20A/R-3D	●	●	15.0-15.9	15	45	68.7	50	20	25	K DCN 14-17.99	ICP/M/K,FCP,HCP	150~159
DCN 160-048-20A/R-3D	●	●	16.0-16.9	16	48	73.3	50	20	25	K DCN 14-17.99	ICP/M/K,FCP,HCP	160~169
DCN 170-051-20A/R-3D	●	●	17.0-17.9	17	51	77.9	50	20	25	K DCN 14-17.99	ICP/M/K,FCP,HCP	170~179
DCN 180-054-25A/R-3D	●	●	18.0-18.9	18	54	82.5	56	25	32	K DCN 18-21.99	ICP/M/K,FCP,HCP	180~189
DCN 190-057-25A/R-3D	●	●	19.0-19.9	19	57	87.0	56	25	32	K DCN 18-21.99	ICP/M/K,FCP,HCP	190~199
DCN 200-060-25A/R-3D	●	●	20.0-20.9	20	60	91.6	56	25	32	K DCN 18-21.99	ICP/M/K,FCP,HCP	200~209
DCN 210-063-25A/R-3D	●	●	21.0-21.9	21	63	96.2	56	25	32	K DCN 18-21.99	ICP/M/K,FCP,HCP	210~219
DCN 220-066-25A/R-3D	●	●	22.0-22.9	22	66	100.8	56	25	32	K DCN 22-26.99	ICP/M/K,FCP,HCP	220~229
DCN 230-069-32A/R-3D	●	●	23.0-23.9	23	69	105.4	60	32	42	K DCN 22-26.99	ICP/M/K,FCP,HCP	230~239
DCN 240-072-32A/R-3D	●	●	24.0-24.9	24	72	110.0	60	32	42	K DCN 22-26.99	ICP/M/K,FCP,HCP	240~249
DCN 250-075-32A/R-3D	●	●	25.0-25.9	25	75	114.5	60	32	42	K DCN 22-26.99	ICP/M/K,FCP,HCP	250~259
DCN 260-078-32A/R-3D	▲	▲	26.0-26.9	26	78	119.0	60	32	42	K DCN 22-26.99	ICP/M/K,FCP	260~269
DCN 270-081-32A/R-3D	▲	▲	27.0-27.9	27	81	123.7	60	32	42	K DCN 27-32.99	ICP/M/K	270~279
DCN 270-081-40A-3D	●		27.0-27.9	27	81	123.7	68	40	50	K DCN 27-32.99	ICP/M/K	270~279
DCN 280-084-32A/R-3D	▲	▲	28.0-28.9	28	84	128.2	60	32	42	K DCN 27-32.99	ICP/M/K	280~289
DCN 280-084-40A-3D	●		28.0-28.9	28	84	128.2	68	40	50	K DCN 27-32.99	ICP/M/K	280~289
DCN 290-087-32A/R-3D	▲	▲	29.0-29.9	29	87	132.8	60	32	42	K DCN 27-32.99	ICP/M/K	290~299
DCN 290-087-40A-3D	●		29.0-29.9	29	87	132.8	68	40	50	K DCN 27-32.99	ICP/M/K	290~299
DCN 300-090-32A/R-3D	▲	▲	30.0-30.9	30	90	137.4	60	32	42	K DCN 27-32.99	ICP/M/K	300~309
DCN 300-090-40A-3D	●		30.0-30.9	30	90	137.4	68	40	50	K DCN 27-32.99	ICP/M/K	300~309
DCN 310-093-32A/R-3D	▲	▲	31.0-31.9	31	93	142.0	60	32	42	K DCN 27-32.99	ICP/M/K	310~319
DCN 310-093-40A-3D	●		31.0-31.9	31	93	142.0	68	40	50	K DCN 27-32.99	ICP/M/K	310~319
DCN 320-096-32A/R-3D	▲	▲	32.0-32.9	32	96	146.5	60	32	42	K DCN 27-32.99	ICP/M/K	320~329
DCN 320-096-40A-3D	●		32.0-32.9	32	96	146.5	68	40	50	K DCN 27-32.99	ICP/M/K	320~329

適合ヘッドはH8~H11頁をご参照下さい。

ドリル本体より大径のドリルヘッドをご使用下さい(加工径φDサイズのヘッドが装着出来ます)。

(1) 機械剛性等により加工穴精度の平均値が変化する可能性があります。

※DCN...A...D(回り止めフラット部付シャンク)、DCN...R...D(円筒シャンク)