

## 規格 Specifications

品番 Article number	呼称 Specification	内径(mm) Inside dia.		厚み (mm) Thickness	最大カット長(mm) Max cut length		材質 Material
		収縮前 Before shrinkage	収縮後 After shrinkage		標準 Standard	特注 Special order	
GRC-PB	20PB	21.5	19.5	0.5	1200		導電PFA Conductive PFA
	30PB	32	29	0.5	1200		
	35PB	36	33	0.5	1200		
	40PB	41	37	0.5	1200		
	45PB	51	43	0.5	1200		
	50PB	53	47	0.5	1200/1800		
	55PB	59	51	0.5	1200		
	60PB	65	56	0.5	1200/1800		
	70PB	74	62	0.5	1800		
	75PB	79	70	0.5	1800		
	80PB	84	75	0.5	1800		
	85PB	89	76	0.5	1800		
	90PB	94	83	0.5	1800		
	100PB	103	92	0.5	1800		
	100PB	106	93	0.5	3600		
	105PB	108	94	0.5	1800		
	110PB	113	100	0.5	1800		
	120PB	122	107	0.5	1800		
	123PB	127	115	0.5	3600		
	125PB	132	117	0.5	1800/3600		
135PB	141	125	0.5	1800			
145PB	150	129	0.5	1800			
150PB	156	138	0.5	1800/3600			

※お問い合わせ・ご注文時には、対象ロールの正確な直径・面長をご連絡ください。最適なチューブを選定いたします。

※上記規格以外にもご相談ください。

※本製品は静電気を発生させにくくする処理を施したものであり、静電気の発生を皆無にするものではありません。(表面抵抗 $10^9\Omega$ 以下)

※保管は必ず冷暗所(30℃以下)にて行ってください。自然収縮の恐れがあります。

※収縮後内径は200℃、10分間加熱時の測定値であり保証値ではありません。

※カット長については400mm以上で100mmピッチでカット販売いたします。1本より御用命ください。

\* Please inform us of the exact die and length of the Roll when equally or order. A suitable product will be selected accordingly.

\* Please contact for regarding requirements that exceed the specifications in the above table.

\* This product has been specially treated to suppress generation of static electricity. It is not guaranteed to totally eliminate generation of static electricity. (Surface resistance is under  $10^9\Omega$ )

\* Product specifications are subject to modification without notice.

\* The inside diameter after shrinkage is the measurement made after heating to 200℃ for 10 minutes. It is not a guaranteed value.

\* Cut length is 400 mm or above, with a pitch of 100 mm. Any quantity of tube order is welcome.