


## マルチマスター

MM...T05/T06/T08/T10/T12/T15

マルチマスター加工ヘッド(ヘッド径8-25mm)




### MM EC... 6枚刃 ねじれ角30°/45°/50°

販売単位: 2個

型番	刃列	ねじれ角	寸法(mm)							α°※	PVDコーティング	
			φD	ap	L	r	C	Ts	φd1		IC903	IC908
MM EC080A05R0.5-6T05	6	30°	8	5	10.0	0.5	—	T05	7.7	6°		●
MM EC080B05R0.5-6T05	6	45°	8	5	10.0	0.5	—	T05	7.7	3°		●
MM EC080A05R1.0-6T05	6	30°	8	5	10.0	1.0	—	T05	7.7	6°		●
MM EC080B05R1.0-6T05	6	45°	8	5	10.0	1.0	—	T05	7.7	3°		●
MM EC080A05R1.5-6T05	6	30°	8	5	10.0	1.5	—	T05	7.7	6°		●
MM EC080B05R1.5-6T05	6	45°	8	5	10.0	1.5	—	T05	7.7	3°		●
MM EC080D05C01-6T05	6	50°	8	5	10.0	—	0.1	T05	7.7	2°	●	
MM EC100B07R000-6T06	6	45°	10	7	13.0	0.0	—	T06	9.6	3°		●
MM EC100A07R0.5-6T06	6	30°	10	7	13.0	0.5	—	T06	9.6	6°		●
MM EC100B07R0.5-6T06	6	45°	10	7	13.0	0.5	—	T06	9.6	3°		●
MM EC100A07R1.0-6T06	6	30°	10	7	13.0	1.0	—	T06	9.6	6°		●
MM EC100B07R1.0-6T06	6	45°	10	7	13.0	1.0	—	T06	9.6	3°		●
MM EC100A07R1.5-6T06	6	30°	10	7	13.0	1.5	—	T06	9.6	6°		●
MM EC100B07R1.5-6T06	6	45°	10	7	13.0	1.5	—	T06	9.6	3°		●
MM EC100B12R1.5-6T06	6	45°	10	12	19.0	1.5	—	T06	9.6	3°		○
MM EC100D07C01-6T06	6	50°	10	7	13.0	—	0.1	T06	9.6	2°	●	
MM EC120B09R000-6T08	6	45°	12	9	16.5	0.0	—	T08	11.7	3°		●
MM EC120A09R0.5-6T08	6	30°	12	9	16.5	0.5	—	T08	11.7	6°		●
MM EC120B09R0.5-6T08	6	45°	12	9	16.5	0.5	—	T08	11.7	3°		○
MM EC120A09R1.0-6T08	6	30°	12	9	16.5	1.0	—	T08	11.7	6°		●
MM EC120B09R1.0-6T08	6	45°	12	9	16.5	1.0	—	T08	11.7	3°		●
MM EC120B09R1.5-6T08	6	45°	12	9	16.5	1.5	—	T08	11.7	3°		●
MM EC120D09C01-6T08	6	50°	12	9	16.5	—	0.1	T08	11.7	3°	●	

高硬度・難削材加工用



### MM EC... 8/10枚刃 ねじれ角30°/45°/50°

販売単位: 2個

型番	刃列	ねじれ角	寸法(mm)							α°※	PVDコーティング	
			φD	ap	L	r	C	Ts	φd1		IC903	IC908
MM EC160A12R0.5-8T10	8	30°	16	12	20.5	0.5	—	T10	15.3	5°		●
MM EC160A12R0.5-8T10H <sup>(1)</sup>	8	30°	16	12	20.5	0.5	—	T10	15.3	5°		○
MM EC160B12R0.5-8T10	8	45°	16	12	20.5	0.5	—	T10	15.3	5°		●
MM EC160A12R1.0-8T10	8	30°	16	12	20.5	1.0	—	T10	15.3	5°		●
MM EC160B12R1.0-8T10	8	45°	16	12	20.5	1.0	—	T10	15.3	5°		○
MM EC160A12R1.6-8T10	8	30°	16	12	20.5	1.6	—	T10	15.3	5°		●
MM EC160B12R1.6-8T10	8	45°	16	12	20.5	1.6	—	T10	15.3	5°		●
MM EC160A12R2.0-8T10	8	30°	16	12	20.5	2.0	—	T10	15.3	5°		●
MM EC160B12R2.0-8T10	8	45°	16	12	20.5	2.0	—	T10	15.3	5°		●
MM EC160D12C02-8T10	8	50°	16	12	20.5	—	0.2	T10	15.3	3°	●	
MM EC200A15R1.0-10T12	10	30°	20	15	25.5	1.0	—	T12	18.3	3°		●
MM EC200A15R2.0-10T12	10	30°	20	15	25.5	2.0	—	T12	18.3	3°		●
MM EC200D15C02-10T12	10	50°	20	15	25.5	—	0.2	T12	18.3	3°	●	
MM EC250A22R0.8-10T15	10	30°	25	22	37.0	0.8	—	T15	23.9	3°		○

高硬度・難削材加工用 (1) センタークラン穴付