



## Cable tie mounts

### MB-Series square design, self-adhesive

Where speed, simplicity and a firm fixing base are required these self adhesive clips are ideal. Particularly suitable for use in control cabinets, telecoms equipment or domestic appliances where the use of holes, screws, or nuts and bolts is impractical or undesirable.

#### Features and benefits

- Simple to instal
- Excellent security, particularly in areas of high vibration
- Maximum surface area with adhesive to achieve high pull-off force
- 4-way entry for cable tie for quicker and more flexible installation




MB-Series Mounts with square design.



For more information on the types of adhesive please see page 140.

<b>MATERIAL</b>	Polyamide 6.6 (PA66)	
<b>Adhesive</b>	Synthetic rubber with base of polyethylene foam	
<b>Operating Temperature</b>	-40 °C to +60 °C	-40 °C to +85 °C
<b>Flammability</b>	UL 94 V2 (excluding adhesive)	

RoHS



Cable Tie Mount MB2A  
(side and plan view)

MB3-MB5  
(side view)

Cable Tie Mounts MB3, MB4, MB5  
(plan view)

TYPE	Width (W)	Length (L)	Height (H)	Hole Ø (FH)	Strap Width max. (G)	Material	Colour	Adhesive	Pack Cont.	Article-No.
MB2A	13.0	13.0	4.1	-	2.7	PA66	Black (BK)	Synthetic rubber	50 pcs.	151-01800
	13.0	13.0	4.1	-	2.7	PA66	White (WH)	Synthetic rubber	100 pcs.	151-01802
MB3A	19.0	19.0	3.8	3.1	4.1	PA66	Black (BK)	Synthetic rubber	100 pcs.	151-28320
	19.0	19.0	3.8	3.1	4.1	PA66	White (WH)	Synthetic rubber	100 pcs.	151-28349
MB4A	28.0	28.0	4.7	4.0	5.4	PA66	Black (BK)	Synthetic rubber	100 pcs.	151-28412
	28.0	28.0	4.7	4.0	5.4	PA66	White (WH)	Synthetic rubber	100 pcs.	151-28469*
MB4CA	29.0	29.0	5.7	4.2	5.4	PA66	Natural (NA)	Synthetic rubber	100 pcs.	151-28459
MB4CAS	29.0	29.0	5.7	4.2	5.4	PA66	Natural (NA)	Synthetic rubber	100 pcs.	151-28449
MB5A	37.7	37.7	7.1	4.8	8.9	PA66	Black (BK)	Synthetic rubber	100 pcs.	151-28602
	37.7	37.7	7.1	4.8	8.9	PA66	White (WH)	Synthetic rubber	100 pcs.	151-28529

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available. \* Plastic box

