





ドゥーグリップ
突切加工用チップ



●チップ幅公差

チップ	W
DGN 1.0	±0.02
DGN 1.4-3.0	±0.03
DGN 3.1-6.35	±0.04

・ドゥーグリップチップ呼称：C8頁

・ブレード詳細：C6、C7頁

■ DGN (ドゥーグリップ)

販売単位：10個

型番	ブレード	寸法 (mm)				PVDコーティング								CVD			サメ状	超硬
		W	R	L	加工深さ lmax	IC308	IC328	IC354	IC508	IC807	IC808	IC830	IC908	IC1028	IC5400	IC30N		
DGN 2002C	C	2.00	0.20	19.9	19.0		●	●			●	●	●	●	▲		●	
DGN 2202C	C	2.20	0.20	19.7	19.0	●	●	●			●	●	●	●	▲	●	●	
DGN 2502C	C	2.50	0.20	20.7	18.0								●					
DGN 3102C	C	3.10	0.20	20.0	19.0	●	●	●		●	●	●	●	●	●	●	●	
DGN 4003C	C	4.00	0.30	18.9	∞	●	●	●		●	●	●	●			●	●	
DGN 5003C	C	5.00	0.30	19.0	∞		●	●			●	●	●	●		●	●	
DGN 6303C	C	6.35	0.35	19.0	∞		●	●			●	▲	●	○			●	
DGN 1002J	J	1.00	0.16	20.6	3.0		●					●	●					
DGN 1402J	J	1.40	0.16	15.8	15.0	●	●	●			●	●	●	●				
DGN 1502J	J	1.50	0.16	20.9	18.0		●					●	●					
DGN 2002J	J	2.00	0.20	19.6	18.0	●												
DGN 2202J	J	2.20	0.20	19.7	18.0	●	●	●		●	●	●	●	●	●	●	●	
DGN 3102J	J	3.10	0.20	20.0	18.0	●	●	●			●	●	●	●	●	●	●	
DGN 3202J	J	3.18	0.20	20.0	18.0								●					
DGN 4003J	J	4.00	0.30	18.9	∞	●	●	●		●	●	●	●	●			●	
DGN 5003J	J	5.00	0.30	18.9	∞		●	●			●	●	●	●			●	
DGN 6303J	J	6.35	0.35	19.0	∞		●	●			●	▲	●	●			●	
DGN 1400JS	JS	1.40	0.02	15.4	15.0								●					
DGN 2200JS	JS	2.20	0.02	19.4	18.0		●					●	●					
DGN 3100JS	JS	3.10	0.02	19.9	18.0	●	●						●					
DGN 2002JT	JT	2.00	0.20	19.8	18.0						●							
DGN 2202JT	JT	2.20	0.20	19.8	18.0						●	●			▲			
DGN 3102JT	JT	3.10	0.20	20.1	18.0						●	●			▲			
DGN 2202UA	UA	2.20	0.20	19.9	18.0		●	●						●				
DGN 3003UA	UA	3.00	0.25	20.5	18.0	○	●	●						●			○	
DGN 3003UT	UT	3.00	0.25	20.5	18.0	○							●					
DGN 4003UT	UT	4.00	0.30	19.3	∞	○	○	○					●					
DGN 5003UT	UT	5.00	0.30	19.0	∞	○	○	○					●	○				
DGN 6008UT	UT	6.00	0.80	19.1	∞		○	○					●					
DGN 1000P	P	1.00	0.05	20.0	3.0					●								
DGN 1500P	P	1.50	0.05	20.0	18.0						●							
DGN 2000P	P	2.00	0.05	20.0	18.0							●						
DGN 3000P	P	3.00	0.05	20.0	18.0							●						
DGN 2002Z	Z	2.00	0.20	21.0	18.0							●		●				
DGN 3002Z	Z	3.00	0.20	21.0	18.0							●		●				
DGN 1900WP	WP	1.90	0.05	19.7	6.0		○											
DGN 2400WP	WP	2.39	0.05	20.4	5.0		○											
DGN 2202LF	LF	2.20	0.20	19.8	18.0								●		▲			
DGN 3102LF	LF	3.10	0.20	20.1	18.0							●	●	▲	▲			
DGN 3102LFT	LF	3.10	0.20	21.1	18.0									▲				
DGN 2002MF	MF	2.00	0.20	19.9	18.0							▲	▲		▲			
DGN 3002MF	MF	3.00	0.20	20.1	18.0										▲			

4mm幅以上のチップは、ねじれ刃構造(1~3mm幅チップはねじれていません)。