


# SPB・SPE・SPC

ねじ込み形管継手

## SPB 六角プラグ (テーパねじ)


単位：mm



継手の呼び	T (R)	H (六角)	l	l <sub>1</sub>	重量 (kg)
SPB02-000F	1/4	17	13	8	0.029
SPB03-000F	3/8	19	14	8	0.043
SPB04-000F	1/2	24	17	9	0.077
SPB06-000F	3/4	30	19	10	0.13
SPB08-000F	1	36	22	11	0.25
SPB10-000F	1 1/4	46	24	12	0.45
SPB12-000F	1 1/2	50	24	14	0.60
SPB16-000F	2	65	28	16	1.11

## SPE 六角プラグ (平行ねじ)


単位：mm



継手の呼び	T1 (G)	l <sub>1</sub>	l <sub>2</sub>	K	H (六角)	O-Ring	重量 (kg)
SPE01-000J	1/8	8	7	14	14	P 8	0.012
SPE02-000J	1/4	12	9	19	19	P11	0.032
SPE03-000J	3/8	12	10	22	22	P14	0.049
SPE04-000J	1/2	14	13	27	27	P18	0.095
SPE06-000J	3/4	16	16	36	36	P24	0.20
SPE08-000J	1	18	18	41	41	P29	0.31
SPE10-000J	1 1/4	20	21	50	50	P38	0.55
SPE12-000J	1 1/2	21	21	55	55	P44	0.70
SPE16-000J	2	25	23	75	75	P56	1.38

## SPC 四角頭付プラグ

単位：mm



継手の呼び	T (R)	H	l <sub>1</sub>	l <sub>2</sub>	重量 (kg)
SPC01-000J	1/8	7	9	7	0.007
SPC02-000J	1/4	9	12	8	0.016
SPC03-000J	3/8	12	13	9	0.03
SPC04-000J	1/2	14	16	10	0.054
SPC06-000J	3/4	17	18	11	0.096
SPC08-000J	1	19	20	12	0.16
SPC10-000J	1 1/4	24	22	13	0.28
SPC12-000J	1 1/2	27	22	14	0.37
SPC16-000J	2	32	26	15	0.66

材質：S10C又はS25C