


スモウカムヘッド

加工径 6.0mm~32.9mm



ICP (鋼・合金鋼用)

*販売単位：2個

型番	寸法(mm)		PVDコーティング	
	φD	s±0.05	IC908	
ICP 06 (0~4)	6.0~6.4	4.00	●	
ICP 06 (5~9)	6.5~6.9	4.30	●	
ICP 07 (0~9)	7.0~7.9	4.60	●	
ICP 08 (0~9)	8.0~8.9	5.40	●	
ICP 09 (0~9)	9.0~9.9	5.80	●	
ICP 10 (0~9)	10.0~10.9	6.20	●	
ICP 11 (0~9)	11.0~11.9	6.60	●	
ICP 12 (0~9)	12.0~12.9	7.00	●	
ICP 13 (0~9)	13.0~13.9	7.60	●	
ICP 14 (0~9)	14.0~14.9	8.15	●	
ICP 15 (0~9)	15.0~15.9	8.73	●	
ICP 16 (0~9)	16.0~16.9	9.30	●	
ICP 17 (0~9)	17.0~17.9	9.90	●	
ICP 18 (0~9)	18.0~18.9	10.50	●	
ICP 19 (0~9)	19.0~19.9	11.00	●	
ICP 20 (0~9)	20.0~20.9	11.60	●	
ICP 21 (0~9)	21.0~21.9	12.20	●	
ICP 22 (0~9)	22.0~22.9	12.80	●	
ICP 23 (0~9)	23.0~23.9	13.30	●	
ICP 24 (0~9)	24.0~24.9	13.90	●	
ICP 25 (0~9)	25.0~25.9	14.50	●	
ICP 26 (0~9)	26.0~26.9	15.05	●	
ICP 27 (0~9)	27.0~27.9	15.65	●	
ICP 28 (0~9)	28.0~28.9	16.20	●	
ICP 29 (0~9)	29.0~29.9	16.80	●	
ICP 30 (0~9)	30.0~30.9	17.40	●	
ICP 31 (0~9)	31.0~31.9	17.95	●	
ICP 32 (0~9)	32.0~32.9	18.55	●	

0.1mmとびで6.0mm~の径寸法を在庫。

ICM (ステンレス・耐熱鋼用)

*販売単位：2個

型番	寸法(mm)		PVDコーティング	
	φD	s±0.05	IC907	IC908
ICM 06 (0~4)	6.0~6.4	4.00		●
ICM 06 (5~9)	6.5~6.9	4.30		●
ICM 07 (0~9)	7.0~7.9	4.60	▲	●
ICM 08 (0~9)	8.0~8.9	5.40	▲	●
ICM 09 (0~9)	9.0~9.9	5.80	▲	●
ICM 10 (0~9)	10.0~10.9	6.20	▲	●
ICM 11 (0~9)	11.0~11.9	6.60	▲	●
ICM 12 (0~9)	12.0~12.9	7.00	▲	●
ICM 13 (0~9)	13.0~13.9	7.60	▲	●
ICM 14 (0~9)	14.0~14.9	8.15	▲	●
ICM 15 (0~9)	15.0~15.9	8.73	▲	●
ICM 16 (0~9)	16.0~16.9	9.30	▲	●
ICM 17 (0~9)	17.0~17.9	9.90	▲	●
ICM 18 (0~9)	18.0~18.9	10.50	▲	●
ICM 19 (0~9)	19.0~19.9	11.00	▲	●
ICM 20 (0~9)	20.0~20.9	11.60	▲	●
ICM 21 (0~9)	21.0~21.9	12.20	▲	●
ICM 22 (0~9)	22.0~22.9	12.80		●
ICM 23 (0~9)	23.0~23.9	13.30		●
ICM 24 (0~9)	24.0~24.9	14.00		●
ICM 25 (0~9)	25.0~25.9	14.50		●
ICM 26 (0~9)	26.0~26.9	15.05		●
ICM 27 (0~9)	27.0~27.9	15.65		●
ICM 28 (0~9)	28.0~28.9	16.20		●
ICM 29 (0~9)	29.0~29.9	16.80		●
ICM 30 (0~9)	30.0~30.9	17.40		●
ICM 31 (0~9)	31.0~31.9	17.95		●
ICM 32 (0~9)	32.0~32.9	18.55		●

0.1mmとびで6.0mm~の径寸法を在庫。

ICK (鋳鉄用)

*販売単位：2個

型番	寸法(mm)		PVDコーティング	
	φD	s±0.05	IC907	IC908
ICK 06 (0~4)	6.0~6.4	4.00		●
ICK 06 (5~9)	6.5~6.9	4.30		●
ICK 07 (0~9)	7.0~7.9	4.60		●
ICK 08 (0~9)	8.0~8.9	5.40	▲	●
ICK 09 (0~9)	9.0~9.9	5.80	▲	●
ICK 10 (0~9)	10.0~10.9	6.20	▲	●
ICK 11 (0~9)	11.0~11.9	6.60	▲	●
ICK 12 (0~9)	12.0~12.9	7.00	▲	●
ICK 13 (0~9)	13.0~13.9	7.60	▲	●
ICK 14 (0~9)	14.0~14.9	8.15	▲	●
ICK 15 (0~9)	15.0~15.9	8.73	▲	●
ICK 16 (0~9)	16.0~16.9	9.30	▲	●
ICK 17 (0~9)	17.0~17.9	9.90	▲	●
ICK 18 (0~9)	18.0~18.9	10.50	▲	●
ICK 19 (0~9)	19.0~19.9	11.00	▲	●
ICK 20 (0~9)	20.0~20.9	11.60	▲	●
ICK 21 (0~9)	21.0~21.9	12.20	▲	●
ICK 22 (0~9)	22.0~22.9	12.80	▲	●
ICK 23 (0~9)	23.0~23.9	13.30	▲	●
ICK 24 (0~9)	24.0~24.9	13.90	▲	●
ICK 25 (0~9)	25.0~25.9	14.50	▲	●
ICK 26 (0~9)	26.0~26.9	15.05	▲	●
ICK 27 (0~9)	27.0~27.9	15.65	▲	●
ICK 28 (0~9)	28.0~28.9	16.20	▲	●
ICK 29 (0~9)	29.0~29.9	16.80	▲	●
ICK 30 (0~9)	30.0~30.9	17.40	▲	●
ICK 31 (0~9)	31.0~31.9	17.95	▲	●
ICK 32 (0~9)	32.0~32.9	18.55	▲	●

0.1mmとびで6.0mm~の径寸法を在庫。

* φD20mm以上は1個から販売可能です。

