



カムドリル(ヘッド交換式ドリルボディ)

DCM-3D、DCM-5D
加工径 7.5mm~25.9mm



加工深さ : 3×D

DCM 075~DCM 210

DCM 220~DCM 250

型番	在庫	寸法(mm)							脱着キー		適合ヘッド
		φD加工径	φPd	L	L ₁ ⁽¹⁾	L ₂	φd	φd ₁	付属品	オプション*	
DCM 075-022-12A-3D	●	7.5-7.9	7	22	33.1	45	12	16	KDCM-8	TKDCM-8	IDI 075~079
DCM 080-024-12A-3D	●	8.0-8.4	8	24	35.0	45	12	16	KDCM-8	TKDCM-8	IDI 080~084
DCM 085-025-12A-3D	●	8.5-8.9	8	25	37.0	45	12	16	KDCM-8	TKDCM-8	IDI 085~089
DCM 090-027-12A-3D	●	9.0-9.4	9	27	39.1	45	12	16	KDCM-9	TKDCM-9	IDI 090~094
DCM 095-028-12A-3D	●	9.5-9.9	9	28	41.1	45	12	16	KDCM-9	TKDCM-9	IDI 095~099
DCM 100-030-16A-3D	●	10.0-10.4	10	30	44.0	48	16	20	KDCM-10	TKDCM-10	IDI 100~104
DCM 105-031-16A-3D	●	10.5-10.9	10	31	46.0	48	16	20	KDCM-10	TKDCM-10	IDI 105~109
DCM 110-033-16A-3D	●	11.0-11.4	11	33	48.1	48	16	20	KDCM-11	TKDCM-11	IDI 110~114
DCM 115-034-16A-3D	●	11.5-11.9	11	34	50.0	48	16	20	KDCM-11	TKDCM-11	IDI 115~119
DCM 120-036-16A-3D	●	12.0-12.4	12	36	52.2	48	16	20	KDCM-12	TKDCM-12	IDI 120~124
DCM 125-037-16A-3D	●	12.5-12.9	12	37	53.8	48	16	20	KDCM-12	TKDCM-12	IDI 125~129
DCM 130-039-16A-3D	●	13.0-13.4	13	39	56.5	48	16	20	KDCM-13	TKDCM-13	IDI 130~134
DCM 135-040-16A-3D	●	13.5-13.9	13	40	58.5	48	16	20	KDCM-13	TKDCM-13	IDI 135~139
DCM 140-042-16A-3D	●	14.0-14.4	14	42	61.2	48	16	20	KDCM-14	TKDCM-14	IDI 140~144
DCM 145-043-16A-3D	●	14.5-14.9	14	43	63.2	48	16	20	KDCM-14	TKDCM-14	IDI 145~149
DCM 150-045-20A-3D	●	15.0-15.9	15	45	65.7	50	20	25	KDCM-15	TKDCM-15	IDI 150~159
DCM 160-048-20A-3D	●	16.0-16.9	16	48	70.0	50	20	25	KDCM-16	TKDCM-16	IDI 160~169
DCM 170-051-20A-3D	●	17.0-17.9	17	51	73.5	50	20	25	KDCM-17	TKDCM-17	IDI 170~179
DCM 180-054-25A-3D	●	18.0-18.9	18	54	78.3	56	25	32	KDCM-18	TKDCM-18	IDI 180~189
DCM 190-057-25A-3D	●	19.0-19.9	19	57	82.3	56	25	32	KDCM-19	TKDCM-19	IDI 190~199
DCM 200-060-25A-3D	●	20.0-20.9	20	60	87.0	56	25	32	KDCM-20	TKDCM-20	IDI 200~209
DCM 210-063-25A-3D	●	21.0-21.9	21	63	90.8	56	25	32	KDCM-21	TKDCM-21	IDI 210~219
DCM 220-066-25A-3D	●	22.0-22.9	22	66	95.1	56	25	32	KDCM-22	TKDCM-22	IDI 220~229
DCM 230-069-25A-3D	●	23.0-23.9	23	69	99.5	56	25	32	KDCM-23	TKDCM-23	IDI 230~239
DCM 240-072-25A-3D	●	24.0-24.9	24	72	103.6	56	25	32	KDCM-24	TKDCM-24	IDI 240~249
DCM 250-075-25A-3D	●	25.0-25.9	25	75	109.0	56	25	32	KDCM-25	TKDCM-25	IDI 250~259

加工深さ : 5×D

型番	在庫	寸法(mm)							脱着キー		適合ヘッド
		φD加工径	φPd	L	L ₁ ⁽¹⁾	L ₂	φd	φd ₁	付属品	オプション*	
DCM 075-037-12A-5D	●	7.5-7.9	7	37	48.1	45	12	16	KDCM-8	TKDCM-8	IDI 075~079
DCM 080-040-12A-5D	●	8.0-8.4	8	40	51.0	45	12	16	KDCM-8	TKDCM-8	IDI 080~084
DCM 085-042-12A-5D	●	8.5-8.9	8	42	54.0	45	12	16	KDCM-8	TKDCM-8	IDI 085~089
DCM 090-045-12A-5D	●	9.0-9.4	9	45	57.1	45	12	16	KDCM-9	TKDCM-9	IDI 090~094
DCM 095-047-12A-5D	●	9.5-9.9	9	47	60.1	45	12	16	KDCM-9	TKDCM-9	IDI 095~099
DCM 100-050-16A-5D	●	10.0-10.4	10	50	64.0	48	16	20	KDCM-10	TKDCM-10	IDI 100~104
DCM 105-052-16A-5D	●	10.5-10.9	10	52	67.0	48	16	20	KDCM-10	TKDCM-10	IDI 105~109
DCM 110-055-16A-5D	●	11.0-11.4	11	55	70.1	48	16	20	KDCM-11	TKDCM-11	IDI 110~114
DCM 115-057-16A-5D	●	11.5-11.9	11	57	73.0	48	16	20	KDCM-11	TKDCM-11	IDI 115~119
DCM 120-060-16A-5D	●	12.0-12.4	12	60	76.2	48	16	20	KDCM-12	TKDCM-12	IDI 120~124
DCM 125-062-16A-5D	●	12.5-12.9	12	62	79.2	48	16	20	KDCM-12	TKDCM-12	IDI 125~129
DCM 130-065-16A-5D	●	13.0-13.4	13	65	82.5	48	16	20	KDCM-13	TKDCM-13	IDI 130~134
DCM 135-067-16A-5D	●	13.5-13.9	13	67	85.5	48	16	20	KDCM-13	TKDCM-13	IDI 135~139
DCM 140-070-16A-5D	●	14.0-14.4	14	70	89.2	48	16	20	KDCM-14	TKDCM-14	IDI 140~144
DCM 145-072-16A-5D	●	14.5-14.9	14	72	92.2	48	16	20	KDCM-14	TKDCM-14	IDI 145~149
DCM 150-075-20A-5D	●	15.0-15.9	15	75	95.7	50	20	25	KDCM-15	TKDCM-15	IDI 150~159
DCM 160-080-20A-5D	●	16.0-16.9	16	80	102.0	50	20	25	KDCM-16	TKDCM-16	IDI 160~169
DCM 170-085-20A-5D	●	17.0-17.9	17	85	107.5	50	20	25	KDCM-17	TKDCM-17	IDI 170~179
DCM 180-090-25A-5D	●	18.0-18.9	18	90	114.3	56	25	32	KDCM-18	TKDCM-18	IDI 180~189
DCM 190-095-25A-5D	●	19.0-19.9	19	95	120.3	56	25	32	KDCM-19	TKDCM-19	IDI 190~199
DCM 200-100-25A-5D	●	20.0-20.9	20	100	127.0	56	25	32	KDCM-20	TKDCM-20	IDI 200~209
DCM 210-105-25A-5D	●	21.0-21.9	21	105	132.8	56	25	32	KDCM-21	TKDCM-21	IDI 210~219
DCM 220-110-25A-5D	●	22.0-22.9	22	110	139.1	56	25	32	KDCM-22	TKDCM-22	IDI 220~229
DCM 230-115-25A-5D	●	23.0-23.9	23	115	145.5	56	25	32	KDCM-23	TKDCM-23	IDI 230~239
DCM 240-120-25A-5D	●	24.0-24.9	24	120	151.6	56	25	32	KDCM-24	TKDCM-24	IDI 240~249
DCM 250-125-25A-5D	●	25.0-25.9	25	125	159.0	56	25	32	KDCM-25	TKDCM-25	IDI 250~259

⁽¹⁾ L₁はIDI...-SG,SKヘッド装着時の寸法です。

ドリル本体より大径のドリルヘッドをご使用下さい。(加工径φDのサイズのヘッドが装着出来ます。)

*オプション脱着キー(詳細H25頁)。標準脱着キーは付属します。

適合ヘッドはH26頁をご参照下さい。