

85A Wheel

85A is a mono-crystalline alumina abrasive. It offers higher grinding performance than pink colored alundum abrasives. 85A wheel provides higher hardness, longer wheel life, and lower grinding force than pink colored wheel in surface grinding.

[Applications] Grinding hardened alloy steels, tool steels, and high carbon steels.



Item No.	Size (mm)			Spec.	M.O.S.	Packing	Remarks
	O.D.	Thk.	Hole				
S850001	180	6.4	31.75	85A 60 J	40	20	
S850002	180	6.4	31.75	85A 60 K	40	20	
S850003	180	6.4	31.75	85A 80 J	40	20	
S850004	180	6.4	31.75	85A 80 K	40	20	
S850005	180	6.4	31.75	85A 100 J	40	20	
S850006	180	6.4	31.75	85A 100 K	40	20	
S850007	180	6.4	31.75	85A 120 J	40	20	
S850008	180	6.4	31.75	85A 120 K	40	20	
S850018	180	10	31.75	85A 46 K	40	20	
S850019	180	10	31.75	85A 60 J	40	20	
S850020	180	10	31.75	85A 60 K	40	20	
S850021	180	10	31.75	85A 80 J	40	20	
S850022	180	10	31.75	85A 80 K	40	20	
S850023	180	10	31.75	85A 100 J	40	20	
S850024	180	10	31.75	85A 100 K	40	20	
S850025	180	13	31.75	85A 46 H	40	20	
S850026	180	13	31.75	85A 46 I	40	20	
S850027	180	13	31.75	85A 46 J	40	20	
S850028	180	13	31.75	85A 46 K	40	20	
S850029	180	13	31.75	85A 60 H	40	20	
S850030	180	13	31.75	85A 60 I	40	20	
S850031	180	13	31.75	85A 60 J	40	20	
S850032	180	13	31.75	85A 60 K	40	20	
S850033	180	13	31.75	85A 80 H	40	20	
S850035	180	13	31.75	85A 80 J	40	20	
S850036	180	13	31.75	85A 80 K	40	20	
S850037	180	13	31.75	85A 100 J	40	20	
S850038	180	13	31.75	85A 100 K	40	20	
S850039	180	16	31.75	85A 46 J	40	20	
S850042	180	16	31.75	85A 60 K	40	20	
S850043	180	16	31.75	85A 80 J	40	20	

Item No.	Size (mm)			Spec.	M.O.S.	Packing	Remarks
	O.D.	Thk.	Hole				
S850045	180	19	31.75	85A 46 J	40	20	
S850047	180	19	31.75	85A 60 J	40	20	
S850049	180	19	31.75	85A 80 J	40	20	
S850050	180	19	31.75	85A 80 K	40	20	
S850051	205	6.4	31.75	85A 60 J	40	20	
S850052	205	6.4	31.75	85A 60 K	40	20	
S850053	205	6.4	31.75	85A 80 J	40	20	
S850054	205	6.4	31.75	85A 80 K	40	20	
S850055	205	6.4	31.75	85A 100 K	40	20	
S850056	205	13	31.75	85A 46 H	40	20	
S850057	205	13	31.75	85A 46 I	40	20	
S850058	205	13	31.75	85A 46 J	40	20	
S850059	205	13	31.75	85A 46 K	40	20	
S850060	205	13	31.75	85A 60 H	40	20	
S850062	205	13	31.75	85A 60 J	40	20	
S850064	205	13	31.75	85A 80 H	40	20	
S850065	205	13	31.75	85A 80 I	40	20	
S850066	205	13	31.75	85A 80 J	40	20	
S850067	205	13	31.75	85A 80 K	40	20	
S850068	205	19	31.75	85A 46 H	40	10	
S850069	205	19	31.75	85A 46 I	40	10	
S850070	205	19	31.75	85A 46 J	40	10	
S850072	205	19	31.75	85A 60 H	40	10	
S850073	205	19	31.75	85A 60 I	40	10	
S850075	205	19	31.75	85A 60 K	40	10	
S850076	205	19	31.75	85A 80 H	40	10	
S850077	205	19	31.75	85A 80 I	40	10	
S850078	205	19	31.75	85A 80 J	40	10	
S850079	205	19	31.75	85A 80 K	40	10	
S850080	205	19	50.8	85A 46 H	40	10	
S850082	205	19	50.8	85A 46 J	40	10	
S850084	205	19	50.8	85A 60 H	40	10	
S850085	205	19	50.8	85A 60 I	40	10	
S850086	205	19	50.8	85A 60 J	40	10	
S850089	205	19	50.8	85A 80 I	40	10	
S850090	205	19	50.8	85A 80 J	40	10	
S850091	205	19	50.8	85A 80 K	40	10	

Depressed Center Wheel

Flexible Depressed Center Wheel

Cutting-off Wheel

Coated Abrasives/ Non-Woven Abrasives

Alumina Fiber Stones

Mounted Wheel

Straight Wheel

Other Shapes

Diamond /CBN Wheel

Truing & Dressing Tools

Grinding & Cutting Fluids

Filter

Safety Products