

CB Touch



【Applications】

- Hardened dies steels / Tool steels

【Features & Benefits】

- High grinding performance for hardened steels.
- Easy dressing with single-point dresser.
- Suitable for surface grinding of dies steels and tool steels, etc.
- Suitable for either wet or dry grinding.

Item No.	Size (mm)				Grit size	M.O.S. (m/s)	Packing	Remarks
	O.D.	Thk.	Hole	Rim Width				
SCV0001	150	6	31.75	5	170	40	1	
SCV0002	150	10	31.75	5	170	40	1	
SCV0003	180	6	31.75	3	170	40	1	
SCV0004	180	6	31.75	5	170	40	1	
SCV0005	180	10	31.75	3	170	40	1	
SCV0006	180	10	31.75	5	170	40	1	
SCV0007	180	13	31.75	3	170	40	1	
SCV0008	180	13	31.75	5	170	40	1	
SCV0009	200	10	31.75	3	170	40	1	
SCV0010	200	10	31.75	5	170	40	1	
SCV0011	200	10	50.8	3	170	40	1	
SCV0012	200	10	50.8	5	170	40	1	
SCV0013	200	13	31.75	3	170	40	1	
SCV0014	200	13	31.75	5	170	40	1	
SCV0015	200	13	50.8	3	170	40	1	
SCV0016	200	13	50.8	5	170	40	1	
SCV0017	200	15	31.75	3	170	40	1	
SCV0018	200	15	50.8	3	170	40	1	
SCV0019	300	15	76.2	3	170	40	1	
SCV0020	300	15	127	3	170	40	1	
SCV0021	300	25	76.2	3	170	40	1	
SCV0022	300	25	127	3	170	40	1	

Mighty Touch



【Applications】

- Hardened dies steels / Tool steels

【Features & Benefits】

- Less surface roughness and superior durability.
- Easy dressing with single-point dresser.
- Suitable for surface grinding of dies steel and tool steel, etc.
- Must be used in wet grinding.

Item No.	Size (mm)				Grit size	M.O.S. (m/s)	Packing	Remarks
	O.D.	Thk.	Hole	Rim Width				
SMV0101	150	6	31.75	5	170	45	1	
SMV0102	150	10	31.75	5	170	45	1	
SMV0103	180	6	31.75	3	170	45	1	
SMV0104	180	6	31.75	5	170	45	1	
SMV0105	180	10	31.75	3	170	45	1	
SMV0106	180	10	31.75	5	170	45	1	
SMV0107	180	13	31.75	3	170	45	1	
SMV0108	180	13	31.75	5	170	45	1	
SMV0109	200	10	31.75	3	170	45	1	
SMV0110	200	10	31.75	5	170	45	1	
SMV0111	200	10	50.8	3	170	45	1	
SMV0112	200	10	50.8	5	170	45	1	
SMV0113	200	13	31.75	3	170	45	1	
SMV0114	200	13	31.75	5	170	45	1	
SMV0115	200	13	50.8	3	170	45	1	
SMV0116	200	13	50.8	5	170	45	1	
SMV0117	200	15	31.75	3	170	45	1	
SMV0118	200	15	50.8	3	170	45	1	
SMV0119	300	15	76.2	3	170	45	1	
SMV0120	300	15	127	3	170	45	1	
SMV0121	300	25	76.2	3	170	45	1	
SMV0122	300	25	127	3	170	45	1	
SMV0123	350	25	127	3	170	45	1	