



SUSFBN60B

● Order No. Example

SUS FBN 60B 18 D28



- ChainNo.60
- Chain Pitch(P)19.05mm
- Roller Link Inner Width(W)12.70mm
- Roller Outside Diameter(Dr)11.91mm
- Tooth Width(T)11.7 mm

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Boss Diameter BD	Boss Length BL	a	Weight kg
SUS FBN 60B	10	68	61.65	★49	32	6	0.49
	11	76	67.62	★51	32	6	0.60
	12	83	73.60	51	32	8	0.69
	13	89	79.60	57	32	8	0.81
	14	95	85.61	62	32	8	0.96
	15	101	91.62	68	32	8	1.10
	16	107	97.65	73	32	8	1.30
	17	113	103.67	73	32	8	1.40
	18	119	109.71	83	40	12	2.00
	19	126	115.74	83	40	12	2.10
	20	132	121.78	83	40	12	2.20
	21	138	127.82	83	40	12	2.30
	22	144	133.86	83	40	12	2.50
	23	150	139.90	83	40	12	2.50
	24	156	145.95	83	40	12	2.60
	25	162	151.99	83	40	12	2.70
30	193	182.25	83	40	12	3.30	