



40SD



SD Single-Double Sprocket

Order No. Example



- Chain No.40
- Chain Pitch (P)12.70mm
- Roller Link Inner Width (W) 7.95mm
- Roller Outside Diameter (Dr) 7.92mm
- Tooth Width (T) 7.2 mm (C)27.8mm

- m Carbon Structural Steel
- h High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum	Maximum					
40SD	10	47	41.10	10	11	15	25	35	0.20		
	11	51	45.08	10	11	16	30	35	0.27		
	12	55	49.07	10	11	18	34	35	0.33		
	13	59	53.07	13	14	20	38	35	0.40		
	14	63	57.07	13	14	25	42	35	0.49		
	15	67	61.08	13	14	28	46	35	0.57		
	16	71	65.10	13	14	30	50	35	0.66		
	17	76	69.12	13	14	32	54	35	0.76		
	18	80	73.14	13	14	38	59	35	0.89		
	19	84	77.16	13	14	42	63	35	1.00		
	20	88	81.18	13	14	45	67	35	1.14		
	21	92	85.21	13	14	48	71	35	1.23		
	22	96	89.24	13	14	50	75	35	1.38		
	23	100	93.27	13	14	52	78	35	1.51		
	24	104	97.30	13	14	55	83	35	1.68		
	25	108	101.33	13	14	58	87	35	1.84		
	26	112	105.36	13	14	62	92	35	2.02		
	27	116	109.40	16	17	65	96	35	2.04		
	28	120	113.43	16	17	68	100	35	2.22		
	29	124	117.46	16	17	70	104	35	2.56		
	30	128	121.50	16	17	75	108	35	2.75		



Sprocket No. and Quantity



* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.



Same-day shipping

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.